



Materials Declaration Form

IPC Form Type *	1752 Distribute	Version	2
Sectionals *	Material Info Manufacturing Info	Subsectionals *	A-D
<i>* : Required Field</i>			

Supplier Information			
Company Name *	STMicroelectronics	Response Date *	2016-04-15
Contact Name *	Refer to Supplier Comment section		Refer to Supplier Comment section
Authorized Representative *	Giovanni Giacopello	Representative Title	IPD MD Champion
Representative Phone *	Refer to Supplier Comment section	Representative Email *	Refer to Supplier Comment section
Supplier Comment	Online Technical Support - STMicroelectronics : http://www.st.com/web/en/support/support.html		

Uncertainty Statement


While STMicroelectronics has endeavored to provide information which is accurate and up to date, this document and its contents are provided on a strict 'as is' and 'as available' basis. STMicroelectronics disclaims all warranties, express or implied related to this document and its contents, including but not limited to implied warranties of completeness, truth, accuracy, merchantability, fitness for a particular purpose and non-infringement. ST shall have no responsibility and assumes no liability for any cost, loss or damage of any kind which could arise, directly or indirectly, from the use or inability to use this document and/or its contents.

Legal Statement			
Supplier Acceptance *	true	Legal Declaration *	Standard

Legal Statement

Supplier certifies that it gathered the provided information and such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Supplier's liability and the Company's remedies for issues that arise regarding information the Supplier provides in this form.

Product				
Mfr Item Number	Mfr Item Name	Version	Mfr Site	Date
BU508AW	TSLW*BT24E62	A	SHENZHEN B/E	2016-04-15
	Amount	UoM	Unit type	ST ECOPACK Grade
	4430.00	mg	Each	ECOPACK2

Manufacturing information				
J-STD-020 MSL Rating	Classification Temp	Nbr of Reflow Cycles		 life.augmented
NAC	NAC	NAC		
bulk Solder Termination	Terminal Plating	Terminal Base Alloy	Comment	
NAC	Tin (Sn), matte	Copper Alloy		

Package Designator	Size	Nbr of instances	Shape	
SIP	15.75-20.15-5.15	2	THROUGH HOLE	
Comment	TO 247			

QueryList : ROHS directive 2011/65/EU _ July 2011	
Query	Response
1 - Product(s) meets EU RoHS requirement without any exemptions	false
2 - Product(s) meets EU RoHS requirements except lead in solder and this usage may qualify under the lead in solder '7b' exemption (other selected exemptions may apply)	false
3 - Product(s) meets EU RoHS requirements by application of the selected exemption(s)	true
4 - Product(s) does not meet EU RoHS requirements and is not under exemptions	false
5 - Product(s) is obsolete, no information is available	false
6 - Product(s) is unknown, no information is available	false
Exemption Id.	Description
7a	Lead in high melting temperature type solders (i.e. lead- based alloys containing 85 % by weight or more lead)

QueryList : REACH-17th December 2015				
Query				Response
1 - Product(s) does not contain REACH Substances Of Very High Concern above the limits per the definition within REACH				true
CategoryLevel_Name	CategoryLevel_Threshold	amount in product (mg)	Application	ppm in product

Material Composition Declaration						Mfr Item Name	TSLW*BT24E2					
Homogeneous Material	Material Group	Mass	UoM	Level	Substance Category	Substance	CAS	Exempt	Mass	UoM	Concentration in homogeneous material (ppm)	Concentration in product (ppm)
Die	Other inorganic materials	10.526	mg	supplier	die	Silicon (Si)	7440-21-3		10.116	mg	961049	2284
				supplier	metallization	Aluminium (Al)	7429-90-5		0.144	mg	13680	33
				supplier	Passivation	Silicon Oxide	7631-86-9		0.164	mg	15580	37
				supplier	back side metallization	Titanium (Ti)	7440-32-6		0.006	mg	571	1
				supplier	back side metallization	Gold (Au)	7440-57-5		0.017	mg	1615	4
				supplier	back side metallization	Nickel (Ni)	7440-02-0		0.079	mg	7505	18
Leadframe	Copper & its alloys	2720.611	mg	supplier	alloy	Copper (Cu)	7440-50-8		2705.048	mg	994280	610620
				supplier	alloy	Iron (Fe)	7439-89-6		1.246	mg	458	281
				supplier	alloy	Iron Phosphide (FeP)	26508-33-8		2.275	mg	836	514
				supplier	metallization	Nickel (Ni)	7440-02-0		11.968	mg	4399	2702
				supplier	metallization	Phosphorus (P)	12185-10-3		0.074	mg	27	17
				supplier	metallization	Phosphorus (P)	12185-10-3		0.074	mg	27	17
Soft solder	Solder	10.737	mg	JIG - R	solder	Lead (Pb)	7439-92-1	7a-Lead in high me	10.254	mg	955015	2315
				supplier	solder	Silver (Ag)	7440-22-4		0.268	mg	24961	60
				supplier	solder	Tin (Sn)	7440-31-5		0.215	mg	20024	49
Bonding wires	Other inorganic materials	0.416	mg	supplier	wire	Aluminium (Al)	7429-90-5		0.415	mg	998076	93
				supplier	wire	Magnesium (Mg)	7439-95-4		0.001	mg	1924	0
				supplier	mold compound	Silica, vitreous	60676-86-0		1462.916	mg	870000	330229
Encapsulation	Other Organic Materials	1681.513	mg	supplier	mold compound	Epoxy resin	25068-38-6		168.151	mg	100000	37957
				supplier	mold compound	Phenol resin	29690-82-2		42.038	mg	25000	9489
				supplier	mold compound	Carbon black	1333-86-4		8.408	mg	5000	1898
Connections coating	Solder	6.197	mg	supplier	solder alloy	Tin (Sn)	7440-31-5		6.197	mg	1000000	1399