



AN4147

Application note

Using the SPIRIT1 transceiver under FCC title 47 part 15 in the 315 MHz band

By Placido De Vita

Introduction

The SPIRIT1 is a very low power RF transceiver, intended for RF wireless applications in the sub-1 GHz band. It is designed to operate in both the license-free ISM and SRD frequency bands at 169, 315, 433, 868, 915 and 920 MHz.

This application note outlines the expected performance when using the SPIRIT1 under FCC title 47 part 15 [2] in the 315 MHz band. There are no specific requirements in this band, no specific use and no channel spacing are defined.

For details on the regulatory limits in the 315 MHz frequency band, please refer to the FCC Title 47 Part 15 regulations [2].

These can be downloaded from:
http://wireless.fcc.gov/index.htm?job=rules_and_regulations.

Contents

1	An overview of FCC regulations	3
1.1	Part 15.231	3
1.2	Parts 15.205 and 15.209	4
2	Application circuit	6
3	Transmitter parameter	9
3.1	Spurious RF conducted emission	10
4	Receiver parameter	12
5	Reference	12
6	Revision history	13

1 An overview of FCC regulations

1.1 Part 15.231

Devices operating in the 315 MHz band must comply with section 15.231 of the FCC Title 47 Part 15 [2] regulations. The provisions in section 15.231 are restricted to periodic operation within the 40.66 - 40.70 MHz band and above 70 MHz. The intentional radiator is restricted to the transmission of a control signal such as those used with alarm systems, door openers, remote switches, etc. Continuous transmissions, voice, video and radio control of toys are not permitted. Data is permitted to be sent with a control signal.

To comply with the provisions for periodic operation, the following conditions must be met:

- A manually operated transmitter shall employ a switch that will automatically deactivate the transmitter within not more than 5 seconds of being released. A transmitter activated automatically shall cease transmission within 5 seconds after activation.
- Periodic transmissions at regular predetermined intervals are not permitted. However, polling or supervision transmissions, including data, to determine system integrity of transmitters used in security or safety applications are allowed if the total duration of transmissions does not exceed 2 seconds per hour.
- Intentional radiators which are employed for radio control purposes during emergencies involving fire, security and safety of life, when activated to signal an alarm, may operate during the pendency of the alarm condition.
- In addition to the provisions of 15.205, the field strength of emissions from intentional radiators operated under this section shall not exceed the values in [Table 1](#). The field strength limits are specified at a distance of 3 meters.
- The limits on the field strength of the spurious emissions in the [Table 1](#) are based on the fundamental frequency of the intentional radiator. Spurious emissions shall be attenuated to the average limits shown in this table or to the general limits shown in section 15.209, whichever limit permits higher field strength.
- The bandwidth of the emission shall be no wider than 0.25% of the center frequency. Bandwidth is determined at the points 20 dB down from the modulated carrier.
- Intentional radiators may operate at a periodic rate exceeding that specified in point 1 and may be employed for any type of operation, including operation prohibited in point 1. In this case, the max field strength is different and is shown in the [Table 2](#). The device operating in the condition described in this point shall be provided with a means for automatically limiting operation so that the duration of each transmission shall not be greater than 1 second and the silent period between transmissions shall be at least 30 times the duration of the transmission, but in no case less than 10 seconds.

Table 1. Field strength of emissions for normal working conditions

Fundamental frequency [MHz]	Field strength of fundamental [$\mu\text{V}/\text{m}$]	Field strength of spurious emission [$\mu\text{V}/\text{m}$]
40.66 – 40.70	2250	225
70 – 130	1250	125
130 – 174	1250 to 3750	125 to 375
174 – 260	3750	375

Table 1. Field strength of emissions for normal working conditions (continued)

Fundamental frequency [MHz]	Field strength of fundamental [$\mu\text{V/m}$]	Field strength of spurious emission [$\mu\text{V/m}$]
260 – 470	3750 to 12500	375 to 1250
Above 470	12500	1250

Table 2. Field strength of emissions for particular working conditions

Fundamental frequency [MHz]	Field strength of fundamental [$\mu\text{V/m}$]	Field strength of spurious emission [$\mu\text{V/m}$]
40.66 – 40.70	1000	100
70 – 130	500	50
130 – 174	500 to 1500	50 to 150
174 – 260	1500	150
260 – 470	1500 to 5000	150 to 500
Above 470	5000	500

1.2 Parts 15.205 and 15.209

As described in the previous paragraphs, radiated harmonics and spurious emissions of devices that comply with section 15.231 and which fall within the restricted bands, as defined in FCC section 15.205, must comply with the radiated emission limits specified in FCC section 15.209. In addition to the provisions of 15.205, the field strength of emissions from intentional radiators operated under this section shall not exceed the values in [Table 1](#). The field strength limits are specified at a distance of 3 meters.

Section 15.205 shows the bands where only spurious emissions are permitted. The field strength of emissions appearing within these frequency bands shall not exceed the limits shown in section 15.209. The following tables show the restricted bands as defined in section 15.205 and the radiated and conducted emission limits are defined in section 15.209.

Table 3. Restricted bands defined in section 15.205

MHz	MHz	MHz	GHz
0.090 – 0.110	16.42 – 16.423	399.9 – 410	4.5 – 5.15
0.495 – 0.505	16.69475 – 16.69525	608 – 614	5.35 – 5.46
2.1735 – 2.1905	16.80425 – 16.80475	960 – 1240	7.25 – 7.75
4.125 – 4.128	25.5 – 25.67	1300 – 1427	8.025 – 8.5
4.17725 – 4.17775	37.5 – 38.25	1435 – 1626.5	9.0 – 9.2
4.20725 – 4.20775	73 – 74.6	1645.5 – 1646.5	9.3 – 9.5
6.215 – 6.218	74.8 – 75.2	1660 – 1710	10.6 – 12.7
6.26775 – 6.26825	108 – 121.94	1718.8 – 1722.2	13.25 – 13.4

Table 3. Restricted bands defined in section 15.205 (continued)

MHz	MHz	MHz	GHz
6.31175 – 6.31225	123 - 138	2200 – 2300	14.47 – 14.5
8.291 – 8.294	149.9 – 150.05	2310 – 2390	15.35 – 16.2
8.362 – 8.366	156.52475 – 156.52525	2483.5 – 2500	17.7 – 21.4
8.37625 – 8.38675	156.7 – 156.9	2690 – 2900	22.01 – 23.12
8.41425 – 8.41475	162.0125 – 167.17	3260 – 3267	23.6 – 24.0
12.29 – 12.293	167.72 – 173.2	3332 – 3339	31.2 – 31.8
12.51975 – 12.52025	240 – 285	3345.8 – 3358	36.43 – 36.5
12.57675 – 12.57725	322 – 335.4	3600 – 4400	Above 38.6
13.36 – 13.41			

Table 4. Radiated and conducted emission limits defined in section 15.209

Frequency [MHz]	Field strength [$\mu\text{V}/\text{m}$]	Measurement distance [m]	Conducted [dBm]
0.009 – 0.490	$2400/f$ [kHz]	300	$12.4 - 20 \cdot \log(f)_{\text{kHz}}$
0.490 – 1.705	$24000/f$ [kHz]	30	$12.4 - 20 \cdot \log(f)_{\text{kHz}}$
1.705 – 30.0	30	30	- 46
30– 88	100	3	- 56
88 – 216	150	3	- 52
16 – 960	200	3	- 49
960	500	3	- 41

2 Application circuit

Figure 1 shows an image of the SPIRIT1 application board. The application is made up of 2 boards: a daughterboard and a motherboard. The daughterboard contains the SPIRIT1 with the circuits necessary for it to work. For correct functionality, the daughterboard must be plugged into the motherboard (see *Figure 2*) by two header 5x2 connectors (J6 and J7).

The motherboard is provided with an STM32L152VBT6 microcontroller to correctly program the transceiver. The microcontroller is programmed with firmware developed for the SPIRIT1 application. A graphical user interface (GUI) is developed to correctly program the SPIRIT1.

The daughterboard is provided with a 52 MHz XTAL to provide the correct oscillator to the SPIRIT1.

The SPIRIT1 has an internal SMPS that drastically reduces power consumption, making it the best-in-class for applications on this bandwidth. The SMPS is fed from the battery (1.8 V to 3.6 V) and provides the device with a programmable voltage (1.4 V typical). An SMA connector is present to connect the board to an antenna or to instrumentation to verify the correct functionality and verify the ETSI standard request.

A few of passive devices (inductors and capacitors) are used for matching/filtering in the power amplifier (PA) and balun network for the receiver.

To reduce application costs, the SPIRIT1 is designed to work without an external antenna switch. The daughterboard is designed to show the SPIRIT1 functionality in this condition. Clearly, an application with antenna switch can be realized, but this is not described in this document.

Figure 1. SPIRIT1 application daughterboard






Figure 2. SPIRIT1 application daughterboard plugged into the motherboard



AM13147v1

Figure 3. Daughterboard schematic



AM13166v1

3 Transmitter parameter

All of the measurements reported here are measured using the following parameters:
 $T_c = 25\text{ }^\circ\text{C}$, $V_{dd} = 3.0\text{ V}$, $f = 315\text{ MHz}$, unless otherwise specified.

Regarding the output power and emission, the standard specifies the maximum field strength ($\mu\text{V/m}$). Microvolts per meter ($\mu\text{V/m}$) are the units used to describe the strength of an electric field created by the operation of a transmitter. A particular transmitter that generates a constant level of power (watts) can produce electric fields of different strengths depending on the type of antenna connected to it. Because it is the electric field that causes interference to authorized radio communications, and since particular electric field strength does not directly correspond to a particular level of transmitter power, the emission limit of short range devices are specified in field strength.

In order to simplify the testing environment, a conversion from the field strength to output power is done, since the latter is easier to measure. Although the precise relation between power and field strength can depend on a number of additional factors, a commonly-used equation to approximate the field strength (V/m) and the power (W) is:

Equation 1

$$(P * G)/(4 * d^2) = (E^2)/(120 * \Pi)$$

where:

- P = transmitter power (EIRP) in watts
- G = gain of the transmitter antenna relative to an isotropic source
- d = distance of the measuring point from the electrical center of the antenna in meters
- E = field strength in volts/meter
- $4 * d^2$ = surface area of the sphere centered at the radiating source whose surface is d meters from the radiating source
- $120 * \Pi$ = characteristic impedance of free space in ohms

Assuming a unity gain antenna ($G = 1$) and considering the measurement distance of 3 meters ($d = 3$), a formula can be summarized with:

Equation 2

$$P = 0.3 * E^2$$

The field strength of the fundamental at 315 MHz is not given directly but has to be calculated from the two values (260 to 470 MHz) defined in [Table 1](#). The calculated value of the field strength of the fundamental at 315 MHz is $6043.5\text{ }\mu\text{V/m}$ which corresponds, applying the formula above, to a value of - 19.6 dBm at 3 m distance. In a similar manner, the field strength of the spurious emissions must be lower than $604.35\text{ }\mu\text{V/m}$ which corresponds, applying the formula above, to a value of - 35 dBm at 3 m distance.

3.1 Spurious RF conducted emission

According to FCC section 15.231, the field strength of all emissions from intentional radiators outside the fundamental and the band defined in section 15.205 must be lower than the values defined in [Table 1](#). The field strength limits are specified at a distance of 3 meters. The limits on the field strength of the spurious emissions in the [Table 1](#) are based on the fundamental frequency of the intentional radiator. Spurious emissions shall be attenuated to the average limits shown in this table or to the general limits shown in section 15.209, whichever limit permits higher field strength.

According to section 15.33, for an intentional radiator operating below 10 GHz, the frequency range of measurements must be up to the tenth harmonic of the highest fundamental or to 40 GHz, whichever is lower. The SPIRIT1 highest fundamental frequency is 315 MHz, so the tenth harmonic is 3.15 GHz. The measurements are performed up to 5 GHz.

In [Figure 4](#) and [5](#) the spurious conducted emissions and the FCC emission mask are shown. The carrier is unmodulated. The SPIRIT1 is fully compliant with the conducted spurious emission requirements.

Figure 4. TX spurious emission below 1 GHz





Figure 5. TX spurious emission above 1 GHz



4 Receiver parameter

No specific requirements are defined for FCC compliance of the receiver in US FCC Title 47 Part 15 [\[2\]](#) in the 315 MHz band. No measurements were done for the receiver.

5 Reference

1. SPIRIT1 datasheet
2. FCC title 47 Part 15: "Radio frequency devices"

6 Revision history

Table 5. Document revision history

Date	Revision	Changes
06-Aug-2012	1	Initial release.

Please Read Carefully:

Information in this document is provided solely in connection with ST products. STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, modifications or improvements, to this document, and the products and services described herein at any time, without notice.

All ST products are sold pursuant to ST's terms and conditions of sale.

Purchasers are solely responsible for the choice, selection and use of the ST products and services described herein, and ST assumes no liability whatsoever relating to the choice, selection or use of the ST products and services described herein.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted under this document. If any part of this document refers to any third party products or services it shall not be deemed a license grant by ST for the use of such third party products or services, or any intellectual property contained therein or considered as a warranty covering the use in any manner whatsoever of such third party products or services or any intellectual property contained therein.

UNLESS OTHERWISE SET FORTH IN ST'S TERMS AND CONDITIONS OF SALE ST DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY WITH RESPECT TO THE USE AND/OR SALE OF ST PRODUCTS INCLUDING WITHOUT LIMITATION IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION), OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.

UNLESS EXPRESSLY APPROVED IN WRITING BY TWO AUTHORIZED ST REPRESENTATIVES, ST PRODUCTS ARE NOT RECOMMENDED, AUTHORIZED OR WARRANTED FOR USE IN MILITARY, AIR CRAFT, SPACE, LIFE SAVING, OR LIFE SUSTAINING APPLICATIONS, NOR IN PRODUCTS OR SYSTEMS WHERE FAILURE OR MALFUNCTION MAY RESULT IN PERSONAL INJURY, DEATH, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE. ST PRODUCTS WHICH ARE NOT SPECIFIED AS "AUTOMOTIVE GRADE" MAY ONLY BE USED IN AUTOMOTIVE APPLICATIONS AT USER'S OWN RISK.

Resale of ST products with provisions different from the statements and/or technical features set forth in this document shall immediately void any warranty granted by ST for the ST product or service described herein and shall not create or extend in any manner whatsoever, any liability of ST.

ST and the ST logo are trademarks or registered trademarks of ST in various countries.

Information in this document supersedes and replaces all information previously supplied.

The ST logo is a registered trademark of STMicroelectronics. All other names are the property of their respective owners.

© 2012 STMicroelectronics - All rights reserved

STMicroelectronics group of companies

Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan - Malaysia - Malta - Morocco - Philippines - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States of America

www.st.com