



life.augmented

List of software parameters to check in case of switch:

From M24C64-FCU to M24C64X-FCU

P.PORTELLI



Application Engineer

MDG/MeMorY Division

Oct 30,2020

- This document provides a list of software parameters to check in case of switch from M24C64-FCU to M24C64X-FCU.

List of software parameters to check

Parameter	M24C64-FCU	M24C64X-FCU	Action needed	Remarks
Datasheet	 M24C64-FCU	 M24C64X rev 7	FYI	Available on ST.COM web site : - M24C64X-FCU - M24C64-FCU
Max Operating Frequency	Fast mode Plus	1MHz	Yes	If the application is running with operating frequency > 400KHz, on M24C64X the max authorized Tlow is 700ns.
Chip enable address	Fixed : 000	Default : 000	No - FYI	At factory delivery, fully compatible. 64X offers configurable chip enable address C2,C1,C0 (factory delivery value = 000). The chip enable address (C2,C1,C0) can be modified in the chip enable register. The register can be written & read with specifics command "write chip enable register" & "read chip enable register".
Chip enable register management	Not Available	Available	No - FYI	With the M24C64X, the user writes & reads the <i>chip enable register</i> with the specific commands "write chip enable register" & "read chip enable register". Can be updated: - The C2,C1,C0 bits for the chip enable address - The SWP bit for the protection of the memory array
Software Write Protect	Not Available	Available	No - FYI	On M24C64X, full protection of the memory array by software. The full protection of the memory can be activated with the SWP bit of the chip enable register. Once activated, the memory array is in read-only for ever. The register can be written & read with specifics command "write chip enable register" & "read chip enable register".

CONFIDENTIALITY OBLIGATIONS:

This document contains confidential information

It is classified ST Confidential and its distribution is submitted to ST Authorization

Disclosure of this document to any non authorized party must be previously authorized by ST only under the provision of a signed NDA between ST and Customer and must be treat as strictly confidential.

Information in this document is provided solely in connection with ST products. STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, modifications or improvements, to this document, and the products and services described herein at any time, without notice.

Information in this document is intended as support for authorized communication between ST and Customer only, for internal discussions purposes.

In no event the information disclosed by ST to Customer hereunder can be used against ST, or in a claim brought in front of any Court or Jurisdiction.

At all times you will comply with the following securities rules:

- Do not copy or reproduce all or part of this document
- Keep this document locked away
- Further copies can be provided on a "need to know basis", Please contact your local ST Sales Office or document writer

Information furnished is believed to be accurate and reliable. However, STMicroelectronics assumes no responsibility for the consequences of use of such information nor for any infringement of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of STMicroelectronics. Specifications mentioned in this publication are subject to change without notice. This publication supersedes and replaces all information previously supplied. STMicroelectronics products are not authorized for use as critical components in life support devices or systems without express written approval of STMicroelectronics.

The ST logo is a trademark of STMicroelectronics International NV and/or its affiliates, registered in the U.S. and other countries

© 2020 STMicroelectronics International NV and/or its affiliates - All Rights Reserved

www.st.com

Thank you

© STMicroelectronics - All rights reserved.

ST logo is a trademark or a registered trademark of STMicroelectronics International NV or its affiliates in the EU and/or other countries.

For additional information about ST trademarks, please refer to www.st.com/trademarks.

All other product or service names are the property of their respective owners.



life.augmented