
STM32WB Series MCUs with an external power amplifier

Introduction

The microcontrollers (MCUs) from the STM32WB Series can support an external power amplifier (PA) to provide higher output power.

This document details the modifications to implement in the Cortex[®]-M4 firmware, to allow the external PA to be driven by the MCU.

This application note is based on the SKY66118-11 PA from Skyworks Solutions (max output power = 20 dBm).

1 Hardware

This document applies to the STM32WB Series Arm® Cortex® core-based microcontrollers.


Note: Arm is a registered trademark of Arm Limited (or its subsidiaries) in the US and/or elsewhere.



The following SKY66118-11 pins must be managed (see the figure and the table below):

- CTX pin to switch the PA in transmission or reception
- CSD pin to enable or disable the PA
- VCTRL pin to control the output power ($1.6\text{ V} < V_{\text{CTRL}} < 3.6\text{ V}$, not represented in the figure below)

Figure 1. SKY66118-11 block diagram



Note: ANT = Antenna, HD = harmonics distortion, OMN = Output matching network, PA = power amplifier, SP2T = single pole 2 throw switch, T/R = transmit/receive

Refer to the SKY66118-11 datasheet available on Skyworks web site for more details.

Table 1. SKY66118-11 CSD and CTX pins

Mode	Description	CSD	CTX
0	All off (Sleep mode)	0	0 or 1
1	Transmit mode	1	1
2	Bypass mode	1	0

The CTX pin must be connected to GPIO PB0 (Port B, pin 0) of the STM32WB Series MCU. The CSD pin is connected to another GPIO.

2 Firmware

CTX pin

For the CTX pin, the code below must be added in the Cortex-M4 firmware, in the initialization section of the GPIOs:

```
GPIO_InitTypeDef  GPIO_InitStruct;

// Enable GPIOB clock for CTX pin
__HAL_RCC_GPIOB_CLK_ENABLE();

// configure the GPIO PB0 in AF6 to be used as RF_TX_MOD_EXT_PA
GPIO_InitStruct.Pull      = GPIO_NOPULL;
GPIO_InitStruct.Mode      = GPIO_MODE_AF_PP;
GPIO_InitStruct.Speed     = GPIO_SPEED_FREQ_HIGH;
GPIO_InitStruct.Alternate = GPIO_AF6_RF_DTB0;
GPIO_InitStruct.Pin       = GPIO_PIN_0;
HAL_GPIO_Init(GPIOB, &GPIO_InitStruct);
```

The CTX signal is managed by the BLE stack (transmission/reception), so there is nothing to add for this functionality.

Check that, in the Cortex-M4 firmware, PB0 is not used by another resource (for example, on the Nucleo board in the P-NUCLEO-WB55 pack, PB0 is used by LED2). If this occurs, this resource must be disabled.

CSD pin

The GPIO chosen to be connected to the CSD pin must be configured in the Cortex-M4 firmware, in the initialization section of the GPIOs (PA0 example):

```
// Enable GPIOA clock for CSD pin */
__HAL_RCC_C2GPIOA_CLK_ENABLE();
__HAL_RCC_GPIOA_CLK_ENABLE( );

// configure the GPIO which will be managed by M0 stack to enable Ext PA
GPIO_InitStruct.Pull = GPIO_NOPULL;
GPIO_InitStruct.Mode = GPIO_MODE_OUTPUT_PP;
GPIO_InitStruct.Speed = GPIO_SPEED_FREQ_HIGH;
GPIO_InitStruct.Pin  = GPIO_PIN_0;
HAL_GPIO_Init(GPIOA, &GPIO_InitStruct);
```

The Cortex-M4 firmware has also to inform the Cortex-M0+ firmware on which GPIO must be managed with the function:

- `SHCI_C2_ExtpaConfig((uint32_t)GPIOA, GPIO_PIN_0, EXT_PA_ENABLED_HIGH, EXT_PA_ENABLED);`
when the PA is used.
- `SHCI_C2_ExtpaConfig((uint32_t) GPIOA, GPIO_PIN_0, EXT_PA, EXT_PA_ENABLED_HIGH, EXT_PA_DISABLED);`
when the PA is not used.

Note: The selected PA must have a turn-on time lower than 300 μ s.

Revision history

Table 2. Document revision history

Date	Version	Changes
30-Sep-2019	1	Initial release.
16-Apr-2020	2	Updated: <ul style="list-style-type: none">• Section 1 Hardware• Section 2 Firmware• Classification of the document

Contents

1	Hardware	2
2	Firmware	3
	Revision history	4
	Contents	5

IMPORTANT NOTICE – PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries (“ST”) reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST’s terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers’ products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, please refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2020 STMicroelectronics – All rights reserved