

STEVAL-CCA042V1

TYPE	FootPrint	Description	QTY	Reference	Manufacturer
1 CCAP	CAP0603	330pF 50V NPO +/- 5%	2	C21,C27	Murata
2 CCAP	CAP0603	1nF 50V +/- 10%	4	C3,C4,C13,C14	Murata
3 CCAP	CAP0603	100nF 50V +/- 10%	11	C5,C6,C8,C9,C10,C18,C19,C22,C24, C25,C28	Murata
4 CCAP	CAP0603	470nF 50V +/- 10%	4	C1,C2,C11,C12	Murata
5 CCAP	CAP0603	2.2uF, 16V, +/-10%	3	C7, C15, C29	Murata
6 CCAP	CAP0603	1uF, 16V, +/-10%	2	C16, C17	Murata
7 ECAP	D <12.0mm	1000uF, 35V, +/-10% , PITCH=5.0mm	1	C23	Rubycon
8 CAP	MYLAY	220nF, PITCH =5mm	2	C20, C26	Murata
9 RES	R0603	22 ohm, +/-10%,1/16W	3	R5,R6,R7	Murata
10 RES	R0603	2.2k ohm, +/-10%, 1/16W	1	R8	Murata
11 RES	R0603	9.1k ohm, +/-10%, 1/16W	1	R13	Murata
12 RES	R0603	33k ohm, +/-10%, 1/16W	2	R2,R4	Murata
13 RES	R0603	39k ohm, +/-10%, 1/16W	1	R3	Murata
14 RES	R0603	100k ohm, +/-10%, 1/16W	1	R1	Murata
1 IC	TDA7491HV	TDA7491HV(SSO36) SLUG DOWN	1	IC1	ST
2 COIL	INDUCTOR	33uH, TYPE:7075P-330M	4	L1,L2,L3,L4	KWANGSUNG
3 CONNECTOR	RCA-2P	RCA SOCKET 2Px2, TYPE:AV2-8.4-12	1	J1	SONGCHENG
4 REGULATOR	TO92	L4931CZ33, 3V3 REGULATOR	1	IC2	ST
5 PCB	80 X 55mm	TDA7491P/LP/HV/TDA7492P- PCB	1		ST
6 Terminal	CNN-Termial	2P, PITCH =5mm Connector Terminal	3	J2,J3,J4	Any source
7 JUMPER	2-WAY JUMPER	2P, PITCH =2.5mm Jumper	4	J5,J6,,J8,J9	Any source
8 SWITCH	SLIDE	3P, PITCH =2.5mm	2	S1,S2	Any source