



Hello, and welcome to this presentation, that introduces the analog peripherals present in the STM32U5.

STM32U5 Analog Peripherals

Peripheral	Number of instances	Description
ADC	One 14-bit ADC (ADC1) One 12-bit ADC (ADC4)	Successive approximation analog-to-digital converters - ADC1: 14-, 12-, 10- or 8-bit configurable resolution - ADC4: 12-bit, 10-bit, 8-bit or 6-bit configurable resolution
DAC	One 12-bit DAC with two channels	8- or 12-bit mode
VREFBUF	One	Used as a voltage reference for the ADCs, DACs and also as a voltage reference for external components through the VREF+ pin Not available in the LQFP48, UFQFPN48, LQFP64 and WLCSP90 packages



2

STM32U5 products integrate one 14-bit ADC, one 12-bit ADC, two 12-bit DACs, VREF voltage buffer, two Comparators and two OPAMPs.

ADC1 has a 14-bit maximum resolution while ADC4 has a 12-bit maximum resolution.

The DAC module embeds two independent 12-bit converters.

The VREFBUF provides a voltage reference that can be used internally by the ADCs and DAC and also externally through the VREF+ pin.

The VREFBUF is not available in packages with a low pin count.

STM32U5 Analog Peripherals

Peripheral	Number of instances	Description
Comparators	Two	Each comparator has configurable plus and minus inputs used for flexible voltage selection: <ul style="list-style-type: none">– Multiplexed I/O pins– DAC channel1 and channel2– Internal reference voltage
Operational Amplifier (OPAMP)	Two	Two inputs and one output The three I/Os can be connected to the external pins, this enables any type of external interconnections The operational amplifier can be configured internally as a follower or as an amplifier with a non-inverting gain ranging from 2 to 16 The positive input can be connected to the internal DAC The output can be connected to the internal ADC



life.augmented

3

Comparators can be used for a variety of functions including:

- Wake-up from low-power mode triggered by an analog signal
- Analog signal conditioning
- Cycle-by-cycle current control loop when combined with a PWM output from a timer.

Comparators inputs can be internally connected to the DAC channels.

The operational amplifiers may reduce the need for an external stand-alone OPAMP. As these OPAMPs can be configured in stand-alone mode with all terminals available for the user, it is possible to use them as a voltage follower, non-inverting and inverting amplifiers, as well as

analog filters such as low- or high-pass filters. They can also act as a pre-amplifier for the ADC input.

Thank you

© STMicroelectronics - All rights reserved.

ST logo is a trademark or a registered trademark of STMicroelectronics International NV or its affiliates in the EU and/or other countries.

For additional information about ST trademarks, please refer to www.st.com/trademarks.

All other product or service names are the property of their respective owners.



Refer to the following presentations for a detailed description of analog peripherals:

- Comparators (COMP)
- Operational Amplifier (OPAMP)
- Voltage Reference Buffer (VREFBUF)
- Analog-to-Digital Converter and Digital-to-Analog Converter (ADC-DAC).