


Secure NFC dynamic tag for Matter commissioning and crypto operations



UDFPN8 (2 x 3 mm)

| Product status |
|----------------|
| ST25DA-C |

Features

Contact interface

- 1.62 V to 3.3 V supply voltage range
- ESD protection:
 - Human body model (HBM): 6 kV for digital and antenna pads
 - Charge device model (CDM): 1 kV based on a STMicroelectronics module
- Two-wire I²C serial interface supporting fast mode (up to 400 kHz)

Contactless interface

- Power supplied by 13.56 MHz carrier
- Complies with ISO/IEC 14443 Type A
- Complies with NFC Forum Type 4 Tag
- 78 pF tuning capacitor, with automatic antenna tuning for optimized performance
- Automatic CPU frequency adaptation for optimum power consumption
- 7-byte unique identifier (UID) on each die

Security features

- Secure MCU
- Active shield
- Monitoring of environmental parameters
- Protection mechanism against faults
- Protection against side-channel attacks
- Unique serial number on each die
- NIST 800-90B compliant true random-number generator (TRNG)
- Elliptic curve digital signature algorithm (ECDSA) with SHA-256 for digital signature generation and verification
- Elliptic curve Diffie-Hellman (ECDH) for key establishment
- Symmetric cryptography with AES-CCM for data confidentiality and integrity
- Symmetric cryptography with AES-CTR for data privacy
- Software fully upgradable (secure OS, cryptographic libraries and applets)

Matter services

- Stores Matter onboarding data in NFC Forum Type 4 tag
- Performs commissioning over NFC Transport Layer (NTL):
 - Powered either by VCC pin or 13.56 MHz contactless carrier
 - SPAKE2+
- Secure storage for certificates and keys needed for Matter commissioning
- Provides Matter signature generation and verification over I²C
- Supports Matter Over-The-Air (OTA) software update

Memory

- More than 3 KBytes of non-volatile memory is allocated for Matter certificates, keys, and attributes.

Operating temperature

- From -25°C to +85°C

Package

- 8 pins UFDFPN8 (2 x 3 mm)

All packages are ECOPACK2 compliant.

1 Description

The **ST25DA-C** device is an NFC dynamic tag integrated circuit providing the upcoming Matter commissioning flow over NFC, and cryptographic services.

The **ST25DA-C** offers a solution for commissioning a new device on a Matter network without requiring external power. On the NFC interface, it offers NFC Forum T4A Tag and Matter NFC Transport Layer applications. It implements secure storage, cryptographic primitives, and protocols to handle Matter Passcode-Authenticated Session Establishment (PASE) based on SPAKE2+ protocol, authentication of Matter device conformance with Matter device attestation, Node Operational Certificate (NOC), offline configuration of the operational network, and online signature service required for Certificate-Authenticated Session Establishment (CASE).


Based on a Common Criteria (CC) certified secure hardware, the device is designed to be the NFC component of a smart IoT device, acting as an NFC secure companion to the main microcontroller.

It exposes an NFC Forum Type 4 interface to communicate with a smartphone, and a high-speed (400 kHz) I²C interface to communicate with the main microcontroller.

1.1 Block diagram

The ST25DA-C device is depicted in the following logical block diagram:

Figure 1. Logical block diagram



DT7257V1

Revision history

Table 1. Document revision history

| Date | Revision | Changes |
|-------------|----------|---|
| 10-Dec-2024 | 1 | Initial release. |
| 03-Nov-2025 | 2 | Updated: <ul style="list-style-type: none">• Section Features• Section 1: Description• Section 1.1: Block diagram |
| 05-Nov-2025 | 3 | First public release. |
| 06-Jan-2026 | 4 | Updated Section Features . |

Contents

| | | |
|------------|-------------------------------|----------|
| 1 | Description | 3 |
| 1.1 | Block diagram | 4 |
| | Revision history | 5 |
| | List of tables | 7 |
| | List of figures | 8 |



List of tables

Table 1. Document revision history 5

List of figures

Figure 1. Logical block diagram 4

IMPORTANT NOTICE – READ CAREFULLY

STMicroelectronics NV and its subsidiaries (“ST”) reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice.

In the event of any conflict between the provisions of this document and the provisions of any contractual arrangement in force between the purchasers and ST, the provisions of such contractual arrangement shall prevail.

The purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgment.

The purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of the purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

If the purchasers identify an ST product that meets their functional and performance requirements but that is not designated for the purchasers' market segment, the purchasers shall contact ST for more information.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2026 STMicroelectronics – All rights reserved