

TS4962IQ class D audio amplifier Evaluation board user guidelines

Features

- TS4962IQ low voltage class D differential audio power amplifier with standby mode
- Operating range from $V_{cc}=2.4V$ to $5.5V$
- $2.2W$ output power @ $V_{cc}=5V$, THD=1%, $F=1kHz$, with 4Ω load
- $1.4W$ output power @ $V_{cc}=5V$, THD=1%, $F=1kHz$, with 8Ω load
- Ultra low power consumption in standby mode (10nA)
- 63dB PSRR @ 217Hz in grounded mode ($A_v=2V/V$)
- Low pop & click
- Fast startup time: 5ms
- Module gain set at $2V/V$

Description

This mono class D demoboard is designed for the TS4962IQ class D audio amplifier. The TS4962IQ device, in a DFN package, is mounted on a two-layer PCB with two power planes acting as a heatsink.

Figure 1. shows the schematic diagram of the demoboard.

Figure 1. Schematic diagram of the mono class D demoboard





Figure 2. shows the top view of the demoboard PCB, with the markings showing the connector placements.

Figure 2. Mono class D demoboard - top view



Caution: When you apply the power supply through Cn6, DO NOT invert the polarity because it would destroy the amplifier U1.

Table 1 lists the connectors on the demoboard, with a description for each, and their configurations.

Table 1. Description of demoboard connectors and their configurations

Connectors	Description
Cn1	Input signal connector (active input signal positive and negative)
Cn2 and Cn3	Connectors to modify input configuration (from capacitor-coupled = no jumper to common mode feedback = short-circuit).
Cn5	Output signal connector (Vo+ and Vo-)
Cn4	Standby control connector (GND, Standby, V _{CC})
Cn6	Power connector (V _{CC} and GND). Power supply voltage from 2.4V to 5.5V.
U1	Class D amplifier TS4962IQ

A list of the components mounted on the demoboard is given in [Table 2](#).

Table 2. Component list for the mono class D demoboard

Designation	Quantity	Description
C1	1	100nF/10V X7R/0603 capacitor
C2	1	100nF/10V X7R/0603 capacitor
C3	1	1 μ F/10V, X5R/0603 capacitor
Cn1	1	3 pins header 2.54mm pitch
Cn2	1	2 pins header 2.54mm pitch
Cn3	1	2 pins header 2.54mm pitch
Cn4	1	3 pins header 2.54mm pitch
Cn5	1	2 pins header 2.54mm pitch
Cn6	1	2 pins header 2.54mm pitch
R1	1	150k, 1/16W/0603 1% resistor
R2	1	150k, 1/16W/0603 1% resistor
U1	1	TS4962IQ

[Figure 3](#) and [Figure 4](#) show the demoboard PCB layers.

Figure 3. PCB bottom layer





Figure 4. PCB top layer



Configuring the demoboard characteristics

Differential gain

The demoboard is set up with the differential gain A_V set to 2V/V.

If necessary, the differential gain can be adapted by modifying the values of resistors R1 and R2, in accordance with the following relation:

$$A_V = \frac{300\text{k}\Omega}{R1} \text{ or } A_V = \frac{300\text{k}\Omega}{R2}$$

where R1=R2 in k Ω

Input configuration

On the demoboard, the Cn2 and Cn3 jumpers allow you to change the input configuration between **capacitor-coupled** and **common-mode feedback**.

In the **capacitor-coupled configuration**, the -3dB cut-off frequency in Hz is:

$$\frac{1}{2\pi \times R_1 \times C_1} = \frac{1}{2\pi \times R_2 \times C_2}$$

with R in Ohms, C in Farads and C1=C2.

More information about component calculations is available in the TS4962 datasheet.

Revision history

Date	Revision	Changes
28-Jul-2006	1	Initial release.
12-Apr-2007	2	Updated Table 2: Component list for the mono class D demoboard .

Please Read Carefully:

Information in this document is provided solely in connection with ST products. STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, modifications or improvements, to this document, and the products and services described herein at any time, without notice.

All ST products are sold pursuant to ST's terms and conditions of sale.

Purchasers are solely responsible for the choice, selection and use of the ST products and services described herein, and ST assumes no liability whatsoever relating to the choice, selection or use of the ST products and services described herein.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted under this document. If any part of this document refers to any third party products or services it shall not be deemed a license grant by ST for the use of such third party products or services, or any intellectual property contained therein or considered as a warranty covering the use in any manner whatsoever of such third party products or services or any intellectual property contained therein.

UNLESS OTHERWISE SET FORTH IN ST'S TERMS AND CONDITIONS OF SALE ST DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY WITH RESPECT TO THE USE AND/OR SALE OF ST PRODUCTS INCLUDING WITHOUT LIMITATION IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION), OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.

UNLESS EXPRESSLY APPROVED IN WRITING BY AN AUTHORIZED ST REPRESENTATIVE, ST PRODUCTS ARE NOT RECOMMENDED, AUTHORIZED OR WARRANTED FOR USE IN MILITARY, AIR CRAFT, SPACE, LIFE SAVING, OR LIFE SUSTAINING APPLICATIONS, NOR IN PRODUCTS OR SYSTEMS WHERE FAILURE OR MALFUNCTION MAY RESULT IN PERSONAL INJURY, DEATH, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE. ST PRODUCTS WHICH ARE NOT SPECIFIED AS "AUTOMOTIVE GRADE" MAY ONLY BE USED IN AUTOMOTIVE APPLICATIONS AT USER'S OWN RISK.

Resale of ST products with provisions different from the statements and/or technical features set forth in this document shall immediately void any warranty granted by ST for the ST product or service described herein and shall not create or extend in any manner whatsoever, any liability of ST.

ST and the ST logo are trademarks or registered trademarks of ST in various countries.

Information in this document supersedes and replaces all information previously supplied.

The ST logo is a registered trademark of STMicroelectronics. All other names are the property of their respective owners.

© 2007 STMicroelectronics - All rights reserved

STMicroelectronics group of companies

Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan - Malaysia - Malta - Morocco - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States of America

www.st.com

