



Bill of materials

Table 1. STDES-A2TBH45M65 main board

Item	Q.ty	Ref.	Part/value	Description	Manufacturer	Order code
1	4	C1, C2, C22, C27	160n	CAP CER 160nF 1.5kV 2220 X7R 10%		
2	6	C4, C8, C9, C10, C12, C15	NA	CAP CER 0603 50V (not assembled)		
3	4	C5, C6, C7, C13, C14	36uF	CAP FOIL RBOX 27uF 1.3kV PP 5%		
4	9	J1, J2, J3, J4, J5, J9, J13, J14, J15	Connector	CONN WP-THRB, M5, 8p, 10x10mm	Würth Elektronik	74655095R
5	2	J6, J7, J8, J10, J11, J12	Connector	CONN WP-THRB, M4, 4p, 7x7mm	Würth Elektronik	74650074R
6	1	P11	Header 2x1	WE Pin Header WR-MM	Würth Elektronik	690357280476
7	4	R1, R6, R8, R9, R10	NA	RES 0603 100mW 1% (not assembled)		
8	4	R2, R4, R5, R7, R18	10k	RES 0805 10k 250mW 1% (not assembled)		
9	2	R3	SC	General symbol for resistor		
10	2	R11, R12, R13, R14	18k	RES 2817 18k 4W 1%		
11	4	TP2, TP3, TP4, TP5, TP11, TP14	testpoint	TP THR 1mm	Keystone Electronics	5001
12	8	TP6, TP7	NA	2-pin, 2.54mm, SMD, header (not assembled)		
13	2	TP15	Testpoint	2-pin, 5.08mm header	SAMTEC	TSW-202-24-T-S
14	1	U1, U2, U4, U5, U6	Gate Driver Module	Single channel gate driver module based on STGAP3		
15	4	U3	A2TBH45M65W3-FC, Acepack 2	A2TBH45M65W3	ST	A2TBH45M65W3-FC

Table 2. STDES-A2TBH45M65 synchronous iso-buck

Item	Q.ty	Ref.	Part/value	Description	Manufacturer	Order code
1	2	C1, C6	CAP CER 0805 1uF 50V X7R 10%	Ceramic capacitor		
2	2	C2, C8	CAP CER 270p 0603 50V C0G 10%	Ceramic capacitor		
3	2	C3, C10	CAP CER 0805 2.2uF 50V X7R 10%	Ceramic capacitor		
4	2	C4, C9	CAP CER 10uF 35V 1206 X7R 10%	Ceramic capacitor		
5	1	C5	CAP CER 100nF 50V 1206 X7R 10%	Ceramic capacitor		
6	1	C7	CAP CER 680pF 50V 0603 C0G 10%	Ceramic capacitor		
7	1	C11	CAP CER 470nF 50V 0603 X7R 10%	Ceramic capacitor		
8	1	C12	CAP CER 68nF 50V 0603 X7R 10%	Ceramic capacitor		
9	1	C13	CAP CER 10pF 50V 0603 C0G 10%	Ceramic capacitor		
10	2	D1, D2	STPS1H100MF, Strmite	Schottky	ST	STPS1H100MF

Item	Q.ty	Ref.	Part/value	Description	Manufacturer	Order code
11	1	P1	CON SOCK 2.54mm 4pin 1row	Header Receptacle 4 pins 1 row		
12	1	P2	CON SOCK 2.54mm 3pin 1row	Header Receptacle 3 pins 1 row		
13	2	Q1, Q2	BC817-40	NPN Transistor		
14	1	R1	RES 910R 0805 125mW 1%	Resistor		
15	1	R2	RES 15k 0603 100mW 1%	Resistor		
16	1	R3	RES 2.4k 0805 125mW 1%	Resistor		
17	1	R4	RES 1.2k 0805 125mW 1%	Resistor		
18	1	R5	RES 120k 0603 100mW 1%	Resistor		
19	1	R6	RES 2k4 0603 100mW 1%	Resistor		
20	1	R7	RES 6.8k 0603 100mW 1%	Resistor		
21	1	R8	RES 56k 0603 100mW 1%	Resistor		
22	1	R9	RES 12k 0603 100mW 1%	Resistor		
23	1	TR1	WE-AGDT Gate Drive Transformer	Transformer	Würth Elektronik	750317894
24	2	U1, U2	TL431ACL3T, SOT23	Shunt voltage reference	ST	TL431ACL3T
25	1	U3	L6986ITR, HTSSOP16	38 V, 5 W synchronous iso-buck controller	ST	L6986ITR

Table 3. STDES-A2TBH45M65 gate driver

Item	Q.ty	Ref.	Part/value	Description	Manufacturer	Order code
1	2	C1, C8	330p	CAP CER 330p 50V 0603 C0G 10%		
2	4	C2, C5, C6, C7	100n	CAP CER 100nF 35V 0603 X7R 10%		
3	1	C3	330n	CAP CER 330nF 50V 0805 X7R 10%		
4	1	C4	100n	CAP CER 100nF 50V 0805 X7R 10%		
5	2	C9, C10	4u7	CAP CER 1uF 50V 0805 X7R 10%		
6	1	C15	SC	CAP CER 100nF 35V 0603 X7R 10%		
7	1	D1	NA	Zener Diode		
8	1	D2	Desat	LED 0603 RED 2mA		
9	1	D3	OK	LED 0603 GREEN 2mA		
10	1	D4	Ready	LED 0603 BLUE 2mA		
11	1	D5	STPS1L40ZF, SOD123	Schottky Diode	ST	STPS1L40ZF
12	2	FM1, FM2	Fiducial Mark	Fiducial Mark		
13	1	J1	Header 1pin	CONN HDR 1pin 1row (not assembled)		
14	1	J2	Header 2x2pin	CONN HDR 2.54mm 4pin 2row	Würth Elektronik	61300421121
15	1	P1	Control	Castelated connector 3pin		
16	1	P2	Power	Castelated connector 2pin		
17	1	P3	DC/DC Prim.	CON SOCK 2.54mm 4pin 1row	Würth Elektronik	61300411121
18	1	P4	Output	Castelated connector 3pin		
19	1	P5	DC/DC Sec.	CON SOCK 2.54mm 3pin 1row	Würth Elektronik	61300311121
20	2	Q1, Q2	BSS138	N-MOS SOT23_6		
21	1	Q3	STL8N6F7, PowerFlat 3.3x3x3	N-MOS PowerFlat 3.3x3.3	ST	STL8N6F7

Item	Q.ty	Ref.	Part/value	Description	Manufacturer	Order code
22	2	R1, R2	270R	RES 270R 0603 100mW 1%		
23	3	R3, R7, R8	NA	RES 0603 100mW 1%		
24	1	R4	0R	RES 0R 0805 125mW		
25	1	R5	4R7	RES 10R 1210 500mW 1%		
26	1	R6	1R3	RES 10R 1210 500mW 1%		
27	1	R9	3k3	RES 3k3 0603 100mW 1%		
28	1	R10	1k5	RES 1k5 0603 100mW 1%		
29	1	R11	6k8	RES 6k8 0603 100mW 1%		
30	1	R15	270R	RES 270R 0603 100mW 1%		
31	1	U1	STGAP3SXS, SO16-W	Galvanically isolated gate driver for SiC MOSFETs with 10 A Source/Sink current	ST	STGAP3SXS
32	1	U4	L78L33ABUTR, SOT-89	General purpose 3-pin LDO with exposed pad	ST	L78L33ABUTR

IMPORTANT NOTICE – READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgment.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2025 STMicroelectronics – All rights reserved