


3D dToF all-in-one lidar module



Product status link

[VL53L9CX](#)

Features

- Fast and accurate 3D direct Time-of-Flight (dToF) camera module
 - Multizone ranging output with up to 54 x 42 separate zones and binning options
 - On-chip processing streaming 2D IR image, depth and ambient maps
 - Confidence level and reflectance maps generated in postprocessing
 - Ranging from <5 cm up to 9 m
 - Up to 60 Hz frame rate capability
 - On-chip histogram processing and algorithmic compensation minimize or remove the impact of cover glass crosstalk and veiling glare
- Fully integrated miniature module with wide field of view (FoV)
 - Scan by two vertical-cavity surface-emitting lasers (VCSEL) flood illumination
 - 940 nm invisible light and integrated analog driver
 - 71° diagonal FoV using metasurface optical elements (MOE) on both transmitter and receiver
 - Receiving array of single photon avalanche diodes (SPADs)
 - Size: 12.8 x 6.1 x 4.6 mm
- Easy integration
 - True all-in-one module with integrated SPAD sensor and VCSEL PMIC
 - Single reflowable component
 - Flexible power supply options:
 - Supports dual power supply operation: 1.2 V & 3.3 V
 - Compatible with a wide range of cover glass materials

Applications

- Robotics
 - SLAM
 - Obstacle avoidance
 - Small object identification
- Augmented reality/virtual reality (AR/VR) enhancement.
 - Dual camera stereoscopy assistance thanks to 2D and depth multizone distance measurement at 60 fps
 - 3D room mapping (multizone and multiobject detection)
 - Gesture recognition and skeletal tracking
- Industrial applications
 - Content management thanks to wide FoV and multizone scanning (liquid level control, load in trucks, tanks, waste bins)
 - People mapping
- Smart homes
 - Smart buildings and smart lighting (user detection to wake up devices)
- IoT
 - User and object detection

- Mobile devices
 - Telephoto zoom camera assist. High resolution and long range allow image crop to align with telephoto camera.
 - Laser-assisted autofocus (LAF). Enhances the camera AF system speed and robustness, especially in difficult low-light or low-contrast scenes.
 - Video focus tracking. 60 Hz ranging allows optimization of continuous focus algorithm.
- Projectors
 - Keystone correction for video projectors

Description

The VL53L9CX is a state of the art, dToF 3D lidar (light detection and ranging) module with market leading resolution of up to 2.3k zones enhancing the ST FlightSense product family. Housed in a miniature reflowable package, it integrates all necessary components to make it a true all-in-one and easy to integrate module. The VL53L9CX includes a SPAD array, postprocessing SoC, two VCSELs powered by a dedicated BCD VCSEL driver providing a flood illumination, physical infrared filters, metasurface optical elements (MOE), and an embedded PMIC. The module is Class 1 laser safe, offering skin protection in addition.

The use of a MOE above the VCSELs allows to project an optimized rectangular FoV onto the scene. The receiver lens focuses the reflection of this light onto the SPAD array.

Unlike conventional IR sensors, the VL53L9CX uses ST's latest generation BSI stacked direct ToF technology, which allows absolute distance measurement whatever the target color and reflectance. It provides accurate ranging from below 5 cm up to 9 m. The VL53L9CX can stream processed data at maximum frame rate (60 Hz), which makes it the fastest, truly integrated 3D lidar camera module on the market. Available output data: depth, 2D IR with active illumination, 2D IR without active illumination, reflectance, and confidence.

The VL53L9CX achieves the best ranging performance, including under strong ambient light conditions, with a range of cover glass materials. Multizone distance measurements are possible up to 54 x 42 zones, with a wide 54°x42° FoV, which can be reduced by software.

1 Application schematic

Figure 1. Example application schematic




Table 1. Power supply details

Voltage rail	Range
VBAT	2.8 V to 4.8 V
AVDD	2.8 V or 3.3 V
DVDD	1.2 V
IOVDD	1.2 V or 1.8V

Revision history

Table 2. Document revision history

Date	Version	Changes
25-Feb-2025	1	Initial release
03-Oct-2025	2	Updated <i>Features</i> and <i>Description</i> to indicate that ranging is possible up to 9 m.

IMPORTANT NOTICE – READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice.

In the event of any conflict between the provisions of this document and the provisions of any contractual arrangement in force between the purchasers and ST, the provisions of such contractual arrangement shall prevail.

The purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgment.

The purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of the purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

If the purchasers identify an ST product that meets their functional and performance requirements but that is not designated for the purchasers' market segment, the purchasers shall contact ST for more information.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2025 STMicroelectronics – All rights reserved