



NPN power transistor



Features

- Surface-mounting DPAK (TO-252) power package in tape and reel
- Electrically similar to TIP47

Application

- Switch mode power supplies
- Audio amplifiers
- General purpose switching and amplifier

Description

The device is manufactured using medium voltage epitaxial planar technology, resulting in a rugged high-performance cost-effective transistor.



Product status link

[MJD47T4](#)

Product summary

Order code	MJD47T4
Marking	MJD47
Package	DPAK
Packing	Tape and reel

1 Electrical ratings

Table 1. Absolute maximum ratings

Symbol	Parameter	Value	Unit
V_{CBO}	Collector-base voltage ($I_E = 0$ V)	350	V
V_{CEO}	Collector-emitter voltage ($I_B = 0$ A)	250	V
V_{EBO}	Collector-base voltage ($I_C = 0$ A)	5	V
I_C	Collector current	1	A
I_{CM}	Collector peak current ($t_p < 5$ ms)	2	A
I_B	Base current	0.6	A
I_{BM}	Base peak current ($t_p < 5$ ms)	1.2	A
P_{TOT}	Total power dissipation at $T_C = 25$ °C	15	W
T_{stg}	Storage temperature range	-65 to 150	°C
T_J	Maximum operating junction temperature	150	°C

Table 2. Thermal data

Symbol	Parameter	Value	Unit
R_{thJC}	Thermal resistance, junction-to-case	8.33	°C/W
R_{thJA}	Thermal resistance, junction-to-ambient	100	°C/W

2 Electrical characteristics

$T_C = 25^\circ\text{C}$ unless otherwise specified.

Table 3. Electrical characteristics

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
I_{CES}	Collector cut-off current	$V_{CE} = 350\text{ V}, V_{BE} = 0\text{ V}$		-	0.1	mA
I_{CEO}	Collector cut-off current	$V_{CE} = 150\text{ V}, I_B = 0\text{ A}$		-	0.1	mA
I_{EBO}	Emitter cut-off current	$V_{EB} = 5\text{ V}, I_C = 0\text{ A}$		-	1	mA
$V_{CEO(sus)}^{(1)}$	Collector-emitter sustaining voltage	$I_C = 30\text{ mA}, I_B = 0\text{ A}$	250	-		V
$V_{CE(sat)}^{(1)}$	Collector-emitter saturation voltage	$I_C = 1\text{ A}, I_B = 0.2\text{ A}$		-	1	V
$V_{BE(on)}^{(1)}$	Base-emitter on-voltage	$I_C = 1\text{ A}, V_{CE} = 10\text{ V}$		-	1.5	V
$h_{FE}^{(1)}$	DC current gain	$I_C = 0.3\text{ A}, V_{CE} = 10\text{ V}$	30	-	150	
		$I_C = 1\text{ A}, V_{CE} = 10\text{ V}$	10	-		
f_T	Transition frequency	$I_C = 0.2\text{ A}, V_{CE} = 10\text{ V}, f = 2\text{ MHz}$	10	-		MHz
h_{fe}	Small signal current gain	$I_C = 0.2\text{ A}, V_{CE} = 10\text{ V}, f = 1\text{ kHz}$	25	-		

1. Pulsed: Pulse duration = 300 μs , duty cycle 1.5%.

2.1 Electrical characteristics (curves)













Figure 1. Safe operating area

Figure 2. Derating curves

Figure 3. DC current gain ($V_{CE} = 1\text{ V}$)

Figure 4. DC current gain ($V_{CE} = 5\text{ V}$)

Figure 5. Collector-emitter saturation voltage vs I_C

Figure 6. Collector-emitter saturation voltage vs I_B



Figure 7. Base-emitter saturation voltage

Figure 8. Collector-base capacitance

Figure 9. Storage time

Figure 10. Crossing time

Figure 11. Fall time

Figure 12. Resistive load switching times


3 Package information

In order to meet environmental requirements, ST offers these devices in different grades of **ECOPACK** packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: www.st.com. ECOPACK is an ST trademark.

3.1 DPAK (TO-252) type C package information


Figure 13. DPAK (TO-252) type C package outline



0068772_C_30

Table 4. DPAK (TO-252) type C mechanical data


Dim.	mm		
	Min.	Typ.	Max.
A	2.20	2.30	2.38
A1	0.90	1.01	1.10
A2	0.00		0.10
b	0.72		0.85
b4	5.13	5.33	5.46
c	0.47		0.60
c2	0.47		0.60
D	6.00	6.10	6.20
D1	5.25		
E	6.50	6.60	6.70
E1	4.70		
e	2.186	2.286	2.386
H	9.80	10.10	10.40
L	1.40	1.50	1.70
L1	2.90 REF		
L2	0.90		1.25
L3	0.51 BSC		
L4	0.60	0.80	1.00
L6	1.80 BSC		
θ1	5°	7°	9°
θ2	5°	7°	9°
V2	0°		8°

Figure 14. DPAK (TO-252) recommended footprint (dimensions are in mm)


FP_0068772_30


3.2 DPAK (TO-252) packing information

Figure 15. DPAK (TO-252) tape outline



AM08852v1

Figure 16. DPAK (TO-252) reel outline



AM06038v1

Table 5. DPAK (TO-252) tape and reel mechanical data

Dim.	Tape		Dim.	Reel	
	mm			mm	
	Min.	Max.		Min.	Max.
A0	6.8	7	A		330
B0	10.4	10.6	B	1.5	
B1		12.1	C	12.8	13.2
D	1.5	1.6	D	20.2	
D1	1.5		G	16.4	18.4
E	1.65	1.85	N	50	
F	7.4	7.6	T		22.4
K0	2.55	2.75			
P0	3.9	4.1		Base qty.	2500
P1	7.9	8.1		Bulk qty.	2500
P2	1.9	2.1			
R	40				
T	0.25	0.35			
W	15.7	16.3			

Revision history

Table 6. Document revision history

Date	Revision	Changes
17-Mar-2022	1	First release.

IMPORTANT NOTICE – READ CAREFULLY

STMicroelectronics NV and its subsidiaries (“ST”) reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST’s terms and conditions of sale in place at the time of order acknowledgment.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of purchasers’ products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2022 STMicroelectronics – All rights reserved