


## Smart power stage with current sensing and temperature monitor



### Features

- Thermally enhanced QFN 5x6 41L package
- Optimized MOSFET switching performance with integrated Schottky diode in LS MOSFET
- Up to 60 A continuous current
- High frequency operation up to 2 MHz
- Power MOSFETs optimized for 12 V input stage and 10% to 15% duty cycle operation
- 3.3 V PWM logic with tri-state and hold-off
- PWM minimum controllable on-time of 30 ns
- Diode emulation mode at light loads for high efficiency over the full load range using GLCTRL pin
- Low PWM propagation delay (< 20 ns)
- Current sense monitor ( $I_{MON}$ )
- Temperature monitor ( $T_{MON}$ )
- Overtemperature alert
- HS MOSFET overcurrent and short alert
- Undervoltage lockout for  $V_{DRV}$
- Material categorization: for definitions of compliance

### Application

- Synchronous buck converters
- Multi-phase VRDs for CPU, GPU, and memory
- DC/DC VR modules

### Description

The PM7060 is an integrated power stage solution optimized for synchronous buck applications to offer high current, high efficiency, and high power density performance. Packaged in 5x6 mm QFN package, the PM7060 enables voltage regulator design to deliver in excess of 60 A per phase current. The internal power MOSFETs utilize state-of-the-art technology that delivers industry benchmark performance to significantly reduce switching and conduction losses.

The PM7060 incorporates an advanced MOSFET gate driver IC that features high current driving capability, adaptive dead-time control, and integrated bootstrap switch, a thermal monitor that alerts the system of excessive junction temperature. This driver is compatible with 3.3 V logic PWM with tri-state to manage High Impedance Output. Diode emulation mode can be enabled at light loads through the use of GLCTRL signal.

The device also integrates a current monitor to provide a real-time scale down of inductor current ( $I_{MON}$ ). A temperature monitor provides the system with an indication of the power stage internal temperature ( $T_{MON}$ ) and can be used to throttle the system operation down to a safer level if needed.

The device also integrates fault alerts such as HS FET overcurrent, overtemperature and HS MOSFET short failures.

Product status link	
PM7060	
Product summary	
Order code	PM7060
Temperature range	-40 to +125
Package	QFN 5x6 41L
Packing	Tape & reel

## Revision history

**Table 1. Document revision history**

Date	Version	Changes
26-Jul-2021	1	Initial release.

**IMPORTANT NOTICE – PLEASE READ CAREFULLY**

STMicroelectronics NV and its subsidiaries (“ST”) reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST’s terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers’ products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, please refer to [www.st.com/trademarks](http://www.st.com/trademarks). All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2019 STMicroelectronics – All rights reserved