


## 60 GHz V-band contactless connectivity transceiver with eUSB2, UART, GPIO, or I<sup>2</sup>C tunneling



VFBGA30  
(2.2 mm x 2.6 mm x 0.8 mm)

### Product status link

[ST60A3H0](#)

### Features

- 60 GHz V-Band transceiver for short range contactless connectivity up to 480 Mbit/s
- Compact solution integrating full RF transceiver operating in Half-Duplex mode
- RF operational bandwidth: From 60 GHz to 61 GHz
- 34 dB typical total link budget
- eUSB2, UART, GPIO, or I<sup>2</sup>C RF tunneling
- Single 1.8 V supply or dual supply 1.8 V (analog/RF) and 1.2 V (digital/GPIO)
- Low power consumption (typical values with single 1.8 V supply):
  - eUSB2 Rx/Tx - 110/130 mW
  - UART/GPIO/I<sup>2</sup>C - 90 mW
  - Standby - 23  $\mu$ W
- 50  $\Omega$  single-ended nominal RF input/output impedance with recommended PCB transition
- Optimized BOM without external matching network and clock references. A reference clock may be used at one end of the RF link to comply with specific regional regulation
- Package: VFBGA 2.2 mm x 2.6 mm x 0.8 mm, 30 balls, 5x6 array, 0.4 mm pitch

### Description

The ST60A3H0 is an RF millimeter-wave transceiver product operating in the 60 GHz V-band from 60 GHz to 61 GHz. The ST60A3H0 has a miniature form factor, optimized bill of materials, and low-power operation. The ST60A3H0 is a high-speed RF transceiver compliant with eUSB2, UART, and I<sup>2</sup>C protocols. The transceiver module contains general-purpose input/outputs (GPIOs) that are also available in tunneling mode. The device is compatible with various antenna configurations, either patch antennas designed on-PCB, or highly directive SMT horn antennas allowing both end-fire and broadside radiation patterns. The ST60A3H0 meets the requirements of applications by virtue of its compactness, low-power operation, ease of use, and its innovative architecture design for optimized system bill of materials.

### Applications

- Contactless test factory automation and after sales services
- Firmware Over-the-Air (FOTA) update
- Contactless data harvesting
- Life proof hole-less personal devices
- Contactless accessories
- Contactless personal equipment docking hub and data transfer
- Industrial contactless connectors
- Board-to-board connection and flex cable replacement

## Revision history

**Table 1. Document revision history**

Date	Revision	Changes
11-Dec-2023	1	Initial release.
08-Oct-2024	2	Added: <ul style="list-style-type: none"><li>RF operational bandwidth in <a href="#">Section Features</a></li><li>New application use cases in <a href="#">Section Applications</a></li></ul>

**IMPORTANT NOTICE – READ CAREFULLY**

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgment.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, refer to [www.st.com/trademarks](http://www.st.com/trademarks). All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2024 STMicroelectronics – All rights reserved