




Automotive-grade trench gate field-stop IGBT 650 V, 200 A in a STPAK package



STPAK



Features

- AEC-Q101 qualified 
- $V_{CE(sat)} = 1.52 \text{ V (typ.) @ } I_C = 200 \text{ A}$
- Positive $V_{CE(sat)}$ temperature coefficient
- Tight parameter distribution
- Low thermal resistance
- Very fast and soft recovery antiparallel diode

Applications

- Main inverter (electric traction)

Description

This device is an IGBT developed using an advanced proprietary trench gate field-stop structure. This device represents an optimum compromise in performance to maximize the efficiency of inverter systems where low-loss are essential. Furthermore, a positive $V_{CE(sat)}$ temperature coefficient and tight parameter distribution result in safer paralleling operation.



Product status link

[STGST200G65DFAG](#)

[STGST200G65DTAG](#)

Product summary

Order code	STGST200G65DFAG
Marking	G200G65DFAG
Package	STPAK longer pins
Packing	Tray
Order code	STGST200G65DTAG
Marking	G200G65DTAG
Package	STPAK longer pins
Packing	Tube

1 Electrical ratings

Table 1. Absolute maximum ratings

Symbol	Parameter	Value	Unit
V_{CES}	Collector-emitter voltage ($V_{GE} = 0$ V)	650	V
$I_C^{(1)}$	Continuous collector current at $T_C = 25$ °C	365	A
	Continuous collector current at $T_C = 100$ °C	228	
$I_{CP}^{(1)}$	Pulsed collector current ($t_p \leq 1$ μ s)	800	A
V_{GE}	Gate-emitter voltage	± 20	V
$I_F^{(1)}$	Continuous forward current at $T_C = 25$ °C	238	A
	Continuous forward current at $T_C = 100$ °C	145	
P_{TOT}	Total power dissipation at $T_C = 25$ °C	1000	W
T_{stg}	Storage temperature range	-55 to 150	°C
T_J	Operating junction temperature range	-55 to 175	°C

1. Limited by maximum junction temperature.

Table 2. Thermal data

Symbol	Parameter	Value	Unit
R_{thJC}	Thermal resistance, junction-to-case, IGBT	0.15	°C/W
	Thermal resistance, junction-to-case, diode	0.29	

2 Electrical characteristics

$T_C = 25\text{ °C}$ unless otherwise specified.

Table 3. Static

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
$V_{(BR)CES}$	Collector-emitter breakdown voltage	$V_{GE} = 0\text{ V}, I_C = 1\text{ mA}$	650			V
$V_{CE(sat)}$	Collector-emitter saturation voltage	$V_{GE} = 15\text{ V}, I_C = 200\text{ A}$		1.52	1.80	V
		$V_{GE} = 15\text{ V}, I_C = 200\text{ A}, T_J = 175\text{ °C}$		1.75		
V_F	Forward on-voltage	$I_F = 150\text{ A}$		1.85	2.32	V
		$I_F = 150\text{ A}, T_J = 175\text{ °C}$		1.47		
		$I_F = 200\text{ A}$		2.00	2.57	
		$I_F = 200\text{ A}, T_J = 175\text{ °C}$		1.65		
$V_{GE(th)}$	Gate threshold voltage	$V_{CE} = V_{GE}, I_C = 2\text{ mA}$	4.75	5.50	6.25	V
I_{CES}	Collector cut-off current	$V_{GE} = 0\text{ V}, V_{CE} = 650\text{ V},$			10	μA
I_{GES}	Gate-emitter leakage current	$V_{CE} = 0\text{ V}, V_{GE} = 20\text{ V}$			50	nA
		$V_{CE} = 0\text{ V}, V_{GE} = -20\text{ V}$	-50			

Table 4. Dynamic

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
C_{ies}	Input capacitance	$V_{CE} = 25\text{ V}, f = 1\text{ MHz}, V_{GE} = 0\text{ V}$	-	14.3	-	nF
C_{oes}	Output capacitance		-	0.7	-	nF
C_{res}	Reverse transfer capacitance		-	0.4	-	nF
Q_g	Total gate charge	$V_{CC} = 400\text{ V}, I_C = 200\text{ A}, V_{GE} = 18\text{ V}$ (see Figure 28. Gate charge test circuit)	-	900	-	nC

Table 5. IGBT switching characteristics (inductive load)

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
$t_{d(on)}$	Turn-on delay time	$V_{CC} = 400\text{ V}$, $V_{GE} = -5\text{ to }+18\text{ V}$, $R_G = 4.7\ \Omega$, $I_C = 200\text{ A}$ (see Figure 27. Test circuit for inductive load switching)	-	68.5	-	ns
t_r	Current rise time		-	41	-	ns
$E_{on}^{(1)}$	Turn-on switching energy		-	1.41	-	mJ
$t_{d(off)}$	Turn-off delay time		-	362	-	ns
t_f	Current fall time		-	48	-	ns
$E_{off}^{(2)}$	Turn-off switching energy		-	4.77	-	mJ
$t_{d(on)}$	Turn-on delay time	$V_{CC} = 400\text{ V}$, $V_{GE} = -5\text{ to }+18\text{ V}$, $R_G = 4.7\ \Omega$, $I_C = 200\text{ A}$, $T_J = 175\text{ }^\circ\text{C}$ (see Figure 27. Test circuit for inductive load switching)	-	68	-	ns
t_r	Current rise time		-	44	-	ns
$E_{on}^{(1)}$	Turn-on switching energy		-	2.53	-	mJ
$t_{d(off)}$	Turn-off delay time		-	400	-	ns
t_f	Current fall time		-	96	-	ns
$E_{off}^{(2)}$	Turn-off switching energy		-	7.46	-	mJ

1. Including the reverse recovery of the diode.

2. Including the tail of the collector current.

Table 6. Diode switching characteristics (inductive load)

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
I_{rm}	Reverse recovery current	$V_{CC} = 400\text{ V}$, $V_{GE} = -5\text{ to }+18\text{ V}$, $R_G = 4.7\ \Omega$, $di/dt = 4318\text{ A}/\mu\text{s}$, $I_C = 200\text{ A}$ (see Figure 27. Test circuit for inductive load switching)	-	101	-	A
t_{rr}	Reverse recovery time		-	164	-	ns
Q_{rr}	Reverse recovery charge		-	6.3	-	μC
E_{rr}	Reverse recovery energy		-	2	-	mJ
I_{rm}	Reverse recovery current	$V_{CC} = 400\text{ V}$, $V_{GE} = -5\text{ to }+18\text{ V}$, $R_G = 4.7\ \Omega$, $di/dt = 4513\text{ A}/\mu\text{s}$, $I_C = 200\text{ A}$, $T_J = 175\text{ }^\circ\text{C}$ (see Figure 27. Test circuit for inductive load switching)	-	198	-	A
t_{rr}	Reverse recovery time		-	300	-	ns
Q_{rr}	Reverse recovery charge		-	22	-	μC
E_{rr}	Reverse recovery energy		-	7.1	-	mJ







2.1 Electrical characteristics (curves)
Figure 1. Power dissipation vs case temperature

Figure 2. Collector current vs case temperature

Figure 3. Output characteristics (T_J = 25 °C)

Figure 4. Output characteristics (T_J = 175 °C)

Figure 5. Output characteristics (T_J = -55 °C)

Figure 6. V_{CE(sat)} vs junction temperature








Figure 7. $V_{CE(sat)}$ vs collector current

Figure 8. Forward bias safe operating area

Figure 9. Transfer characteristics

Figure 10. Diode V_F vs forward current

Figure 11. Normalized $V_{GE(th)}$ vs junction temperature

Figure 12. Normalized $V_{(BR)CES}$ vs junction temperature








Figure 13. Capacitance variations

Figure 14. Gate charge vs gate-emitter voltage

Figure 15. Switching energy vs collector current

Figure 16. Switching energy vs temperature

Figure 17. Switching energy vs collector emitter voltage

Figure 18. Switching energy vs gate resistance














Figure 19. Switching times vs collector current

Figure 20. Switching times vs gate resistance

Figure 21. Reverse recovery current vs diode current slope

Figure 22. Reverse recovery time vs diode current slope

Figure 23. Reverse recovery charge vs diode current slope

Figure 24. Reverse recovery energy vs diode current slope


Figure 25. Normalized thermal impedance for IGBT

Figure 26. Normalized thermal impedance for diode


3 Test circuits


Figure 27. Test circuit for inductive load switching

Figure 28. Gate charge test circuit

Figure 29. Switching waveform

Figure 30. Diode reverse recovery waveform


4 Package information

To meet environmental requirements, ST offers these devices in different grades of **ECOPACK** packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions, and product status are available at: www.st.com. ECOPACK is an ST trademark.

4.1 STPAK package information

Figure 31. STPAK package outline



DM00305987_10

Table 7. STPAK package mechanical data

Ref.	Dimensions			Notes
	mm			
	Min.	Typ.	Max.	
A	18.60	18.80	19.00	
A1	12.85	13.05	13.25	
A2	2.00	2.30	2.60	
A3	13.40	13.90	14.40	Exposed Pad
A4	1.95	2.45	2.95	
A5	3.80	4.00	4.20	
A6	2.10	2.30	2.50	
B	43.40	43.70	44.00	
B3	32.20	32.50	32.80	
B4	39.10	39.40	39.70	
B5	36.07	36.37	36.67	
B6	39.07	39.37	39.67	
c	0.34	0.39	0.44	
C		18.55	19.10	Encompass both large and small cav.
C2	12.90	13.10	13.30	
C3		14.35		
C4		17.65		
D	27.90	28.10	28.30	
D1		0.69		
D2	18.00 (18.50)	18.50 (19.00)	19.00 (19.50)	Refer to the values in brackets for the longer pins type
D3	8.60 (9.10)	9.10 (9.60)	9.60 (10.10)	Refer to the values in brackets for the longer pins type
E1	17.20	17.70	18.20	Exposed pad
E3	9.15	9.65	10.15	
h1	0.85	0.90	0.95	x2 - Pins width
h2	4.00	4.10	4.20	
l	0.60	0.70	0.80	
eee	0.50			
fff	0.10 at 23 °C – 0.05 at 220 °C			Convex with center higher than edges
ggg	0.05			
hhh	0.10			
iii	0.60			

Revision history

Table 8. Document revision history

Date	Revision	Changes
10-Dec-2021	1	Initial release.
13-Nov-2023	2	Updated <i>Applications</i> on cover page. Updated <i>Figure 13. Capacitance variations</i> . Updated <i>Section 4.1 STPAK package information</i> . Minor text changes.
16-Dec-2024	3	Updated <i>Section 1: Electrical ratings</i> . Updated <i>Figure 1. Power dissipation vs case temperature</i> , <i>Figure 2. Collector current vs case temperature</i> , <i>Figure 8. Forward bias safe operating area</i> , <i>Figure 25. Normalized thermal impedance for IGBT</i> and <i>Figure 26. Normalized thermal impedance for diode</i> . Added STGST200G65DTAG order code in STPAK longer pins package. The document has been updated accordingly.
20-Feb-2025	4	Updated Section Product status link / summary .



Contents

1	Electrical ratings	2
2	Electrical characteristics	3
2.1	Electrical characteristics (curves)	5
3	Test circuits	10
4	Package information	11
4.1	STPAK package information	11
	Revision history	13



IMPORTANT NOTICE – READ CAREFULLY

STMicroelectronics NV and its subsidiaries (“ST”) reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST’s terms and conditions of sale in place at the time of order acknowledgment.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of purchasers’ products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2025 STMicroelectronics – All rights reserved