

15W Wireless Power Receiver



Features

- Up to 15 W output power
- High efficiency synchronous rectifier
- Low drop-out linear regulator
- 4 V to 12 V programmable output voltage
- 32-bit, 64 MHz Arm® Cortex® M0+ core
- Configurable GPIOs
- I²C target interface for host controller
- Multilevel ASK modulator, FSK demodulator
- Overcurrent and thermal protections
- Overvoltage clamping protection
- Accurate current sense system for Foreign Object Detection (FOD)
- Package: WLCSP40 5 x 8 Ball (2.12 mm x 3.32 mm x 0.56 mm) pitch 0.4 mm

Product status link

STWLC38JRM

Product summary

Order code	STWLC38JRM
Package	WLCSP40
Packing	Tape and reel

Application

- Smartwatches, fitness trackers, True Wireless Stereo (TWS)
- Medical and healthcare equipment
- Crypto wallets

Description

The STWLC38JRM is a highly integrated wireless power receiver solution suitable for applications up to 15 W.

The STWLC38JRM shows excellent efficiency performance thanks to the integrated low-loss synchronous rectifier and the low drop-out linear regulator: both elements are dynamically managed by the digital core to minimize the overall power dissipation over a wide range of output load conditions.

STWLC38JRM features embedded RRAM (Resistive RAM) nonvolatile memory to enable I²C interface customization and support of proprietary communication and charging protocols.

Additional firmware patching also improves the application flexibility of STWLC38JRM.

The STWLC38JRM is housed in a chip scale package to fit real-estate sensitive applications like wearable devices.

Revision history

Table 1. Document revision history

Date	Version	Changes
11-June-2025	1	Initial release

IMPORTANT NOTICE – READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgment.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2025 STMicroelectronics – All rights reserved