


## Qi-compliant inductive wireless power receiver for 70W applications



### Features

- Up to 70W output power
- Up to 15W output power in Tx mode
- Qi 1.2.4 and 1.3 compliant
- Integrated 27 V synchronous rectifier with  $\geq 98\%$  efficiency
- ARC(Adaptive Rectifier Configuration) mode for spatial freedom
- Low drop-out linear regulator with output current and input voltage loops
- Programmable output voltage up to 20V in steps of 25mV
- 32bit,64Mhz ARM Cortex M3 core with 16KB FTP,16KB RAM,80KB ROM
- 10-bit A/D converter
- 6 configurable GPIO's
- I2C Slave , Master interface
- High speed SPI interface for external flash for design in
- 8-levels ASK modulator, Enhanced FSK demodulator
- Accurate current sense system for Foreign Object Detection(FOD)
- Coil Q-factor measurement for FOD in Tx mode
- Over voltage, Over current and thermal protection
- Flip chip 90 bumps (4.3 mm x 3.9 mm)

### Application

#### Application

- Smartphones, Tablets, Laptop
- Power banks, cordless power tools
- Medical devices

### Description

The STWLC98 is a highly integrated wireless power receiver suitable for applications delivering an output power up to 70W. The chip has been designed to support Qi specifications 1.2.4 and 1.3 for inductive communication protocol with Extended Power Profile (EPP) and proprietary ST Super Charge (STSC) protocol for fast charging.

With integrated low-loss synchronous rectifier and low drop-out linear regulator, STWLC98 achieves high efficiency with low power dissipation.


Through I2C interface the user can access and modify the configuration parameters for customized applications, the final configuration parameters are stored in embedded Few Times Programmable (FTP) non-volatile memory and automatically retrieved at power-up.

The device can also operate as wireless transmitter up to 15W (coil dependent)

Chip-Scale Package and low BOM count makes it very suitable for compact applications.

Product status link	
<a href="#">STWLC98</a>	
Product summary	
<b>Order code</b>	STWLC98JR
<b>Package</b>	Flip chip(4.3x3.9mm)
<b>Packing</b>	Tape and reel

# 1 Typical Application Diagram



## Revision history

**Table 1. Document revision history**

Date	Version	Changes
27-Aug-2021	1	Initial release.

**IMPORTANT NOTICE – PLEASE READ CAREFULLY**

STMicroelectronics NV and its subsidiaries (“ST”) reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST’s terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers’ products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, please refer to [www.st.com/trademarks](http://www.st.com/trademarks). All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2021 STMicroelectronics – All rights reserved