


Aerospace 100 V, 0.3 A switching rectifier in LCC-2D package



Features

- Surface mount hermetic LCC-2D package
 - Low thermal case resistance: 60 °C/W
 - Low package mass, 120 mg
- Low leakage off state, $I_R = 50 \text{ nA}$ at 75 V
- Low forward voltage: $V_F = 0.8 \text{ V}$ at 10 mA and $T_j = 25 \text{ °C}$
- Ultrafast switching, $t_{rr} = 9 \text{ ns}$ at $I_F = I_R = 10 \text{ mA}$ and $T_j = 25 \text{ °C}$
- Radiation performance
 - 3 Mrad (Si) high dose rate
- ESCC qualified: detail specification 5101/026

Applications

- Satellite and spacecraft power systems
- Low power switch mode power supply
- Snubber diode for low power converter
- Auxiliary transistor driver diode
- Reverse polarity protection
- Redundancy OR-ing diode

Description

Designed for harsh cosmic radiation conditions, the 1N6642U is a 100 V low-leakage ultrafast rectifier that is housed in the lightweight, high thermal conductive LCC-2D package.

This hermetic surface mount package exhibits an industry standard compatible footprint, such as the D5A.

This full planar technology 1N6642U rectifier allows superior performances and high reliability up to 175°C and is characterized in total ionizing dose for Rad-Hard applications.

This rectifier is ESCC qualified, which makes it eligible for use in space programs. It is typically used in low voltage switch-mode power converters, high frequency DC-to-DC, step-down regulators, or chopper drives, performing as free-wheeling diode, transistor driver diode, reverse polarity protection, or redundancy OR-ing diode.

Product status link

[1N6642U](#)

Product summary


$I_{F(AV)}$	0.3 A
V_{RRM}	100 V
$V_F(\text{max.})$	0.8 V at 10 mA and 25 °C
$T_J(\text{max.})$	175 °C

1 Characteristics

Table 1. Absolute ratings (limiting values)

Symbol	Parameter	Value	Unit
V_{RRM}	Repetitive peak reverse voltage	100	V
$V_{RWM}^{(1)}$	Peak working reverse voltage	75	V
$I_{F(RMS)}$	RMS forward current	500	mA
$I_{F(AV)}$	Average forward current ⁽²⁾	300	mA
I_{FSM}	Non repetitive surge forward current	$t_p = 8.3$ ms sinusoidal 2	A
T_{stg}	Storage temperature range	-65 to +175	°C
T_{op}	Operating temperature range (case temperature)	-65 to +175	°C
T_j	Maximum operating junction temperature	175	°C
T_{sol}	Maximum soldering temperature ⁽³⁾	245	°C
ESD	Electro static discharge, air discharge, HBM model, class 3B	5.8	kV

1. See Figure 1.
2. $T_{case} = +155$ °C derate linearly to 0 A at $T_j = 175$ °C.
3. Maximum duration 5 s. The same package cannot be re-soldered until 3 minutes have elapsed after initial soldering.

Figure 1. V_{RRM} and V_{RWM} definition with their waveform

Table 2. Thermal parameters

Symbol	Parameter	Max. value	Unit
$R_{th(j-c)}$	Junction to case (DC) , mounted on infinite heat sink	60	°C/W
$R_{th(j-a)}$	Junction to ambient (DC)	280	°C/W

For more information, refer to the application note:

- [AN5088](#): Rectifiers thermal management, handling and mounting recommendation

Table 3. Static electrical characteristics

Symbol	Parameter	Test conditions		Min.	Max.	Unit
$V_{BR}^{(1)}$	Breakdown voltage	$I_R = 100 \mu A$	$T_j = 25^\circ C$	100		V
$I_{RR}^{(1)}$	Reverse leakage current	$V_R = 100 V$	$T_j = 25^\circ C$		60	nA
			$T_j = -55^\circ C$		50	μA
		$V_R = 75 V$	$T_j = 25^\circ C$		50	nA
			$T_j = 150^\circ C$		40	μA
		$V_R = 20 V$	$T_j = 25^\circ C$		25	nA
			$T_j = 150^\circ C$		30	μA
$V_F^{(2)}$	Forward voltage drop	$I_F = 100 mA$	$T_j = -55^\circ C$		1.2	V
		$I_F = 10 mA$	$T_j = 25^\circ C$		0.8	
		$I_F = 100 mA$	$T_j = 25^\circ C$		1.2	
		$I_F = 10 mA$	$T_j = 150^\circ C$		0.8	

1. Pulse test: $t_p = 5 ms$, $\delta < 2\%$, $\delta =$ duty cycle

2. Pulse test: $t_p = 680 \mu s$, $\delta < 2\%$

To evaluate the conduction losses, use the following equation:

$$P = 0.74 \times I_{F(AV)} + 1.00 \times I_F^2 (RMS)$$

For more information, refer to the following application notes related to the power losses:

- [AN604](#): Calculation of conduction losses in a power rectifier
- [AN4021](#): Calculation of reverse losses on a power diode

Table 4. Dynamic characteristics

Symbol	Parameter	Test conditions	Test conditions	Max.	Unit
t_{RR}	Reverse recovery time	$I_F = I_R = 10 mA^{(1)}$	$T_j = 25^\circ C$	9	ns
		$I_F = 1 A$, $dI_F/dt = -15 A/\mu s$, $V_R = 30 V$		20	
C_j	Total diode capacitance	$V_{AC} = 50 mV$, $V_R = 0 V$, $F = 1 MHz$	$T_j = 25^\circ C$	5	pF
		$V_{AC} = 50 mV$, $V_R = 1.5 V$, $F = 1 MHz$		2.8	
V_{FP}	Forward recovery voltage	$I_F = 200 mA$	$T_j = 25^\circ C$	5	V
t_{FR}	Forward recovery time	$I_F = 200 mA$, $V_{FR} = 1.1 \times V_F(0.2A)$	$T_j = 25^\circ C$	20	ns

1. Guaranteed by design.

1.1 Characteristics (curves)

Figure 2. Forward voltage drop versus forward current (typical values)




Figure 3. Forward voltage drop versus forward current (maximum values)




Figure 4. Reverse leakage current versus reappplied reverse voltage (typical values)




Figure 5. Relative variation of thermal impedance junction to case versus pulse duration





Figure 6. Junction capacitance versus reappplied reverse voltage (typical values)




2 Package information

To meet environmental requirements, ST offers these devices in different grades of **ECOPACK** packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions, and product status are available at: www.st.com. ECOPACK is an ST trademark.

2.1 LCC-2D package information

Figure 7. LCC-2D package outline




8164237_5

Note: The anode is identified by a metallization in two top angle castellations and by the index mark on the bottom metallization n° 1.

Table 5. LCC-2D package mechanical data

Ref.	Dimensions					
	Millimeters			Inches (for reference only)		
	Min.	Typ.	Max.	Min.	Typ.	Max.
A	1.86	2.03	2.20	0.073	0.080	0.087
B	4.44	4.57	4.77	0.175	0.180	0.188
C	1.84	1.97	2.10	0.072	0.078	0.083
D	1.53	1.70	1.87	0.060	0.067	0.074
E	0.48		0.71	0.019		0.028
F		1.3			0.051	
G		1.67			0.066	
H		0.37			0.015	
I		0.15			0.006	
r1		0.15			0.006	
r2		0.20			0.008	

Dimension data specified for the gold plated version and the solder dip version before tinning.

Figure 8. LCC2-D footprint density level B


8164237_5

3 Ordering information

Table 6. Ordering information

Order code	ESCC detail specification	Quality level	Package	Lead finishing	Product marking	Mass	Bulk qty.	Packing
1N6642UD1	-	Engineering model	LCC-2D	Gold	1N6642UD1	120 mg	50	Waffle pack
1N6642U01D	5101/026/07	Flight model		Gold	510102607			
1N6642U02D	5101/026/08	Flight model		Hot solder dip	510102608			

Note: Contact ST sales office for information about the specific conditions for products in die form.

4 Other information

4.1 Product marking description

Here below is described the marking of the package of both the engineering and flight models.

Figure 9. ESCC flight model marking outline




Table 7. ESCC flight model marking

Field	Description
ST	ST logo
YYWWZ	Date code and lot index in the week ⁽¹⁾
PM	Product marking
SN	Serialization number
F	Country of origin
ESA	ESA logo

1. Date code includes YY = two-digit year, WW = two-digit week, Z = assembly plant code.

Figure 10. Engineering model marking outline




Table 8. Engineering model marking

Field	Description
ST	ST logo
YYWWZ	Date code and lot index in the week ⁽¹⁾
PM	Product marking
F	Country of origin


1. Date code includes YY = two-digit year, WW = two-digit week, Z = assembly plant code.

4.2 Packing information

The 1N6642U versions are delivered in a 50-position, 50.8 x 50.8 mm² waffle pack consecutively populated from position 1.

The Figure 11 shows how to identify position 1, the orientation of the product in the waffle pack.

Figure 11. 1N6642U waffle pack outline



The diode anode is on the top pin of the device, and the anode identification dot is orientated at the opposite of the waffle pack truncated corner.

4.3 Documentation

In the [Table 9](#) is a summary of the documentation provided with each type of products.

Table 9. Documentation provided for each type of product

Quality level	Documentation
Engineering model	Certificate of conformance including : <ul style="list-style-type: none"> • Customer name • Customer purchase order number • ST sales order number and item • ST part number • Quantity delivered • Date code • Reference data sheet • Reference to TN1181 on engineering models • ST Rennes assembly lot ID
Flight model	Certificate of conformance including : <ul style="list-style-type: none"> • Customer name • Customer purchase order number • ST sales order number and item • ST part number • Quantity delivered • Date code • Serial numbers • Diffusion line (plant + wafer size) • Diffusion run (wafer lot number) and wafer ID • Reference of the applicable ESCC qualification maintenance lot • Reference to the ESCC detail specification • ST Rennes assembly lot ID number

Revision history

Table 10. Document revision history

Date	Revision	Changes
26-Mar-2010	1	First issue.
23-Sep-2011	2	Updated ESCC status in Features and added footnote to <i>Table 3</i> .
8-Nov-2013	3	Updated <i>Table 1</i> , <i>Table 5</i> and <i>Table 7</i> and inserted Other information.
04-Dec-2015	4	Updated <i>Table 7</i> and reformatted to current standard.
17-Nov-2025	5	Updated <i>Features</i> , <i>Description</i> , and Section 4: Other information . Added <i>Applications</i> and <i>Packing</i> information. Minor text changes.

Contents

1	Characteristics	2
1.1	Characteristics (curves)	4
2	Package information.....	5
2.1	LCC-2D package information	5
3	Ordering information	7
4	Other information.....	8
4.1	Product marking description	8
4.2	Packing information	9
4.3	Documentation	10
	Revision history	11

IMPORTANT NOTICE – READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice.

In the event of any conflict between the provisions of this document and the provisions of any contractual arrangement in force between the purchasers and ST, the provisions of such contractual arrangement shall prevail.

The purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgment.

The purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of the purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

If the purchasers identify an ST product that meets their functional and performance requirements but that is not designated for the purchasers' market segment, the purchasers shall contact ST for more information.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2025 STMicroelectronics – All rights reserved