

STM32F412G-DISCO

MB1209

Table of contents

Sheet 1: Project overview (this page)
Sheet 2: Top
Sheet 3: MCU
Sheet 4: Power
Sheet 5: ST-Link/V2-1
Sheet 6: QSPI
Sheet 7: Peripherals
Sheet 8: Audio
Sheet 9: USB_OTG_FS
Sheet 10: LCD
Sheet 11: Extension connectors

Legend

General comment such as function title, configuration, ...
Text to be added to silkscreen.
Warning text.
A Notes to generate the board layout.


Open Platform License Agreement

The Open Platform License Agreement (“Agreement”) is a binding legal contract between you (“You”) and STMicroelectronics International N.V. (“ST”), a company incorporated under the laws of the Netherlands acting for the purpose of this Agreement through its Swiss branch 39, Chemin du Champ des Filles, 1228 Plan-les-Ouates, Geneva, Switzerland.
By using the enclosed reference designs, schematics, PC board layouts, and documentation, in hardcopy or CAD tool file format (collectively, the “Reference Material”), You are agreeing to be bound by the terms and conditions of this Agreement. Do not use the Reference Material until You have read and agreed to this Agreement terms and conditions. The use of the Reference Material automatically implies the acceptance of the Agreement terms and conditions.
The complete Open Platform License Agreement can be found on www.st.com/opla .


U_Top
Top.SchDoc


Title: Project Overview		
Project: STM32F412G-DISCO		
Variant: F412ZGT6		
Revision: D-04	Reference: MB1209	
Size: A4	Date: 02/06/2021	Sheet: 1 of 12








Arduino uno connector








Reset Button




The 4 LEDs are top side


MICRO SD (TF) Card




I2C Extension Connector




JOYSTICK







Top side: layout of CN15




*, standard orientation. Rotations by 90, 180, 270 degrees possible by registers.

240x240 pixels TFT LCD with Capacitive Touch Panel



Capacitive Touch Panel connector of FRD154B2902-D-CTQ






CTP operation: MCU operating voltage range 1.8 to 3.6V

Pull-down to insure CTP is in Reset at power-on

SB41 open and SB42 closed = IM high: LCD in 16bits mode
SB41 closed and SB42 opened = IMlow : LCD in 8bits mode

LCD Operation: MCU operating voltage range 1.65 to 3.6V




higher voltage side (CTP)
lower voltage side (MCU)
I2C Level shifter option
(TR1, TR2, R65, R87 parts are not soldered)

Common mode supply filter

Not Fitted

Layout: parts close to STLD40D and grouped in same area with BLGND as local ground plane



Backlight driver & FPC connector for LCD panel



