



## Rad-Hard 60 V, 30 A, N-channel Power MOSFET



**SMD.5**



### Features

| $V_{DS}$ | $I_D$ | $R_{DS(on)}$ typ. | $Q_g$ |
|----------|-------|-------------------|-------|
| 60 V     | 30 A  | 36 mΩ             | 43 nC |

- Fast switching
- 100 % avalanche tested
- Hermetic package
- 50 krad TID
- SEE radiation hardened

### Description

The STRH40N6 is a N-channel Power MOSFET able to operate under severe environment conditions and radiation exposure. It provides high reliability performance and immunity to the total ionizing dose (TID) and single event effects (SEE).

Qualified as per ESCC detail specification No. 5205/024 and available in SMD.5 hermetic package it is specifically recommended for space and harsh environment applications and suitable for in-Satellite power conversion, motor control and power switch circuits.

In case of discrepancies between this datasheet and the relevant agency specification, the latter takes precedence.

#### Product status link

[STRH40N6](#)

### Device summary

| Product summary |                   |                  |         |             |                 |
|-----------------|-------------------|------------------|---------|-------------|-----------------|
| Part numbers    | Quality level     | ESCC Part number | Package | Lead finish | Radiation level |
| STRH40N6S1      | Engineering model | 5205/024         | SMD.5   | Gold        | -               |
| STRH40N6SG      | ESCC              |                  |         | Solder-dip  | 50 krad         |
| STRH40N6ST      | flight            |                  |         |             |                 |

Note: See [Table 8](#) for ordering information.

# 1 Electrical ratings

**Table 1. Absolute maximum ratings**

| Symbol         | Parameter   | Value      | Unit |
|----------------|---|------------|------|
| $V_{DS}^{(1)}$ | Drain-source voltage ( $V_{GS} = 0$ )                   | 60         | V    |
| $V_{GS}^{(2)}$ | Gate-source voltage                                     | $\pm 20$   | V    |
| $I_D$          | Drain current (continuous)                              | 30         | A    |
|                | Drain current (continuous) at $T_{amb} = 100\text{ °C}$ | 19         | A    |
| $I_{DM}^{(3)}$ | Drain current (pulsed)                                  | 120        | A    |
| $P_{TOT}$      | Total dissipation at $T_C = 25\text{ °C}$               | 75         | W    |
| $P_{TOT}$      | Total dissipation at $T_a = 25\text{ °C}$               | 2.5        | W    |
| $dv/dt^{(4)}$  | Peak diode recovery voltage slope                       | 2.5        | V/ns |
| $T_{op}$       | Operating temperature range                             | -55 to 150 | °C   |
| $T_j$          | Max. operating junction temperature range               | 150        | °C   |

1. This rating is guaranteed at  $T_j \geq 25\text{ °C}$  (see [Figure 9](#)).
2. This value is guaranteed over the full range of temperature.
3. Pulse width limited by safe operating area.
4.  $I_{SD} \leq 40\text{ A}$ ,  $di/dt \leq 1060\text{ A}/\mu\text{s}$ ,  $V_{DD} = 80\%V_{(BR)DSS}$

**Table 2. Thermal data**

| Symbol     | Parameter                               | Value | Unit |
|------------|---|-------|------|
| $R_{thJC}$ | Thermal resistance, junction-to-case    | 1.67  | °C/W |
| $R_{thJA}$ | Thermal resistance, junction-to-ambient | 50    | °C/W |

## 2 Avalanche data

**Table 3. Avalanche data**

| Symbol   | Parameter  | Value | Unit |
|----------|--|-------|------|
| $I_{AR}$ | Avalanche current, repetitive or not-repetitive<br>(pulse width limited by $T_J$ max.)   | 15    | A    |
| $E_{AS}$ | Single pulse avalanche energy<br>(starting $T_J = 25\text{ °C}$ , $I_D = 20\text{ A}$ , $V_{DD} = 40\text{ V}$ )                                 | 354   | mJ   |
| $E_{AS}$ | Single pulse avalanche energy<br>(starting $T_J = 110\text{ °C}$ , $I_D = 20\text{ A}$ , $V_{DD} = 40\text{ V}$ )                                | 105   |      |
| $E_{AR}$ | Repetitive avalanche<br>( $V_{DD} = 50\text{ V}$ , $I_{AR} = 17.5\text{ A}$ , $f = 10\text{ KHz}$ ,<br>$T_J = 25\text{ °C}$ , duty cycle = 50 %) | 20    | mJ   |
|          | Repetitive avalanche<br>( $V_{DD} = 40\text{ V}$ , $I_{AR} = 15\text{ A}$ , $f = 100\text{ KHz}$ ,<br>$T_J = 25\text{ °C}$ , duty cycle = 10 %)  | 1.3   |      |
|          | Repetitive avalanche<br>( $V_{DD} = 40\text{ V}$ , $I_{AR} = 15\text{ A}$ , $f = 100\text{ KHz}$ ,<br>$T_J = 110\text{ °C}$ , duty cycle = 10 %) | 0.4   |      |

1. Maximum rating value.

### 3 Electrical characteristics

**Table 4. Electrical characteristics ( $T_{amb} = 25\text{ °C}$  unless otherwise specified)**

| Symbol              | Parameter   | Test conditions  | Min. | Max.  | Unit          |
|---------------------|---|--|------|-------|---------------|
| $I_{DSS}$           | Zero gate voltage drain current<br>( $V_{GS} = 0$ ) | $BV_{DSS} = 48\text{ V}$   |      | 10    | $\mu\text{A}$ |
|                     |   | $BV_{DSS} = 48\text{ V}, T_C = 125\text{ °C}$  |      | 100   | $\mu\text{A}$ |
| $I_{GSS}$           | Gate body leakage current,<br>( $V_{DS} = 0$ )      | $V_{GS} = 20\text{ V}$   |      | 100   | nA            |
|                     |   | $V_{GS} = -20\text{ V}$  | -100 |       |               |
|                     |   | $V_{GS} = -20\text{ V}, T_C = 125\text{ °C}$   |      | 200   |               |
|                     |   | $V_{GS} = 20\text{ V}, T_C = 125\text{ °C}$  | -200 |       |               |
| $V_{(BR)DSS}^{(1)}$ | Drain-to-source breakdown voltage                   | $V_{GS} = 0\text{ V}, I_D = 1\text{ mA}$   | 60   |       | V             |
| $V_{GS(th)}$        | Gate threshold voltage                              | $V_{DS} = V_{GS}, I_D = 1\text{ mA}$   | 2    | 4.5   | V             |
|                     |   | $V_{DS} = V_{GS}, I_D = 1\text{ mA}, T_C = 125\text{ °C}$  | 1.5  | 3.7   |               |
|                     |   | $V_{DS} = V_{GS}, I_D = 1\text{ mA}, T_C = -55\text{ °C}$  | 2.1  | 5.5   |               |
| $R_{DS(on)}$        | Static drain-source on resistance                   | $V_{GS} = 12\text{ V}, I_D = 15\text{ A}$  |      | 0.045 | $\Omega$      |
|                     |   | $V_{GS} = 12\text{ V}, I_D = 15\text{ A}, T_a = 125\text{ °C}$                                     |      | 0.076 |               |
| $C_{iss}$           | Input capacitance                                   | $V_{DS} = 25\text{ V}, f = 1\text{ MHz}, V_{GS} = 0\text{ V}$                                      | 1312 | 1968  | pF            |
| $C_{oss}^{(2)}$     | Output capacitance                                  |  | 281  | 421   | pF            |
| $C_{rss}$           | Reverse transfer capacitance                        |  | 111  | 167   | pF            |
| $Q_g$               | Total gate charge                                   | $V_{DD} = 30\text{ V}, I_D = 40\text{ A}, V_{GS} = 12\text{ V}$                                    | 35   | 52    | nC            |
| $Q_{gs}$            | Gate-to-source charge                               |  | 9    | 13    | nC            |
| $Q_{gd}$            | Gate-to-drain ("Miller") charge                     |  | 12   | 18    | nC            |
| $t_{d(on)}$         | Turn-on delay time                                  | $V_{DD} = 30\text{ V}, I_D = 20\text{ A}, R_G = 4.7\text{ }\Omega, V_{GS} = 12\text{ V}$           | 13   | 21    | ns            |
| $t_r$               | Rise time   |  | 26   | 92    |               |
| $t_{d(off)}$        | Turn-off delay time                                 |  | 18   | 48    |               |
| $t_f$               | Fall time   |  | 7    | 16    |               |
| $V_{SD}^{(3)}$      | Diode forward voltage                               | $I_{SD} = 30\text{ A}, V_{GS} = 0\text{ V}$  |      | 1.5   | V             |
|                     |   | $I_{SD} = 30\text{ A}, V_{GS} = 0\text{ V}, T_a = 125\text{ °C}$                                   |      | 1.275 |               |
| $t_{rr}^{(2)}$      | Reverse recovery time                               | $I_{SD} = 40\text{ A}, di/dt = 100\text{ A}/\mu\text{s}, V_{DD} = 48\text{ V}, T_j = 25\text{ °C}$ | 288  | 432   |               |

1. This rating is guaranteed at  $T_j \geq 25\text{ °C}$  (see Figure 9. Normalized  $V_{(BR)DSS}$  vs temperature).

2. Not tested in production, guaranteed by process.

3. Pulsed: pulse duration = 300  $\mu\text{s}$ , duty cycle  $\leq 1.5\%$

## 4 Radiation characteristics

This products is guaranteed in radiation as per ESCC 5205/024 and ESCC 22900 specification at 50 krad. Each lot tested in radiation is accepted according to the characteristics as per [Table 5](#).

### 4.1 Total dose radiation (TID) testing

The bias with  $V_{GS} = +15\text{ V}$  and  $V_{DS} = 0\text{ V}$  is applied during irradiation exposure.

The parameters listed in [Table 5](#) are measured:

- Before irradiation
- After irradiation
- After 24 hrs at room temperature
- after 168 hrs at 100 °C anneal

**Table 5. Post-irradiation electrical characteristics ( $T_{amb} = 25\text{ °C}$  unless otherwise specified)**

| Symbol        | Parameter  | Test conditions                                | Min. | Max.  | Unit          |
|---------------|--|--|------|-------|---------------|
| $I_{DSS}$     | Zero gate voltage drain current ( $V_{GS} = 0$ ) | $V_{DS} = 48\text{ V}$                         |      | 10    | $\mu\text{A}$ |
| $I_{GSS}$     | Gate body leakage current, ( $V_{DS} = 0$ )      | $V_{GS} = 20\text{ V}$                         |      | 100   | nA            |
|               |  | $V_{GS} = -20\text{ V}$                        | -100 |       |               |
| $V_{(BR)DSS}$ | Drain-to-source breakdown voltage                | $V_{GS} = 0\text{ V}$ , $I_D = 1\text{ mA}$    | 48   |       | V             |
| $V_{GS(th)}$  | Gate threshold voltage                           | $V_{DS} = V_{GS}$ , $I_D = 1\text{ mA}$        | 2    | 4.5   | V             |
| $R_{DS(on)}$  | Static drain-source on resistance                | $V_{GS} = 12\text{ V}$ , $I_D = 15\text{ A}$   |      | 0.045 | $\Omega$      |
| $V_{SD}$      | Diode forward voltage                            | $I_{SD} = 30\text{ A}$ , $V_{GS} = 0\text{ V}$ |      | 1.5   | V             |

1. Pulsed: pulse duration = 300  $\mu\text{s}$ , duty cycle  $\leq 1.5\%$

## 4.2 Single event effect RBSOA

The STRH40N6 is extremely resistant to heavy ions exposure as per MIL-STD-750E, test method 1080, bias circuit of Figure 2.


SEB and SEGR tests are performed with a fluence of  $3e+5$  ions/cm<sup>2</sup> with the following acceptance criteria:

- SEB test: drain voltage checked, trigger level is set to  $V_{DS} = -5$  V. Stop condition: as soon as a SEB occurs or if the fluence reaches  $3e+5$  ions/cm<sup>2</sup>.
- SEGR test: the gate current is monitored every 200 ms. A gate stress is performed before and after irradiation. Stop condition: as soon as the gate current reaches 100 nA (during irradiation or during PIGS test) or if the fluence reaches  $3e+5$  ions/cm<sup>2</sup>.


**Table 6. Single event effect (SEE), reverse biased safe operating area (RBSOA)**

| Ion | Let (Mev/(mg/cm <sup>2</sup> )) | Energy (MeV) | Range (μm) |
|-----|---------------------------------|--------------|------------|
| Kr  | 32                              | 768          | 94         |
| Br  | 38                              | 300          | 38         |
| I   | 61                              | 330          | 31         |

**Figure 1. Single event effect, RBSOA**




**Figure 2. Single event effect, bias circuit**




AM09224v1

## 5 Electrical characteristics (curves)


**Figure 3. Safe operating area**




**Figure 4. Thermal impedance**









**Figure 5. Output characteristics**




**Figure 6. Transfer characteristics**




**Figure 7. Gate charge vs gate-source voltage**

**Figure 8. Capacitance variations**

**Figure 9. Normalized  $V_{(BR)DSS}$  vs temperature**

**Figure 10. Static drain-source on-resistance**

**Figure 11. Normalized gate threshold voltage vs temperature**

**Figure 12. Normalized on-resistance vs temperature**


**Figure 13. Source drain-diode forward characteristics**




## 6 Test circuits

**Figure 14. Switching times test circuit for resistive load**




*Note:* Max driver  $V_{GS}$  slope = 1 V/ns (no DUT)

**Figure 15. Source drain diode waveform**



**Figure 16. Unclamped inductive load test circuit (single pulse and repetitive)**




## 7 Package information

To meet environmental requirements, ST offers these devices in different grades of **ECOPACK** packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions, and product status are available at: [www.st.com](http://www.st.com). ECOPACK is an ST trademark.

### 7.1 SMD.5 package information

**Figure 17. SMD.5 package outline**



7386434\_REV7

**Table 7. SMD.5 package mechanical data**

| Dim. | mm    |       |       |
|------|-------|-------|-------|
|      | Min.  | Typ.  | Max.  |
| A    | 2.84  |       | 3.30  |
| A1   | 0.25  | 0.38  | 0.51  |
| b    | 7.13  | 7.26  | 7.39  |
| b1   | 5.58  | 5.72  | 5.84  |
| b2   | 2.28  | 2.41  | 2.54  |
| b3   | 2.92  | 3.05  | 3.18  |
| D    | 10.03 | 10.16 | 10.28 |
| D1   | 0.76  |       |       |
| E    | 7.39  | 7.52  | 7.64  |
| e    |       | 1.91  |       |

**Note:** The lid is not connected to any pin.

## 8 Order codes

**Table 8. Ordering information**

| Part number | Agency specification | Quality level     | Radiation level | Package | Weight | Lead finish | Marking <sup>(1)</sup> | Packing    |
|-------------|----------------------|-------------------|-----------------|---------|--------|-------------|------------------------|------------|
| STRH40N6S1  | -                    | Engineering model | -               | SMD.5   | 1 g    | Gold        | STRH40N6S1             | Strip pack |
| STRH40N6SG  | 5205/024/01          | ESCC              | 50 krad         |         |        |             | Solder-dip             |            |
| STRH40N6ST  | 5205/024/02          | flight            |                 |         |        | 520502402F  |                        |            |

1. *Specific marking only. The full marking includes in addition: For the Engineering Models: ST logo, date code; country of origin (FR). For ESCC flight parts: ST logo, date code, country of origin (FR), ESA logo, serial number of the part within the assembly lot.*

Contact ST sales office for information about specific conditions for products in die form.

## 9 Other information

### 9.1 Traceability information

Date code information is described in the table below.

**Table 9. Date codes**

| Model  | Date code <sup>(1)</sup> |
|--------|--------------------------|
| EM     | 3yywwN                   |
| Flight | yywwN                    |

1. yy = year, ww = week number, N = lot index in the week.

### 9.2 Documentation

**Table 10. Documentation provided for each type of product**

| Quality level     | Radiation level | Documentation  |
|-------------------|-----------------|--|
| Engineering model | -               | Certificate of conformance   |
| Flight            | 50 krad         | Certificate of conformance<br>ESCC qualification maintenance lot reference<br>Radiation data at 25 / 50 krad at 0.1 rad / s. |

## Revision history

**Table 11. Document revision history**

| Date        | Revision | Changes   |
|-------------|----------|---|
| 03-Jan-2011 | 1        | First release.  |
| 25-Aug-2011 | 2        | Updated order codes in <i>Table 1: Device summary</i> and <i>Table 14: Ordering information</i> .<br>Minor text changes.  |
| 09-Nov-2011 | 3        | Updated dynamic values on <i>Table 7: Pre-irradiation switching times</i> .<br>Document status changed from preliminary data to datasheet.  |
| 28-Mar-2012 | 4        | Updated title in cover page.  |
| 03-Oct-2012 | 5        | <i>Figure 4: Safe operating area</i> has been modified.   |
| 01-Jul-2013 | 6        | Updated order codes in <i>Table 1: Device summary</i> , <i>Table 12: Single event effect (SEE)</i> , <i>safe operating area (SOA)</i> , <i>Figure 2: Single event effect, SOA</i> and <i>Table 14: Ordering information</i> .<br>Added <i>Section 7.1: Other information</i> .<br>Minor text changes. |
| 09-Sep-2013 | 7        | Updated <i>features</i> in cover page.  |
| 14-May-2014 | 8        | Updated <i>Table 5: Pre-irradiation on/off states</i> .   |
| 19-May-2014 | 9        | Updated <i>Table 9: Post-irradiation on/off states @ T<sub>J</sub> = 25 °C, (Co60 γ rays 50 K Rad(Si))</i> .  |
| 04-Mar-2016 | 10       | Updated: <i>Features</i> , <i>Table 5</i> , <i>Table 8</i> , <i>Table 9</i> , <i>Table 10</i> , <i>Table 11</i> and <i>Table 15</i> .<br>Updated <i>Section 6: Package information</i> .<br>Minor text changes.   |
| 15-Jun-2021 | 11       | Updated <i>SMD.5 package information</i> .<br>Minor text changes.   |
| 07-Jul-2021 | 12       | Updated ESCC detail specification No. from 5205/021 to 5205/024.  |
| 04-Oct-2021 | 13       | Updated <i>Table 8</i> and <i>Table 10</i> .  |
| 08-Feb-2024 | 14       | Updated <i>Table 4</i> .  |
| 11-Sep-2024 | 15       | Updated <a href="#">Table 4</a> , and <a href="#">Table 5</a> .   |

**IMPORTANT NOTICE – READ CAREFULLY**

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgment.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, refer to [www.st.com/trademarks](http://www.st.com/trademarks). All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2024 STMicroelectronics – All rights reserved