

SOD128Flat

Automotive-grade rectifiers



SOD128Flat AEC-Q101-qualified power Schottky diodes


Housed in an SOD128Flat package – only 26 mg and 1 mm thick – ST's qualified 60 and 100 V power Schottky rectifiers are suited for miniature LED lighting, battery-powered equipment, power converters, motor drives, reverse battery protection diodes in automotive applications and equipment installed in harsh industrial environments thanks to a T_j range from -40 to 175 °C. Almost 60% thinner than the standard 2.4 mm-high SMA package – while fully footprint compatible – designers can create lighter and slimmer modules, or easily use these as replacements in existing designs.

KEY FEATURES

- 3 A, 5 A, 60 V and 100 V power Schottky diodes
- SOD128Flat smart package, only 1-mm thick
- Footprint compatible with standard SMA package
- Automotive-grade qualified
- AEC-Q101 qualified and PPAP capable
- T_j range from -40 to $+175$ °C
- ECOPACK®2 resin, RoHS-compliant packages


TARGETED APPLICATIONS

- LED lighting systems
- Small DC/DC converters (flyback, buck, and buck-boost typologies)
- Reverse battery protection circuits



BLOCK DIAGRAM

Small buck converter example



PACKAGE RANGE



STPS360AFY / STPS3H100AFY / STPS5H100FY
SOD128Flat non-exposed pad package

SOD128FLAT AUTOMOTIVE-GRADE POWER SCHOTTKY DIODE SELECTION GUIDE

	3 A	5 A
	SOD128Flat	
60 V	STPS360AFY	
100 V	STPS3H100AFY	STPS5H100AFY



© STMicroelectronics - February 2017 - Printed in United Kingdom - All rights reserved
The STMicroelectronics corporate logo is a registered trademark of the STMicroelectronics group of companies
All other names are the property of their respective owners

