




life.augmented



Quick Start Guide EVLIOL4LSV1

Industrial Tower Light Driver board based on L6364,
IPS4260L and STM32G071

Quick Start Guide Contents

Hardware Overview

Setup & Demo Examples

Documents & Related Resources

EVLIOL4LSV1

Hardware overview 1/2

Hardware Description

The EVLIOL4LSV1 is a driver board developed for industrial tower light applications. It simplifies all jumpers and jumper caps to streamline the circuitry, making the entire board closer to the final application product.

For general users, since its M12 connector meets the universal IO-Link standard, this board can be directly connected to any IO-Link master port. As the EVLIOL4LSV1 has preloaded examples with the IO-Link protocol stack, it can establish communication with the master quickly and stably. The communication connection status can be intuitively judged through the red and green indicators on the board. By importing the IO-Link file of EVLIOL4LSV1 into the control interface of the master, users can intuitively control the LED indicators' on and off states through PDO and monitor the button's pressed/released state on PDI.


For secondary developers, the board includes components such as L6364Q, STM32G071, IPS4260L, and SMBJ30CA. With the IO-Link ministack provided by ST (currently adapted to the G0, L0, and L4 series MCUs), developers can quickly verify the IO-Link communication function of the L6364Q and perform secondary development based on the reserved GPIO. The four-channel low-side driver chip IPS4260L on the board allows developers to drive simple 24V DC loads (indicators, solenoid valves, etc.), and its driving capability of up to 500mA per channel can meet most industrial light load application scenarios.

Main Features:

- IO-Link Communication (Supported by L6364Q and ST IO-Link Ministack)
- 4 Keys indicates the digital input
- 4 Low-side channel for external loads(tower light, valves)
- Reserved GPIOs for secondary development and evaluation of ST IO-Link Ministack
- Overload and over-temperature protections
- Open load detection
- ESD protection by SMBJ30CA
- UVLO



Latest info available at www.st.com
EVLIOL4LSV1




Key Products on the Nucleo expansion board:

SMBJ30CA, L6364Q, STM32G071, M24C02, IPS4260L
IO-Link Tower Light Driver board & ST IO-Link Ministack
evaluation board

EVLIOL4LSV1

Hardware overview 2/2



Bottom view



- Features for user
- Features for developer

X-CUBE-IOD02 software package

SW architecture overview

Software Description :

The package allows you to develop IO-Link sensor applications based on the L6364 mounted on the X-NUCLEO-IOD02A1 expansion board when connected to a NUCLEO-L073RZ or NUCLEO-G071RB or NUCLEO-L452RE or NUCLEO-F303RE development board.

The package can also be used to develop IO-Link sensor applications based on the L6362A mounted on the STEVAL-IOD003V1 expansion board when connected to a NUCLEO-L073RZ or NUCLEO-L452RE development board.


The software architecture is based on mini-stack libraries combined with source code communicating via APIs, and is designed to accommodate custom application development.

The expansion is built on STM32Cube software technology to ease portability across different STM32 microcontrollers.

Key Features:

- Complete software to build applications for the L6364 and L6362A IO-Link transceiver
- GPIOs, SPI, UART and IRQs configuration
- Smart software architecture based on mini-stack libraries combined with source code (communicating through API) and IODD configuration file
- Sample implementation available for X-NUCLEO-IOD02A1 expansion board connected to a NUCLEO-L073RZ or NUCLEO-G071RB or NUCLEO-L452RE or NUCLEO-F303RE development board
- Sample implementation available for STEVAL-IOD003V1 expansion board connected to a NUCLEO-L073RZ or NUCLEO-L452RE development board
- Easy portability across different MCU families, thanks to STM32Cube
- Free, user-friendly license terms

Latest info available at www.st.com
X-CUBE-IOD02



Quick Start Guide Contents

Hardware Overview


Setup & Demo Examples

Documents & Related Resources

Demo Example: Bill Of Material

HW pre-requisites

- 1x *IO-Link Master* (e.g. **STEVAL-IDP004V2**)
- 1x EVLIOL4LSV1
- 1x M12-A 4Pin Cable
- 1x 24V DC Power Supply
- 1x USB type A to micro-B cable
- 1x Laptop/PC with Windows 7, 8 or above
- (Optional) 1x 24VDC load (e.g. Tower Light, Valve)



Demo Example: software tools

SW pre-requisites

Both user and developer needs:

- TEConcept IO-Link Control Tool V3.9 (depends on master)
- USB Driver (CDM212364_Setup)

Developer also needs:


- X-CUBE-IOD02: software package with ST IO-Link ministack
- STCUBEPROGRAMMER: for downloading the firmware into the board.

Quick Start Up Steps (1/2)

TEConcept IO-Link Control Tool

Steps:

- Connect all the hardware as previous HW pre-requisites shown.
- Connect the Master to TEConcept IO-Link Control Tool
- Click “Power on” button of the port which EVLIOL4LSV1 connected. The board turns on red led



Quick Start Up Steps (2/2)

TEConcept IO-Link Control Tool

Steps:

- Click “IO-Link” button of the port which EVLIOL4LSV1 connected. The board turns off red led and turns on green led
- Click “Select device” and import the IODD of EVLIOL4LSV1. The app shows more parameters and the raw data shows a user-friendly format
- Click “Power on” and “IO-Link” of the port which EVLIOL4LSV1 connected
- Press the keys and the “PD Input” changes accordingly. Overwrite the “OUT”, the LED indicator turn on accordingly

Name	Index	Subindex	Rights	Type	Unit	Value
var Vendor Name	16	0	RO	String	STMicroelectronics	
var Vendor Text	17	0	RO	String	www.st.com	
var Product Name	18	0	RO	String	IO-Link-DIO	
var Product Text	20	0	RO	String	IO-Link-DIO	
var Product ID	19	0	RO	String	IO-Link-DIO	
var Serial Number	21	0	RO	String	0	
var Firmware Revision	23	0	RO	String	V2.1.0	
var Hardware Revision	22	0	RO	String	A	
var Vendor ID 1	0	8	RO	Unsigned In...	4	
var Vendor ID 2	0	9	RO	Unsigned In...	37	
var Device ID 1	0	10	RO	Unsigned In...	0	
var Device ID 2	0	11	RO	Unsigned In...	0	
var Device ID 3	0	12	RO	Unsigned In...	1	
var UART and COM Mode	76	0	RO	String	(Unknown)	
var System Command	2	0	WO	Unsigned In...	(Unknown)	

Name	Value	Formatted Value	Unit
Raw data	0x00	0x00	
Digital Input			
KEY1	UNPRESSED (false)	UNPRESSED (false)	
KEY2	UNPRESSED (false)	UNPRESSED (false)	
KEY3	UNPRESSED (false)	UNPRESSED (false)	
KEY4	UNPRESSED (false)	UNPRESSED (false)	

Name	Value	Formatted Value	Unit
Raw data	0xFF		
Process Data Out			
OUT1	ON (true)	ON (true)	
OUT2	ON (true)	ON (true)	
OUT3	ON (true)	ON (true)	
OUT4	ON (true)	ON (true)	



Further Information (Optional for user)

TEConcept IO-Link Control Tool

In the IO-Link Control Tool, the columns that can be seen include "Device Control", "Port Control", "Connected device state", "Parameter", and "Process Data".

In "Device Control" (red box), users can import the device description file "IODD". The device description file can translate the raw process data transmitted by IO-Link into more intuitive and readable results/status/options, and record the index address, parameter name, and data value of the parameters. Each time the master connects to the slave, the IO-Link Control Tool will automatically search and load the IODD that matches the Vendor ID and Device ID in the IODD library.

In "Port Control" (yellow box), users can power on/power off the port. Configure the CQ mode, including "Inactive", "DI" (Digital Input), "DO" (Digital Output), and "IO-Link" communication.

In "Connected device state" (blue box), the device information of the slave will be read, including vendor number, device number, product number, serial number, etc. The "Cycle time" is an important concept and parameter of IO-Link, defining a master-slave communication behavior where the master actively sends data and requests slave data. The cycle time is the time interval between two master-slave communication behaviors.

In "Parameter" (green box), user can see "Direct Parameter" and "Index Service Data Unit, ISDU". Users can distinguish them as direct parameters being the basic parameters of the device, including cycle time, minimum cycle time, vendor number, device number, product number, etc. ISDU records the parameter configuration of the slave device application layer, such as the distance judgment threshold of the distance sensor, the channel working mode of the multi-channel input/output module, and other parameters. The index address range of direct parameters is index = 0 or 1, and the subindex address range is subindex = 0~15. The index address range of ISDU is index > 1, subindex = 0.

The difference between parameters and process data is that parameters are not updated in real-time by polling but are read/written upon active request. On the host computer, you can click "Read All" to read all the parameters listed in the IODD at once. Click "Read Select" to read the parameter data of the selected index address. Click "Write Select" to write the parameter data to the selected index address.

In "Process Data" (black box), users can see the input process data "PD Input" uploaded by the slave and the output process data "PD Output" issued by the master. When the IODD is not imported, users see the raw process data in hexadecimal. After importing the IODD, users can see the parsed data, such as the state of the button being pressed/not pressed, the state of the indicator light being on/off.

The master can read the valid indication bit of the input process data from the slave and can also set the valid indication bit of the output process data. The valid indication bit ensures the validity of the data. When the slave is in a special situation, such as during online upgrade or in a high-temperature working environment, the slave can declare the input process data as invalid while uploading the input process data, leaving the decision-making power of data processing to the upper layer. Similarly, the master can also set the valid indication bit of the output process data. Note: Data validity indication and data integrity verification are not the same concept. Verifying data integrity can filter out data that has been tampered with in a noisy environment during transmission. Data integrity verification can be achieved through CRC check, parity check, and checksum.

The screenshot displays the TEConcept IO-Link Control Tool interface, divided into several functional areas:

- Device Control (Red Box):** Shows device information for a MiniDIO (230 4k Baud) with IO-Link revision V1.1, bit rate COM3, and a minimum cycle time of 4000 µs. It includes a "Select device" button.
- Port Control (Yellow Box):** Features "Power OFF" and "Power ON" buttons, along with configuration options for "Inactive", "DI", "DO", and "IO-Link".
- Connected device state (Blue Box):** Lists device details such as Vendor ID (0x0425), Device ID (0x000001), Product ID (IO-Link-DIO), Serial number (0), Vendor name (STMicroelectronics), Product name (IO-Link-DIO), Cycle time (4 000 µs), IO-Link Revision (V1.1), Port state (IO-Link), Operate in IO-Link (Yes), and Fault (NOFAULT).
- Parameters (Green Box):** A table listing parameters with columns for Name, Index, Subindex, Rights, Type, Unit, and Value.

Name	Index	Subindex	Rights	Type	Unit	Value
Identification Menu						
var Vendor Name	16	0	RO	String		STMicroelectronics
var Vendor Text	17	0	RO	String		www.st.com
var Product Name	18	0	RO	String		IO-Link-DIO
var Product Text	20	0	RO	String		IO-Link-DIO
var Product ID	19	0	RO	String		IO-Link-DIO
var Serial Number	21	0	RO	String		0
var Firmware Revision	23	0	RO	String		V2.1.0
var Hardware Revision	22	0	RO	String		A
var Vendor ID 1	0	8	RO	Unsigned In...		4
var Vendor ID 2	0	9	RO	Unsigned In...		37
var Device ID 1	0	10	RO	Unsigned In...		0
var Device ID 2	0	11	RO	Unsigned In...		0
var Device ID 3	0	12	RO	Unsigned In...		1
var UART and COM Mode	76	0	RO	String		(Unknown)
var System Command	2	0	WO	Unsigned In...		(Unknown)
Observation Menu						
- Process Data (Black Box):** Shows "PD input" and "PD output" with columns for Name, Value, Formatted Value, and Unit.

Name	Value	Formatted Value	Unit
PD input: Validity: valid			
△ Raw data	0x00	0x00	
Process Data In			
KEY1	UNPRESSED (false)	UNPRESSED (false)	
KEY2	UNPRESSED (false)	UNPRESSED (false)	
KEY3	UNPRESSED (false)	UNPRESSED (false)	
KEY4	UNPRESSED (false)	UNPRESSED (false)	
Process Data Out			
OUT1	OFF (false)	OFF (false)	
OUT2	OFF (false)	OFF (false)	
OUT3	OFF (false)	OFF (false)	
OUT4	OFF (false)	OFF (false)	

Quick Start Guide Contents

Hardware Overview

Setup & Demo Examples

Documents & Related Resources

Documents & related resources

All documents are available in the **DOCUMENTATION** tab of the related products webpage

EVLIO4LSV1 (IO-Link Device)

- **DB5300:** IO-Link actuator for industrial tower light based on L6364Q and IPS4260L – **Data Brief**
- **QSG:** this document - **Quick Start Guide**
- Schematics, Gerber files, BOM

STEVAL-IDP004V2 (IO-Link Master)

- **DB4029:** IO-Link master multi-port evaluation board based on L6360 – **Data Brief**
- **UM2232:** Getting started with the IO-Link evaluation solution firmware for STEVAL-IDP004V2 and STEVAL-IDP003V1 - **User manual**
- Schematics, Gerber files, BOM

X-CUBE-IOD02 (ST IO-Link Ministack)

- **DB3884:** Industrial IO-Link device software expansion for STM32Cube - **Data Brief**
- **UM2749:** Getting started with the X-CUBE-IOD02 industrial IO-Link device transceiver software expansion for STM32Cube - **User manual**

TEConcept IO-Link Control Tool

- <https://www.teconcept.de/en/downloads/> – **Link**