


Automotive OMNIFET II fully autoprotected Power MOSFET

Datasheet - production data



- Linear current limitation
- Thermal shutdown
- Short-circuit protection
- Integrated clamp
- Low current drawn from input pin
- Diagnostic feedback through input pin
- ESD protection
- Direct access to the gate of the Power MOSFET (analog driving)
- Compatible with standard Power MOSFET

Features

Max on-state resistance (per ch.)	R_{ON}	120 m Ω
Current limitation (typ)	I_{LIMH}	3.5 A
Drain-source clamp voltage	V_{CLAMP}	40 V

- AEC-Q100 qualified
- ECOPACK: lead free and RoHS compliant
- Designed to drive DC-13 loads according to EN 60947-5-1
- Designed to drive resistive, capacitive, inductive loads



Description

The VNS3NV04DP-E device is made up of two monolithic chips (OMNIFET II) housed in a standard SO-8 package. The OMNIFET II is designed using STMicroelectronics VIPower M0-3 technology and is intended for replacement of standard Power MOSFETs in up to 50 kHz DC applications.

Built-in thermal shutdown, linear current limitation and overvoltage clamp protect the chip in harsh environments.

Fault feedback can be detected by monitoring voltage at the input pin.

Table 1. Device summary

Package	Order codes	
	Tray	Tape and reel
SO-8	VNS3NV04DP-E	VNS3NV04DPTR-E

Contents

1	Block diagram and pin description	5
2	Electrical specifications	6
2.1	Absolute maximum ratings	6
2.2	Thermal data	7
2.3	Electrical characteristics	7
2.4	Electrical characteristics curves	12
3	Protection features	17
3.1	Overvoltage clamp protection	17
3.2	Linear current limiter circuit	17
3.3	Overtemperature and short circuit protection	17
3.4	Status feedback	17
4	Package and packing information	18
4.1	ECOPACK packages	18
4.2	SO-8 mechanical data	18
4.3	SO-8 packing information	20
5	Revision history	21

List of tables

Table 1.	Device summary	1
Table 2.	Configuration diagram (top view)	5
Table 3.	Current and voltage conventions	6
Table 4.	Absolute maximum ratings	6
Table 5.	Thermal data	7
Table 6.	Off	7
Table 7.	On	7
Table 8.	Dynamic	8
Table 9.	Switching	8
Table 10.	Source drain diode	8
Table 11.	Protections	8
Table 12.	SO-8 mechanical data	18
Table 13.	SO-8 package dimension	19
Table 14.	Document revision history	21

List of figures

Figure 1.	Block diagram	5
Figure 2.	Switching time test circuit for resistive load	9
Figure 3.	Test circuit for diode recovery times	10
Figure 4.	Unclamped inductive load test circuits	10
Figure 5.	Input charge test circuit.	11
Figure 6.	Unclamped inductive waveforms	11
Figure 7.	Source-drain diode forward characteristics	12
Figure 8.	Static drain-source on resistance	12
Figure 9.	Derating curve	12
Figure 10.	Static drain-source on resistance vs input voltage (part 1).	12
Figure 11.	Static drain-source on resistance vs input voltage (part 2).	12
Figure 12.	Transconductance	12
Figure 13.	Static drain-source on resistance vs I_d	13
Figure 14.	Transfer characteristics	13
Figure 15.	Turn-on current slope (part 1).	13
Figure 16.	Turn-on current slope (part 2).	13
Figure 17.	Input voltage vs input charge	13
Figure 18.	Turn-off drain source voltage slope (part 1)	13
Figure 19.	Turn-off drain-source voltage slope (part 2)	14
Figure 20.	Capacitance variations	14
Figure 21.	Switching time resistive load (part 1)	14
Figure 22.	Switching time resistive load (part 1)	14
Figure 25.	Normalized input threshold voltage vs temperature	15
Figure 26.	Normalized current limit vs junction temperature	15
Figure 27.	Step response current limit.	15
Figure 23.	Output characteristics	15
Figure 24.	Normalized on resistance vs temperature	15
Figure 28.	SO-8 tube shipment (no suffix).	20
Figure 29.	Tape and reel shipment (suffix "TR")	20

1 **Block diagram and pin description**

Figure 1. Block diagram






Table 2. Configuration diagram (top view)



2 Electrical specifications

Table 3. Current and voltage conventions



2.1 Absolute maximum ratings

Stressing the device above the rating listed in the “Absolute maximum ratings” table may cause permanent damage to the device. These are stress ratings only and operation of the device at these or any other conditions above those indicated in the operating sections of this specification is not implied. Exposure to Absolute maximum rating conditions for extended periods may affect device reliability. Refer also to the STMicroelectronics SURE program and other relevant quality document.

Table 4. Absolute maximum ratings

Symbol	Parameter	Value	Unit
V_{DSn}	Drain-Source Voltage ($V_{INn} = 0\text{ V}$)	Internally clamped	V
V_{INn}	Input voltage	Internally clamped	V
I_{INn}	Input current	+/- 20	mA
$R_{IN\ MINn}$	Minimum input series impedance	220	Ω
I_{Dn}	Drain current	Internally limited	A
I_{Rn}	Reverse DC output current	-5.5	A
V_{ESD1}	Electrostatic discharge ($R = 1.5\text{ K}\Omega$, $C = 100\text{ pF}$)	4000	V
V_{ESD2}	Electrostatic discharge on output pins only ($R = 330\ \Omega$, $C = 150\text{ pF}$)	16500	V
P_{tot}	Total dissipation at $T_c = 25\text{ }^\circ\text{C}$	4	W
T_j	Operating junction temperature	Internally limited	$^\circ\text{C}$
T_c	Case operating temperature	Internally limited	$^\circ\text{C}$
T_{stg}	Storage temperature	-55 to 150	$^\circ\text{C}$

2.2 Thermal data

Table 5. Thermal data

Symbol	Parameter	Max value	Unit
$R_{thj-lead}$	Thermal resistance junction-lead (per channel)	30	°C/W
$R_{thj-amb}$	Thermal resistance junction-ambient	80 ⁽¹⁾	°C/W

1. When mounted on a standard single-sided FR4 board with 50mm² of Cu (at least 35 µm thick) connected to all DRAIN pins of the relative channel

2.3 Electrical characteristics

Values specified in this section are for -40 °C < T_j < 150 °C, unless otherwise stated.

Table 6. Off

Symbol	Parameter	Test conditions	Min	Typ	Max	Unit
V _{CLAMP}	Drain-source clamp voltage	V _{IN} = 0 V; I _D = 1.5 A	40	45	55	V
V _{CLTH}	Drain-source clamp threshold voltage	V _{IN} = 0 V; I _D = 2 mA	36			V
V _{INTH}	Input threshold voltage	V _{DS} = V _{IN} ; I _D = 1 mA	0.5		2.5	V
I _{ISS}	Supply current from input pin	V _{DS} = 0 V; V _{IN} = 5 V		100	150	µA
V _{INCL}	Input-source clamp voltage	I _{IN} = 1 mA	6	6.8	8	V
		I _{IN} = -1 mA	-1		-0.3	V
I _{DSS}	Zero input voltage drain current (V _{IN} = 0 V)	V _{DS} = 13 V; V _{IN} = 0 V; T _j = 25 °C			30	µA
		V _{DS} = 25 V; V _{IN} = 0 V			75	µA

Table 7. On

Symbol	Parameter	Test conditions	Min	Typ	Max	Unit
R _{DS(on)}	Static drain-source on resistance	V _{IN} = 5 V; I _D = 1.5 A; T _j = 25 °C	—	—	120	mΩ
		V _{IN} = 5 V; I _D = 1.5 A	—	—	240	mΩ

T_j = 25 °C, unless otherwise specified

Table 8. Dynamic

Symbol	Parameter	Test conditions	Min	Typ	Max	Unit
$g_{fs}^{(1)}$	Forward transconductance	$V_{DD} = 13\text{ V}; I_D = 1.5\text{ A}$	—	5.0	—	S
C_{OSS}	Output capacitance	$V_{DS} = 13\text{ V}; f = 1\text{ MHz}; V_{IN} = 0\text{ V}$	—	150	—	pF

Table 9. Switching

Symbol	Parameter	Test conditions	Min	Typ	Max	Unit
$t_{d(on)}$	Turn-on delay time	$V_{DD} = 15\text{ V}; I_D = 1.5\text{ A};$ $V_{gen} = 5\text{ V}; R_{gen} = R_{IN}$ $R_{IN} = 220\ \Omega$ (see Figure 2)		90	300	ns
t_r	Rise time			250	750	ns
$t_{d(off)}$	Turn-off delay time			450	1350	ns
t_f	Fall time			250	750	ns
$t_{d(on)}$	Turn-on delay time	$V_{DD} = 15\text{ V}; I_D = 1.5\text{ A};$ $V_{gen} = 5\text{ V}; R_{gen} = 2.2\text{ K}\Omega$ (see Figure 2)		0.45	1.35	μs
t_r	Rise time			2.5	7.5	μs
$t_{d(off)}$	Turn-off delay time			3.3	10.0	μs
t_f	Fall time			2.0	6.0	μs
$(di/dt)_{on}$	Turn-on current slope	$V_{DD} = 15\text{ V}; I_D = 1.5\text{ A};$ $V_{gen} = 5\text{ V};$ $R_{gen} = R_{IN\text{ MIN}} = 220\ \Omega$		4.7		A/ μs
Q_i	Total input charge	$V_{DD} = 12\text{ V}; I_D = 1.5\text{ A}; V_{IN} = 5\text{ V};$ $I_{gen} = 2.13\text{ mA}$ (see Figure 5)		8.5		nC

Table 10. Source drain diode

Symbol	Parameter	Test conditions	Min	Typ	Max	Unit
$V_{SD}^{(1)}$	Forward on voltage	$I_{SD} = 1.5\text{ A}; V_{IN} = 0\text{ V}$		0.8		V
t_{rr}	Reverse recovery time	$I_{SD} = 1.5\text{ A}; di/dt = 12\text{ A}/\mu\text{s};$ $V_{DD} = 30\text{ V}; L = 200\ \mu\text{H}$ (see Figure 3)		107		ns
Q_{rr}	Reverse recovery charge			37		μC
I_{RRM}	Reverse recovery current			0.7		A

1. Pulsed: Pulse duration = 300 μs , duty cycle 1.5%

$-40\text{ }^\circ\text{C} < T_j < 150\text{ }^\circ\text{C}$, unless otherwise specified

Table 11. Protections

Symbol	Parameter	Test conditions	Min	Typ	Max	Unit
I_{lim}	Drain current limit	$V_{IN} = 5\text{ V}; V_{DS} = 13\text{ V}$	3.5	5	7	A
t_{dlim}	Step response current limit	$V_{IN} = 5\text{ V}; V_{DS} = 13\text{ V}$		10		μs
T_{jsh}	Overtemperature shutdown		150	175	200	$^\circ\text{C}$

Table 11. Protections (continued)

Symbol	Parameter	Test conditions	Min	Typ	Max	Unit
T_{jrs}	Overtemperature reset		135			°C
I_{gf}	Fault sink current	$V_{IN} = 5\text{ V}$; $V_{DS} = 13\text{ V}$; $T_J = T_{Jsh}$	10	15	20	mA
E_{as}	Single pulse avalanche energy	Starting $T_J = 25\text{ °C}$; $V_{DD} = 24\text{ V}$; $V_{IN} = 5\text{ V}$; $R_{gen} = R_{IN\text{ MIN}} = 220\text{ }\Omega$; $L = 24\text{ mH}$ (see Figure 4 and Figure 6)	100			mJ

Figure 2. Switching time test circuit for resistive load




Figure 3. Test circuit for diode recovery times




Figure 4. Unclamped inductive load test circuits




Figure 5. Input charge test circuit





Figure 6. Unclamped inductive waveforms



2.4 Electrical characteristics curves

Figure 7. Source-drain diode forward characteristics




Figure 8. Static drain-source on resistance




Figure 9. Derating curve




Figure 10. Static drain-source on resistance vs input voltage (part 1)




Figure 11. Static drain-source on resistance vs input voltage (part 2)





Figure 12. Transconductance






Figure 13. Static drain-source on resistance vs Vin




Figure 14. Transfer characteristics




Figure 15. Turn-on current slope (part 1)




Figure 16. Turn-on current slope (part 2)




Figure 17. Input voltage vs input charge




Figure 18. Turn-off drain source voltage slope (part 1)




Figure 19. Turn-off drain-source voltage slope (part 2)




Figure 21. Switching time resistive load (part 1)




Figure 23. Output characteristics




Figure 24. Normalized on resistance vs temperature




Figure 25. Normalized input threshold voltage vs temperature




Figure 26. Normalized current limit vs junction temperature





Figure 27. Step response current limit



3 Protection features

During normal operation, the INPUT pin is electrically connected to the gate of the internal power MOSFET through a low impedance path.

The device then behaves like a standard power MOSFET and can be used as a switch from DC up to 50 KHz. The only difference from the user's standpoint is that a small DC current I_{SS} (typ. 100 μ A) flows into the INPUT pin in order to supply the internal circuitry.

The following sections describe the device features.

3.1 Overvoltage clamp protection

Internally set at 45 V, along with the rugged avalanche characteristics of the Power MOSFET stage give this device unrivalled ruggedness and energy handling capability. This feature is mainly important when driving inductive loads.

3.2 Linear current limiter circuit

Limits the drain current I_D to I_{lim} whatever the INPUT pin voltages. When the current limiter is active, the device operates in the linear region, so power dissipation may exceed the capability of the heatsink. Both case and junction temperatures increase, and if this phase lasts long enough, junction temperature may reach the overtemperature threshold T_{jsh} .

3.3 Overtemperature and short circuit protection

These are based on sensing the chip temperature and are not dependent on the input voltage. The location of the sensing element on the chip in the power stage area ensures fast, accurate detection of the junction temperature. Overtemperature cutout occurs in the range 150 to 190 °C, a typical value being 170 °C. The device is automatically restarted when the chip temperature falls of about 15 °C below shutdown temperature.

3.4 Status feedback

In the case of an overtemperature fault condition ($T_j > T_{jsh}$), the device tries to sink a diagnostic current I_{gf} through the INPUT pin in order to indicate fault condition. If driven from a low impedance source, this current may be used in order to warn the control circuit of a device shutdown. If the drive impedance is high enough so that the INPUT pin driver is not able to supply the current I_{gf} , the INPUT pin falls to 0 V. This however not affects the device operation: no requirement is put on the current capability of the INPUT pin driver except to be able to supply the normal operation drive current I_{SS} .

Additional features of this device are ESD protection according to the Human Body model and the ability to be driven from a TTL Logic circuit.

4 Package and packing information

4.1 ECOPACK packages

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: www.st.com. ECOPACK is an ST trademark.


4.2 SO-8 mechanical data

Table 12. SO-8 mechanical data

Dim.	mm		
	Min.	Typ.	Max.
A			1.75
A1	0.10		0.25
A2	1.25		
b	0.28		0.48
c	0.17		0.23
D ⁽¹⁾	4.80	4.90	5.00
E	5.80	6.00	6.20
E1 ⁽²⁾	3.80	3.90	4.00
e		1.27	
h	0.25		0.50
L	0.40		1.27
L1		1.04	
k	0°		8°
ccc			0.10

1. Dimension "D" does not include mold Flash, protrusions or gate burrs. Mold flash, protrusions or gate burrs shall not exceed 0.15 mm in total (both side).
2. Dimension "E1" does not include interlead flash or protrusions. Interlead flash or protrusions shall not exceed 0.25 mm per side.

Table 13. SO-8 package dimension



4.3 SO-8 packing information

Figure 28. SO-8 tube shipment (no suffix)





Figure 29. Tape and reel shipment (suffix "TR")



5 Revision history

Table 14. Document revision history

Date	Revision	Changes
09-Mar-2011	1	Initial release.
18-Sep-2013	2	Updated Disclaimer
04-Jul-2023	3	Updated Table 4: Absolute maximum ratings .
19-Oct-2025	4	Updated Features

IMPORTANT NOTICE – PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2025 STMicroelectronics – All rights reserved