




STSPIN L6480 and L6482

ST motor drivers are moving the future

Digital. Accurate. Versatile.


The L6480 and L6482 ICs integrate a complex logic core providing a set of **high-level features**



Digital. Accurate. Versatile.

3

The devices also integrate **analog circuitry** and a **complete gate driving stage** making it a complete solution for stepper motor driving applications requiring high power.



L6480 and L6482 characteristics


4

- Supply voltage **7.5 to 85 V**
- Dual full-bridge **gate drivers**
- Fully **programmable gate driving**
- Overcurrent protection based on MOSFET drain-source drop
- Up to **128 microsteps** (L6480)
- Current control
 - **L6480: Voltage mode driving**
 - **L6482: Advanced current control**
- **Sensorless stall detection** (L6480)
- **Digital Motion Engine**
 - Programmable speed profile
 - High-level commands
- **8-bit 5 MHz SPI interface**
(Daisy-chain compatible)
- Integrated 16 MHz oscillator
- Integrated 5-bit ADC
- Integrated 15 V / 7.5 V voltage regulator
- Integrated 3.3 V voltage regulator
- **Overcurrent, overtemperature and undervoltage protections**
- **HTSSOP package**

Intelligence integration


5

Before L6480/82 ...



with **L6480/82** ...


- System is greatly simplified
- Dedicated MCU no longer needed to perform speed profile and positioning calculations
- Less components
- Single MCU can drive more devices at the same time



A full-digital interface to MCU


7

- The fast SPI interface with **daisy-chain** capability allows a single MCU to manage multiple devices
- Programmable alarm **FLAG** open-drain output for interrupt-based FW
In daisy-chain configuration, **FLAG** pins of different devices can be OR-wired to save host controller GPIOs
- **BUSY** open-drain output allows the MCU to know when the last command has been performed
In daisy-chain configuration, **BUSY** pins of different devices can be OR-wired to save host controller GPIOs
- **BUSY** can be used as **SYNC** signal giving a feedback of the step-clock to the MCU
(programmable # of microsteps)



Fully programmable speed profile boundaries

8




Positioning features: Movement command

9

Move(N, DIR) command
perform a motion of N steps
in the selected direction.

This command can be
performed only when the
motor is stopped.



Positioning features:

Absolute positioning commands



10

GoTo(Target) command: reach the target position using shortest path.

This command can be performed only when motor is stopped or is running at constant speed.

GoTo_DIR(Target, DIR) command: reach the target position moving the motor in the selected direction.


This command can be performed only when the motor is stopped or is running at constant speed.



Speed tracking features: Constant speed command

11


Run(SPD, DIR) command drives the motor to reach the target speed SPD in the selected direction. Target speed and direction can be changed anytime.




Limit switch management

12


At power-up, the load could be in an unknown position.
The absolute position counter should be initialized.



The **GoUntil** command moves the mechanical load to the limit switch position.



The **ReleaseSW** command moves the mechanical load on the limit switch triggering threshold.



Undervoltage on the ADC input

13

The ADC input can also be monitored to detect an undervoltage condition on the motor supply voltage.

If the ADC input falls below the fixed **1.16 V** threshold, an UVLO_ADC event is signaled by the device diagnostic but no automatic actions are performed.

When the ADC is used for the power supply configuration (ADCIN voltage at 1.65 V when nominal voltage is present), the **UVLO** is signaled when the VS voltage is **below 70 % of the nominal value.**

Programmable overcurrent protection

14


Each MOSFET of the external power stage is protected by an overcurrent protection system.

The overcurrent protection system monitors the voltage drop of the MOS and detects when its value exceeds the programmed threshold which can be set **from 31.25 mV to 1 V**. In this case, the whole power stage is **immediately turned OFF**.

The power stage **cannot be enabled until a GetStatus command releases the failure condition**.


Programmable overcurrent protection

15



Warning temperature and thermal shutdown

16



The devices integrate a diagnostic register collecting the information about the status of the system:




STATUS Register

- Power stage enabled/disabled
- Command under execution (BUSY)
- Motor status (direction, acc., dec., etc.)
- Step-clock mode
- Overcurrent
- Thermal status
- Undervoltage (it indicates the power-up status also)
- Undervoltage on ADC input
- Stall detection
- SW status
- SW input falling edge (limit switch turn-on)
- Incorrect or not performable command received

Programmable gate drivers


Integrated gate drivers are fully programmable, allowing the L6480 and L6482 to fit a wide variety of MOSFETs and adjusting output slew-rates according to application requirements.




Integrated voltage regulators

Supply management:

- Integrated voltage regulators allow the device to be self-supplied through a high-voltage bus.
- Input and output pins of both voltage regulators are accessible. Several supply scenarios are supported.
- **Regulators cannot be used to supply external devices.**






L6480

Voltage mode driving


BEMF compensation

21

Without BEMF compensation




With BEMF compensation



BEMF compensation

22




BEMF compensation

23


According to motor conditions (acc/deceleration, constant speed, hold), a different torque, and then current, could be needed.

The device logic switches from different compensation parameters sets according to motor status.



BEMF compensation



24



Supply voltage compensation


25

The voltage sinewaves are generated through a PWM modulation. As a consequence, the actual phase voltage depends on the supply voltage of the power stage.



Supply voltage compensation


26




Sensorless stall detection

28

Using integrated current sensing and the adjustable STALL current threshold (i.e. voltage drop on the external MOSFET), a cheap and easy stall detection can be implemented.




Normal operation




Sensorless stall detection

29

Using integrated current sensing and the adjustable STALL current threshold (i.e. voltage drop on the external MOSFET), a cheap and easy stall detection can be implemented.



STALL!
BEMF is null and
current is suddenly
increased




Sensorless stall detection

30

The stall condition is checked measuring the voltage drop on the low-side MOSFETS only.

STALL DAC generates a reference current which is used to generate the reference voltage



Sensorless stall detection voltage threshold

Sensorless stall detection limitations

31

Stall detection performances can be reduced in the following conditions:


- Low speed
(negligible BEMF value)
- High speed
(current can be low because the low-pass filtering effect of the inductor)

Slow speed optimization


32


- During low-speed movements, the sinewave current could suffer from zero-crossing distortion. As result, **the motor rotation is discontinuous.**
- New low-speed optimization algorithm heavily reduces the distortion. **Smoothness of the driving is increased.**

Without low speed optimization



With low speed optimization






L6482

Advanced current control

- **Automatic selection of the decay mode**
Stable current control in microstepping
- **Slow decay and fast decay balancing**
Reduced current ripple
- **Predictive current control**
Average current control

Challenges to perform the right decay

35




During the OFF state, both slow and fast decay must be used for a better control:

L6482 performs an
AUTO-ADJUSTED DECAY

Auto-adjusted decay

36




Parameter	Function
TON_MIN	Target minimum ON time
$TOFF_FAST$	Maximum fast decay duration
TSW	Fixed OFF time(*)

(*) No predictive control

Auto-adjusted decay


37



Parameter	Function
TON_MIN	Target minimum ON time
TOFF_FAST	Maximum fast decay duration
TSW	Fixed OFF time(*)



Falling step control

38



Predictive current control: average current

39



The extra on time is calculated cycle-by-cycle using the following formula:


$$t_{\text{PRED}n} = (t_{\text{ON}n-1} + t_{\text{ON}n})/2$$

Note: The TON_MIN limit of the current control is checked on t_{ON} time only.

If $t_{\text{ON}} < \text{TON_MIN}$, no extra on time is performed and the decay adjustment sequence is performed.

Predictive current control: average current

40




When the system reaches the stability $\rightarrow t_{\text{PRED}}^n = t_{\text{ON}}^n$

In this case, the average current is equal to the reference: the system implements a control of the average value of the current.

Predictive current control: switching freq.

41




Current sensing

42

The peak DAC defines the amplitude of the microstepping sinewave (TVAL_X registers)

The microstep DAC returns a fraction of the peak according to the EL_POS register


The reference is compared to the voltage on the SENSE pin



Typical application

43


- Minimal component count
- MCU needs only **1 SPI interface** and **2-4 optional GPIOs**



Typical application

44

- Minimal component count
- MCU needs only **1 SPI interface** and **2-4 optional GPIOs**



Competitive advantages

45

- High level of integration
- Voltage mode driving
- External power stage is protected
- Advanced diagnostics
- Extended power range
- Suitable for multi-motor applications

Further information and full design support can be found at www.st.com/stspin