



life.augmented

# STM32WB series MCU with built-in Bluetooth® 5.0 and IEEE 802.15.4



# Make the choice of STM32WB series the 7 keys points to make the difference

 **Bluetooth® 5**


**OPENTHREAD**  
released by Google



**Open 2.4 GHz radio  
Multi-protocol**




**Dual-core / Full control  
Ultra-low-power**



**IoT Protection ready**



**Massive integration  
Cost saving**



**A large offer**




**STM32  
CubeMonitor-RF**

**Advanced RF tool, Energy control  
with C code generation**




**No matter what!**

# Multiprotocol and open radio




- Fully certified Bluetooth® 5.0 radio
- 2x faster speed with 2Mbps capable mode
- Extend network coverage with BLE Mesh
- Last IEEE 802.15.4 standard ready
- OpenThread, ZigBee 3.0
- Bluetooth 5.0 and 802.15.4 protocols in Static and Dynamic concurrent mode
- Proprietary protocol capable (Bluetooth Low Energy like or 802.15.4)
- Best-in-class RF with up to +6dBm output power and 102 dB link budget
- Energy sensitive application with only 4.5mA in RX and 5.2mA in TX (@ 0dBm)
- BOM cost reduction thanks to Integrated balun

# Make it yours




# Simplicity of development

## 2 independent cores for real-time execution



- **Drawbacks**

- Time sharing
- Longer processing time – Greedy current consumption
- Need companion MCU (increased cost)



- **Benefits**

- SOC solution (1 single die)
- Full flexibility - Easy development – User experience
- Increase battery life
- All-in-1 solution - cost saving
- Speed up time to market
- Easy certification process

# Rich feature set

## KEY FEATURES

**2 independent cores for real time execution**

### Ultra-low-power consumption

- 50  $\mu$ A/MHz Active mode (at 3.0V)
- 2.1  $\mu$ A Stop mode (Radio in standby + 256KB RAM)
- < 50 nA Shutdown mode

### Peripherals

- 2xI<sup>2</sup>C, 1xUSART, 1xLP-UART, 2xSPI, 1x USB 2.0 FS device supporting Battery Charging Detection, 1xSAI, Quad-SPI (XIP), 6x 16-bit timer (including LPWM and low-power one)

**1.7 to 3.6V voltage range (DC/DC, LDO)**

**-40°C to +105°C temperature range**

**Security**  
PCROP, PKA,  
TRNG  
AES 256-bit,  
CKS

Arm® Cortex®-M4  
MPU + FPU  
+ DSP Inst.  
@ 64 MHz

ART Accelerator™  
Up to 1MB Flash  
Up to 256KB SRAM

LCD 8x40

ADC 12-bit  
2x Comp  
Temp sensor  
Cap. Touch

USB 2.0 FS  
Crystal-less  
SPI, I<sup>2</sup>C  
LP-UART  
SAI, Quad-SPI

Arm Cortex-M0+ Core  
@ 32 MHz  
2.4 GHz Radio  
**Bluetooth 5.0**  
**802.15.4**  
Concurrent mode

# Benefit of dual cores processing

## 1 Independent Radio activity

- Uploading data to mesh network or smartphone
- OTA of Radio protocol stack or application FW
- Running on Arm Cortex-M0+

## 2 Energy saving mode

- RAM + RTC running @ 2.1  $\mu$ A
- Fast wake up @ 5  $\mu$ s

## 3 Main application activity


- Computing data (sensor fusion ...)
- Flexible Arm Cortex-M4 CPU speed up to 64 MHz
- Batch Acquisition Mode (BAM) with CPU & Flash turned off

## 4 Dual CPU activity

- 50  $\mu$ A/MHz only!
- Both Radio and Application running independently

## 5 Super saving mode

- Shutdown < 50 nA
- Battery energy saving





# All in one MCU full flexibility control

- Robust RF link **-100dBm** sensitivity with IEEE 802.15.4 and **+6 dBm** output power
- Upgrade legacy 802.15.4 device to **Bluetooth 5.0**
- **Update** securely Radio and stack firmware with build-in FUS
- Bluetooth 5 and 802.15.4 protocols **Mesh capable** to extend network range



Lighting

- **Up to 105°C** radio capable
- **External PA** support to get ultra wide communication distance
- Down to **600 nA mode with RTC** and 32KB of RAM
- Only **5µs wakeup** time over 16 wakeup lines
- PCROP, **ECC**, TRNG, **PKA**, for best design robustness
- Reduce BOM cost with **built-in LCD booster**



Industrial devices

- **Beacon** profile available among a huge list
- **Embedded balun** to minimize design cost
- Only **5.2mA Radio TX** current to extend beacon life time
- **Up to +6 dBm** output power to get best beacon range
- **< 2.1 µA Stop mode** with full RAM for **battery life** optimization
- Down to 1.71 full feature capable



Beaconing



Fleet maintenance

- Retrofit legacy product to **Bluetooth® 5.0** and concurrency mode
- Remotely upgrade device with **OTA capability**
- **Brand protection** with Authenticated **FW upgrade** system



Fitness/Healthcare

- **Multipoint** BLE 5 connections
- Small form factor design with **CSP100 pins**
- Battery life time care with **< 50 nA** Shutdown mode
- Dynamic Efficient **50 µA/MHz**
- Extend memory storage with **Quad-SPI**
- Handle advanced algorithm with **1 Mbyte** of Flash
- Cost optimized product with USB 2.0 **crystal-less** device




Home security and Audio

- **-100 dBm** sensitivity to increase area coverage
- **Customer Key Storage (CKS)** for trustable Application update
- Manage full duplex **audio** with embedded SAI
- USB FS 2.0 with Battery **Charging Detection** for remote device



# IoT protection ready (1/2)



## radio stack and/or application FW update



- 1 New FW package received
- 2 New FW detected Update is launched
- 3 App Processor send New FW package signature and encryption key for authentication
- 4 Authentication signature matches preprogrammed key Case not, the process is aborted and device resets
- 5 New FW package is decrypted with proprietary Key. Device upload on going.

# IoT protection ready (2/2)

## STM32WB counter measure against attacks

Advanced	Attacks	Attacks description	STM32WB Countermeasures
Basic	<b>Non Invasive Attacks</b> 	<ul style="list-style-type: none"> <li>• Environment modification                             <ul style="list-style-type: none"> <li>• Temperature</li> <li>• Voltage</li> <li>• Clock ....</li> </ul> </li> <li>• Fault injection (glitches....)</li> <li>• Exploit debug features</li> <li>• Side channel, power Analysis, ...</li> </ul>	<ul style="list-style-type: none"> <li>• Temperature sensor</li> <li>• Power supply integrity monitor</li> <li>• Clock security system</li> <li>• Tamper pads</li> <li>• Memory ECC, Parity check</li> <li>• RTC alarm, registers, SRAM mass erase</li> <li>• JTAG Read out protection</li> <li>• BOOT from Flash only</li> </ul>
	<b>Software Attacks</b> 	<ul style="list-style-type: none"> <li>• Low Authentication / Encryption</li> <li>• Extract keys</li> <li>• Exploitation of applicative test features</li> <li>• Malware / Virus</li> <li>• Replay, privilege escalation</li> </ul>	<ul style="list-style-type: none"> <li>• Customer Key Storage (CKS)</li> <li>• RNG, Crypto accelerator, CRC</li> <li>• Write memory protection</li> <li>• Read Out memory protection</li> <li>• Memory Protection Unit (MPU)</li> <li>• Firmware Upgrade Service (FUS)</li> <li>• Secure Firmware Update (SFU)</li> <li>• Proprietary Code Read-Out Protection (PCROP)</li> <li>• 96-bit ID</li> </ul>

# Massive cost saving

The more feature integration, the more the BOM drops down !

## Silicon cost


- RF balun cost: Embedded
- External components: 7
- 32 kHz Master clock output available
- Crystal for USB 2.0 FS operation: embedded
- LCD display booster: embedded (only single glass)
- Capacitive touch controller: embedded
- PCB cost: 2 layers PCB only

## Ecosystem cost


- Bluetooth® 5.0 stack: Free of charge
- ZigBee 3.0 stack: Free of charge
- OpenThread stack: Free of charge
- Generic 802.15.4 MAC: Free of charge
- Generic HCI drivers: Free of charge
- STM32CubeMX: Free of charge
- STM32CubeMonitor-RF: Free of charge
- IDEs (AC6: SW4STM32; ST: STM32CubeIDE): Free of charge
- BLE and 802.15.4 concurrency avoids to use a second radio MCU

# STM32WB50 value line

Essentials features product targeting  
entry-level Bluetooth® 5.0 and Mesh application



# STM32WB50 positioning



# STM32WB - a large offer

Bluetooth® 5.0, OpenThread, ZigBee 3.0  
and proprietary protocol capable




from 1.7 V to 3.6 V  
from -40°C to +105°C

Legend:  STM32WBx5 line  STM32WBx0 Value line pin-to-pin compatible with STM32WBx5

# Advanced functionalities

## Audio - Voice & streaming

Full-duplex audio streaming over Bluetooth® 5.0 using Opus codec  
STM32Cube function pack for STM32WB MCU: [FP-AUD-BVLINKWB1](#)



STM32WB Nucleo development board  
+  
Digital MEMS microphones Expansion board





## Sensor fusion & activity recognition

BLE connectivity with environmental and motion sensors  
STM32Cube function pack for STM32WB MCU: [FP-SNS-MOTENVWB1](#)





STM32WB Nucleo-64  
development board  
+  
Motion MEMS and  
Environmental Sensor  
Expansion board



Both packages are compatible with  
**STBLESensor** app for iOS and Android




# Prototyping made as easy as 1,2,3



# IPD - MLPF-WB55-01E3 harmonic filter with integrated impedance matching



Integrated Balun



STM32WB
Arm Cortex-M4 Application Firmware + Peripherals
Arm Cortex-M0+ Radio Stack

MLPF-WB55-01E3
Integrated STM32WB impedance matching
Deep rejection harmonic filter



# STM32CubeMonitor-RF

- Exercise wireless features of STM32WB55
  - Bluetooth® Low Energy (BLE) commands
  - BLE RF tests
  - send OpenThread commands
  - perform 802.15.4 RF tests

- DUT - Nucleo, USB dongle or customer boards.
- USB or UART to Virtual Com Port




Mode selection



# Software development tools

A complete flow, from configuration up to monitoring




Windows

macOS®



FREE  
IDE's



armKEIL




STM32  
CubeIDE

More to come after mass market launch

STM32  
CubeMonitor-RF

STM32  
CubeProgrammer



**STM32CubeMX**  
Configure & Generate Code


**Partners IDEs**  
Compile and Debug

**STM32CubeMonRF**  
**STM32CubeProg**

# Find easily the MCU that suits YOU tablets/phones/computers ST MCU finder




- Browse STM32 & STM8 families wide portfolio and select the product that best fit their needs
- Access to technical information
- Also works offline !



[www.st.com/STMCUFinder](http://www.st.com/STMCUFinder)



# End-to-End Ecosystem







# STM32 MCU “Wireless” series



High Perf  
MCUs

**STM32F2**

398 CoreMark  
120 MHz

**STM32F4**

608 CoreMark  
180 MHz

**STM32H7**

3224 CoreMark  
240 MHz Cortex -M4  
480 MHz Cortex -M7

**STM32F7**

1082 CoreMark  
216 MHz



Mainstream  
MCUs

**STM32F0**

106 CoreMark  
48 MHz

**STM32G0**

142 CoreMark  
64 MHz

**STM32F1**

177 CoreMark  
72 MHz

**STM32F3**

245 CoreMark  
72 MHz

**STM32G4**

550 CoreMark  
170 MHz



Ultra-low Power  
MCUs

**STM32L0**

75 CoreMark  
32 MHz

**STM32L1**

93 CoreMark  
32 MHz

**STM32L5**

424 CoreMark  
110 MHz

**STM32L4**

273 CoreMark  
80 MHz

**STM32L4+**

409 CoreMark  
120 MHz



Wireless  
MCUs

**STM32WL**

161 CoreMark  
48 MHz

**STM32WB**

216 CoreMark  
64 MHz



Arm® Cortex® core

-M0

-M0+

-M3

-M33

-M4

-M7



life.augmented

● Optimized for mixed-signal applications

● Cortex-M0+ Radio co-processor



# Releasing your creativity



[/STM32](#)



[@ST\\_World](#)



[community.st.com](#)



[www.st.com/STM32WB](#)



# Thank you

© STMicroelectronics - All rights reserved.

ST logo is a trademark or a registered trademark of STMicroelectronics International NV or its affiliates in the EU and/or other countries.

For additional information about ST trademarks, please refer to [www.st.com/trademarks](http://www.st.com/trademarks).

All other product or service names are the property of their respective owners.



life.augmented