
EVLVIPGAN65WP – 65W USB PD adaptor reference design with VIPERGAN65W

Introduction


This document describes the EVLVIPGAN65WP, a 65 W QR mode flyback adaptor reference design for USB Type-C™ PD adaptors with the following characteristics:

- 4-point average active mode efficiency: > 92%
- Input power consumption in no load condition: < 50 mW (@230 V_{AC})
- Compliant with IEC55022 Class B conducted EMI, even with reduced EMI filter
- RoHS compliant

The evaluation board has been developed using the VIPERGAN65W, a new advanced offline HV converter from STMicroelectronics, having the following features:

- 700 V power GaN with embedded senseFET (Si) and HV startup
- QR operation with dynamic blanking time and adjustable valley synchronization delay functions to maximize efficiency at any input line and load condition
- Valley-lock to ensure constant valley skipping
- Input voltage feedforward compensation for mains-independent OPP intervention
- Adaptive burst mode for advanced power management in light load conditions
- Frequency jittering for EMI suppression

Figure 2. EVLVIPGAN65WP reference design – bottom



2 Test board: design and evaluation

The electrical specifications of the evaluation board are listed in [Table 1](#) according to USB Power Delivery Specification Rev. 3.0.

Table 1. Electrical specifications

| Parameter | Min. | Typ. | Max. | Unit |
|---|--------|------|--------|-----------------|
| AC main input voltage | 90 | | 264 | V _{AC} |
| Main frequency (f _L) | 47 | | 63 | Hz |
| Standby input power – 5 V _{OUT} @230 V _{AC} | | | 50 | mW |
| Ambient operating temperature | | | 60 | °C |
| Output parameters – 5 V setting | | | | |
| Output voltage | 4.75 | 5 | 5.25 | V |
| Output current | 2.85 | 3 | 3.15 | A |
| Output parameters – 9 V setting | | | | |
| Output voltage | 8.55 | 9 | 9.45 | V |
| Output current | 2.85 | 3 | 3.15 | A |
| Output parameters – 12 V setting | | | | |
| Output voltage | 11.4 | 12 | 12.6 | V |
| Output current | 2.85 | 3 | 3.15 | A |
| Output parameters – 15 V setting | | | | |
| Output voltage | 14.25 | 15 | 15.75 | V |
| Output current | 2.85 | 3 | 3.15 | A |
| Output parameters – 20 V setting | | | | |
| Output voltage | 19 | 20 | 21 | V |
| Output current | 3.0875 | 3.25 | 3.4125 | A |

3 Schematic and bill of materials



Figure 3. Input board circuit schematic

Figure 4. Main board circuit schematic


Figure 5. Daughterboard circuit schematic




Table 2. Bill of materials of the reference design – input board

| Reference | Part/Value | Description | Manufacturer | Order code |
|-----------|---------------------|----------------------------|--------------------|---------------------|
| BR1 | 600V - 2A | Bridge rectifier | Comchip Technology | Z4DGP408L-HF |
| BR2 | 600V - 2A | Bridge rectifier | Comchip Technology | Z4DGP408L-HF |
| C1 | 47nF - 275Vac | Polypropylene X2 capacitor | Würth Elektronik | 890334023015 |
| C2 | 100nF ±10% - 450Vcc | MLCC capacitor | TDK | C3216X7T2W104K160AE |
| C23 | 100nF ±10% - 450Vcc | MLCC capacitor | TDK | C3216X7T2W104K160AE |
| C24 | 100nF ±10% - 450Vcc | MLCC capacitor | TDK | C3216X7T2W104K160AE |
| C25 | 100nF ±10% - 450Vcc | MLCC capacitor | TDK | C3216X7T2W104K160AE |
| C26 | 47nF - 275Vac | Polypropylene X2 capacitor | Würth Elektronik | 890334023015 |
| C38 | 100nF ±10% - 450Vcc | MLCC capacitor | TDK | C3216X7T2W104K160AE |
| C39 | 100nF ±10% - 450Vcc | MLCC capacitor | TDK | C3216X7T2W104K160AE |
| CM | 10mH - 1.2A | Common mode choke | Coilcraft | CJ5094-CL |
| F1 | 3A - 250Vac | FUSE | Littelfuse | 0443003.DR |
| L1 | 47uH | Power choke | Burns | SRN8040TA-470M |
| R1 | 4.7MΩ±5% - 0.25W | Resistor | Vishay Dale | CRCW12064M70JNEA |
| R2 | 4.7MΩ±5% - 0.25W | Resistor | Vishay Dale | CRCW12064M70JNEA |
| RV1 | 275Vac | Disk varistor | Würth Elektronik | 820572711 |

Table 3. Bill of materials of the reference design – main board

| Reference | Part/Value | Description | Manufacturer | Order code |
|-----------|---------------|------------------------|------------------|--------------------|
| C3 | 120uF - 400V | Electrolytic capacitor | Rubycon | 400HXW120MEFR16X30 |
| C4 | 470pF - 1000V | MLCC | Würth Elektronik | 885342208017 |

| Reference | Part/Value | Description | Manufacturer | Order code |
|-----------|--------------------------|-------------------------------------|---------------------|----------------------|
| C5 | 1uF - 50V | MLCC | TDK | CGA3E3X5R1H105K080AB |
| C6 | 10nF - 100V | MLCC | TDK | C1608X7R2A103K080AA |
| C7 | 22uF - 50V | Electrolytic capacitor | Rubycon | 860160672011 |
| C8 | 4.7uF - 100V | MLCC capacitor | TDK | CNC6P1X7R2A475K2 |
| C9 | 1uF - 100V | MLCC capacitor | TDK | C3216X7R2A105K160AA |
| C10 | 680uF - 25V | Conductive polymer hybrid ECAP | KEMET | EEH-AZS1E561B |
| C11 | 680uF - 25V | Conductive polymer hybrid ECAP | KEMET | EEH-AZS1E561B |
| C12 | 4.7uF - 50V | MLCC capacitor | Wurth Elektronik | 885012208094 |
| C14 | NC | | | |
| C15 | 4.7nF - 250Vac | Y1 safety ceramic disc capacitors | Murata | DE1E3RA472MA4BN1F |
| C16 | 100nF - 50V | MLCC capacitor | Wurth Elektronik | 885012206095 |
| C17 | NC | | | |
| C18 | 220nF - 450V | MLCC capacitor | TDK | C3225X7T2W224M200AE |
| C20 | 220pF - 100V | MLCC capacitor | Murata | GCM1885C2A221FA16D |
| C22 | 22nF - 100V | MLCC capacitor | KEMET | C0603C223K1RACTU |
| C40 | 4.7uF - 100V | MLCC capacitor | TDK | CNC6P1X7R2A475K2 |
| C41 | 100pF - 50V | MLCC capacitor | Wurth Elektronik | 710-885012006057 |
| C42 | 220nF - 450V | MLCC capacitor | TDK | C3225X7T2W224M200AE |
| D1 | 2A - 600V | Fast switching rectifier | STMicroelectronics | STTH2L06U |
| D2 | 1A - 200V | Small signal switching diode | SMC Diode Solutions | DSS120U |
| D3 | 100mA - 40V | Small signal Schottky diode | Rohm | RB510SM-40FHT2R |
| D8 | 1A - 200V | Small signal switching diode | SMC Diode Solutions | DSS120U |
| D9 | 250mA - 100V | Small signal switching diode | NXP | BAT46WH,115 |
| Dz1 | 18V - 500mW | Zener diode | Diodes | BZT52C18 |
| OPTO | 70V - 100mA | Optocoupler | Vishay | SFH6106-4T |
| Q1 | 100V - 12Ω | N-channel - Small signal MOSFET | Infineon | BSS169IXTSA1 |
| Q2 | 120V - 8mΩ - Logic Level | N-channel Power MOSFET | Infineon | BSC0302LS |
| Q5 | 100V - 12Ω | N-channel - Small signal MOSFET | Infineon | BSS169IXTSA1 |
| R3 | 270kΩ±1% - 0.5W - 400V | Anti-surge thick film chip resistor | Panasonic | ERJ-P06F2703V |
| R4 | 270kΩ±1% - 0.5W - 400V | Anti-surge thick film chip resistor | Panasonic | ERJ-P06F2703V |
| R5 | 18Ω±5% - 0.66W - 500V | Anti-surge thick film chip resistor | Panasonic | ERJP08J180V |

| Reference | Part/Value | Description | Manufacturer | Order code |
|-----------|------------------------|--|--------------------|-------------------|
| R6 | 10MΩ±5% - 0.25W - 800V | Thick film high voltage chip resistors | Burns | CHV1206-JW-106ELF |
| R7 | 680kΩ±1% - 0.25W | Thick film chip resistors | Panasonic | ERJ-UP3F6803V |
| R8 | 220kΩ±1% - 0.25W | Thick film chip resistors | Panasonic | ERJ-UP3F2203V |
| R9 | 4.3kΩ±1% - 0.25W | Thick film chip resistors | Panasonic | ERJ-UP3F4301V |
| R10 | 51kΩ±1% - 0.1W | Thick film chip resistors | Yageo | RT0603FRE1051KL |
| R11 | 75kΩ±1% - 0.25W | Thick film chip resistors | Yageo | RT0603FRE1075KL |
| R12 | 18kΩ±1% - 0.25W | Thick film chip resistors | Panasonic | 667-ERJ-UP3F1802V |
| R13 | 4.7kΩ±1% - 0.25W | Thick film chip resistors | Panasonic | ERJPA3F4701V |
| R15 | NC | | | |
| R16 | 0Ω | Thick film chip resistors | Panasonic | ERJ-H3G0R00V |
| R17 | 330Ω±1% - 0.25W | Thick film chip resistors | Panasonic | ERJ-UP3F3300V |
| R18 | 270kΩ±1% - 0.5W - 400V | Anti-surge thick film chip resistor | Panasonic | ERJ-P06F2703V |
| R19 | 68kΩ±1% - 0.25W | Thick film chip resistors | Panasonic | ERJ-UP3F6802V |
| R20 | 68kΩ±1% - 0.25W | Thick film chip resistors | Panasonic | ERJ-UP3F6802V |
| R21 | 1kΩ±1% - 0.25W | Thick film chip resistors | Panasonic | ERJ-UP3F1001V |
| R22 | 15kΩ±1% - 0.25W | Thick film chip resistors | Panasonic | ERJ-UP3F1502V |
| TF1 | 500uH | Flyback transformer | Würth Elektronik | 750320045 rev.02 |
| U1 | | HV converter | STMicroelectronics | VIPERGAN65W |
| U2 | | Synchronous rectification controller | STMicroelectronics | SRK1001 |

Table 4. Bill of materials of the reference design – daughterboard

| Reference | Part/Value | Description | Manufacturer | Order code |
|-----------|--------------|----------------|------------------|----------------------|
| C27 | 1uF - 50V | MLCC capacitor | Würth Elektronik | 885012207103 |
| C28 | 1uF - 50V | MLCC capacitor | Würth Elektronik | 885012207103 |
| C29 | 33nF - 50V | MLCC capacitor | Würth Elektronik | 885012206092 |
| C30 | 1uF - 100V | MLCC capacitor | TDK | C3216X7R2A105K160AA |
| C31 | 1uF - 100V | MLCC capacitor | TDK | C3216X7R2A105K160AA |
| C32 | 470nF - 100V | MLCC capacitor | AVX | 08051C474KAT2A |
| C33 | 2.2uF - 50V | MLCC capacitor | Murata | GRM188R61H225KE11D |
| C34 | 10uF - 50V | MLCC capacitor | Murata | 81-GRT31CR61H106KE1L |

| Reference | Part/Value | Description | Manufacturer | Order code |
|-----------|------------------|--|--------------------|----------------------|
| C35 | 1uF - 100V | MLCC capacitor | Murata | GCM21BC72A105KE36L |
| C43 | 100nF - 100V | MLCC capacitor | Murata | GCM21BR72A104KA7K |
| D6 | 1A - 800V | Fast switching rectifier | VISHAY | RS1K |
| D7 | 1.2V - 10mA | Dual TRANSIL array for ESD protection | STMicroelectronics | ESDA25LY |
| D10 | 250mA - 100V | Small signal switching diode | NXP | BAT46WH,115 |
| Jout | | Connector USB 3.1, type C, 90° | Molex | 201267-0005 |
| Q3 | 30V - 10m | P-channel Power MOSFET | Vishay | SISH101DN-T1-GE3 |
| Q4 | 30V - 10m | P-channel Power MOSFET | Vishay | SISH101DN-T1-GE3 |
| R23 | 10mΩ±1% - 0.75W | Metal foil low resistance chip resistors | Susumu | KRL1632E-C-R010-F-T1 |
| R24 | 100Ω±1% - 0.5W | Thick film chip resistors | Panasonic | ERJP06F1000V |
| R25 | 47kΩ±1% - 0.1W | Thick film chip resistors | Vishay | CRCW060347K0FKEA |
| R26 | 10kΩ±1% - 0.25W | Thick film chip resistors | Panasonic | ERJ-UP3F1002V |
| R27 | 510Ω±1% - 0.25W | Thick film chip resistors | Panasonic | ERJ-PA3F5100V |
| R28 | 100Ω±1% - 0.25W | Thick film chip resistors | Panasonic | ERJ-UP3F1000V |
| R29 | 4.7kΩ±1% - 0.1W | Thick film chip resistors | Panasonic | ERJ-3EKF4701V |
| R30 | 4.7kΩ±1% - 0.1W | Thick film chip resistors | Panasonic | ERJ-3EKF4701V |
| R31 | 4.7kΩ±1% - 0.1W | Thick film chip resistors | Panasonic | ERJ-3EKF4701V |
| R32 | 3kΩ±1% - 0.25W | Thick film chip resistors | Panasonic | ERJ-UP3F3001V |
| R33 | 2.7kΩ±1% - 0.1W | Thick film chip resistors | Panasonic | ERJ-3EKF2701V |
| R34 | NC | | | |
| RT2 | 47kΩ±5% - 0.125W | NTC thermistor | Vishay | NTCS0603E3473JHT |
| U3 | | Standalone USB PD controller | STMicroelectronics | STUSB4761QTR |
| U4 | 5V - 85mA | LDO regulator | STMicroelectronics | LDK715M50R |
| TRIM | 1uF - 50V | SMT vertical header | Würth Elektronik | 665104131822 |

The transformer characteristics are listed in the table below.

Table 5. Transformer characteristics

| Parameter | Value |
|---|------------------|
| Manufacturer | Würth Elektronik |
| Part number | 750320045 rev.02 |
| Primary inductance | 500µH ± 10% |
| Leakage inductance | 7.5µH max. |
| Primary (12 - 1) to Aux1 (10 - 2) turns ratio | 2.53 |
| Primary (12 - 1) to Aux2 (3 - 2) turns ratio | 3.43 |
| Primary (12 - 1) to Secondary (FL1 – FL2) turns ratio | 6 |

Another transformer version with extended rail (Würth Elektronik 750320431, www.we-online.com) is available for applications where customers prefer having a drop-in component with similar characteristics and performance.

Figure 6. Dimensional drawing and pin placement diagram – distances (bottom view)




Figure 7. Dimensional drawing and pin placement diagram – electrical diagram





Figure 8. Dimensional drawing and pin placement diagram – bottom, side, and top view


4 Efficiency measurements

The active mode efficiency is defined as the average of the efficiencies measured at 25%, 50%, 75%, and 100% of the rated output power, at nominal input voltages ($V_{IN} = 115 V_{AC}$ and $V_{IN} = 230 V_{AC}$).

External power supplies (the power supplies, which are contained in a separate housing from the end-use devices that they are powering) need to comply with the European Code of Conduct, version 5 “Active mode efficiency” criterion, which states that an SMPS with power throughput of 65 W should have an active mode efficiency higher than 89%.

Another standard to be applied is the DoE Level 6 Efficiency Standards recommendation, whose active mode efficiency requirement for the same power throughput is 88%.

Table 6 to Table 7 show the efficiency measurement results.

Table 6. Average efficiency at 115 V_{AC}

| Output load (%) | I _{OUT} (A) | V _{OUT} (V) | P _{IN} (W) | P _{OUT} (W) | Efficiency (%) |
|--------------------|----------------------|----------------------|---------------------|----------------------|----------------|
| 5 V output | | | | | |
| 25% | 0.750 | 5.010 | 4.154 | 3.758 | 90.47 |
| 50% | 1.501 | 5.003 | 8.248 | 7.510 | 91.05 |
| 75% | 2.252 | 4.995 | 12.403 | 11.249 | 90.70 |
| 100% | 3.008 | 4.988 | 16.738 | 15.004 | 89.64 |
| Average efficiency | | | | | 90.47 |
| 9 V output | | | | | |
| 25% | 0.750 | 9.031 | 7.406 | 6.773 | 91.45 |
| 50% | 1.499 | 9.022 | 14.632 | 13.524 | 92.43 |
| 75% | 2.247 | 9.014 | 21.926 | 20.254 | 92.37 |
| 100% | 3.000 | 9.007 | 29.451 | 27.021 | 91.75 |
| Average efficiency | | | | | 92.00 |
| 12 V output | | | | | |
| 25% | 0.750 | 12.044 | 9.840 | 9.033 | 91.80 |
| 50% | 1.498 | 12.034 | 19.460 | 18.027 | 92.64 |
| 75% | 2.246 | 12.026 | 29.157 | 27.010 | 92.64 |
| 100% | 2.995 | 12.021 | 39.089 | 36.003 | 92.11 |
| Average efficiency | | | | | 92.30 |
| 15 V output | | | | | |
| 25% | 0.747 | 15.059 | 12.275 | 11.249 | 91.64 |
| 50% | 1.496 | 15.047 | 24.307 | 22.510 | 92.61 |
| 75% | 2.244 | 15.043 | 36.423 | 33.756 | 92.68 |
| 100% | 2.992 | 15.037 | 48.829 | 44.991 | 92.14 |
| Average efficiency | | | | | 92.27 |
| 20 V output | | | | | |
| 25% | 0.810 | 20.075 | 17.746 | 16.261 | 91.63 |
| 50% | 1.622 | 20.064 | 35.113 | 32.544 | 92.68 |
| 75% | 2.433 | 20.060 | 52.780 | 48.806 | 92.47 |
| 100% | 3.243 | 20.053 | 70.901 | 65.032 | 91.72 |
| Average efficiency | | | | | 92.13 |

Table 7. Average efficiency at 230 V_{AC}


| Output load (%) | I _{OUT} (A) | V _{OUT} (V) | P _{IN} (W) | P _{OUT} (W) | Efficiency (%) |
|--------------------|----------------------|----------------------|---------------------|----------------------|----------------|
| 5 V output | | | | | |
| 25% | 0.747 | 5.015 | 4.287 | 3.746 | 87.38 |
| 50% | 1.501 | 5.006 | 8.522 | 7.514 | 88.17 |
| 75% | 2.251 | 4.999 | 12.688 | 11.253 | 88.69 |
| 100% | 3.008 | 4.989 | 16.834 | 15.007 | 89.15 |
| Average efficiency | | | | | 88.35 |
| 9 V output | | | | | |
| 25% | 0.750 | 9.035 | 7.699 | 6.776 | 88.01 |
| 50% | 1.498 | 9.027 | 14.949 | 13.522 | 90.45 |
| 75% | 2.246 | 9.017 | 22.212 | 20.252 | 91.18 |
| 100% | 3.000 | 9.007 | 29.416 | 27.021 | 91.86 |
| Average efficiency | | | | | 90.38 |
| 12 V output | | | | | |
| 25% | 0.747 | 12.049 | 10.116 | 9.001 | 88.98 |
| 50% | 1.496 | 12.043 | 19.954 | 18.016 | 90.29 |
| 75% | 2.247 | 12.032 | 29.401 | 27.036 | 91.96 |
| 100% | 2.995 | 12.021 | 38.890 | 36.003 | 92.58 |
| Average efficiency | | | | | 90.95 |
| 15 V output | | | | | |
| 25% | 0.750 | 15.062 | 12.572 | 11.297 | 89.86 |
| 50% | 1.495 | 15.053 | 24.588 | 22.504 | 91.52 |
| 75% | 2.246 | 15.043 | 36.509 | 33.787 | 92.54 |
| 100% | 2.995 | 15.033 | 48.385 | 45.024 | 93.05 |
| Average efficiency | | | | | 91.74 |
| 20 V output | | | | | |
| 25% | 0.811 | 20.082 | 18.177 | 16.287 | 89.60 |
| 50% | 1.620 | 20.073 | 35.241 | 32.518 | 92.27 |
| 75% | 2.434 | 20.060 | 52.464 | 48.826 | 93.07 |
| 100% | 3.244 | 20.050 | 69.649 | 65.042 | 93.39 |
| Average efficiency | | | | | 92.08 |

Table 8 shows the efficiency measured at 10% of the rated output power.

Table 8. Average efficiency at 10% of the max. output load

| V _{IN} [V _{AC}] | I _{OUT} (A) | V _{OUT} (V) | P _{IN} (W) | P _{OUT} (W) | Efficiency (%) |
|------------------------------------|----------------------|----------------------|---------------------|----------------------|----------------|
| 5 V output | | | | | |
| 115 | 0.300 | 5.015 | 1.709 | 1.505 | 88.06 |
| 230 | 0.300 | 5.017 | 1.768 | 1.505 | 85.12 |
| 9 V output | | | | | |
| 115 | 0.302 | 9.035 | 3.029 | 2.729 | 90.10 |

| V_{IN} [V _{AC}] | I_{OUT} (A) | V_{OUT} (V) | P_{IN} (W) | P_{OUT} (W) | Efficiency (%) |
|-----------------------------|---------------|---------------|--------------|---------------|----------------|
| 230 | 0.300 | 9.035 | 3.131 | 2.711 | 86.59 |
| 12 V output | | | | | |
| 115 | 0.300 | 12.050 | 3.998 | 3.615 | 90.42 |
| 230 | 0.300 | 12.053 | 4.164 | 3.616 | 86.84 |
| 15 V output | | | | | |
| 115 | 0.300 | 15.065 | 5.031 | 4.520 | 89.84 |
| 230 | 0.299 | 15.066 | 5.204 | 4.505 | 86.57 |
| 20 V output | | | | | |
| 115 | 0.326 | 20.084 | 7.407 | 6.547 | 88.39 |
| 230 | 0.326 | 20.088 | 7.644 | 6.549 | 85.68 |



4.1 No load consumptions

The input power of the converter has been measured in no load; in this condition, the converter works in burst mode so that the average switching frequency is reduced, thus minimizing the frequency related losses. The no load condition is realized with nothing connected to the USB Type-C® port, which opens the by-pass MOSFETs Q3 and Q4 in the daughterboard and sets the output voltage of the converter to 5 V.

Table 9. No load consumptions

| V_{IN} [V _{AC}] | P_{IN} (mW) |
|-----------------------------|---------------|
| 5 V output | |
| 115 | 27.10 |
| 230 | 46.14 |

5 Typical waveforms

The following figures show the GaN (primary side) and SR MOSFET (secondary side) drain to source voltage for minimum and maximum AC input voltage at maximum output power.

Figure 11. VIPerGaN and SR MOSFET V_{DS} at 90 V_{AC} (20 V – 3.25 A)





Figure 12. VIPerGaN and SR MOSFET V_{DS} at 265 V_{AC} (20 V – 3.25 A)



The output voltage ripple has been measured at different output voltages with two different loads (0 A and maximum available current). Tests have been performed at the nominal input voltages (115 V_{AC} and 230 V_{AC}).

Figure 13. Ripple at 115 V_{AC}, 5 V – 0 A




Figure 14. Ripple at 230 V_{AC}, 5 V – 0 A




Figure 15. Ripple at 115 V_{AC}, 5 V – 3 A




Figure 16. Ripple at 230 V_{AC}, 5 V – 3 A




Figure 17. Ripple at 115 V_{AC}, 9 V – 0 A




Figure 18. Ripple at 230 V_{AC}, 9 V – 0 A




Figure 19. Ripple at 115 V_{AC}, 9 V – 3 A




Figure 20. Ripple at 230 V_{AC}, 9 V – 3 A




Figure 21. Ripple at 115 V_{AC}, 12 V – 0 A




Figure 22. Ripple at 230 V_{AC}, 12 V – 0 A




Figure 23. Ripple at 115 V_{AC}, 12 V – 3 A




Figure 24. Ripple at 230 V_{AC}, 12 V – 3 A




Figure 25. Ripple at 115 V_{AC}, 15 V – 0 A




Figure 26. Ripple at 230 V_{AC}, 15 V – 0 A




Figure 27. Ripple at 115 V_{AC}, 15 V – 3 A







Figure 28. Ripple at 230 V_{AC}, 15 V – 3 A




Table 10. Output voltage ripple test results

| V _{IN} [V _{AC}] | V _{OUT} (V) | I _{OUT} (A) | Ripple (mV) | Max. ripple (mV) as per USB PD Specification Rev. 3.0 |
|------------------------------------|----------------------|----------------------|-------------|---|
| 115 V _{AC} | 5 | 0 | ± 89.69 | ± 250 |
| | 5 | 3 | ± 68.72 | ± 250 |
| | 9 | 0 | ± 71.65 | ± 450 |
| | 9 | 3 | ± 59.20 | ± 450 |
| | 12 | 0 | ± 56.06 | ± 600 |
| | 12 | 3 | ± 62.62 | ± 600 |
| | 15 | 0 | ± 63.12 | ± 750 |
| | 15 | 3 | ± 75.94 | ± 750 |
| | 20 | 0 | ± 60.70 | ± 1000 |

| V_{IN} [V_{AC}] | V_{OUT} (V) | I_{OUT} (A) | Ripple (mV) | Max. ripple (mV) as per USB PD Specification Rev. 3.0 |
|-----------------------|---------------|---------------|-------------|---|
| 115 V_{AC} | 20 | 3.25 | ± 107.6 | ± 1000 |
| 230 V_{AC} | 5 | 0 | ± 86.76 | ± 250 |
| | 5 | 3 | ± 63.95 | ± 250 |
| | 9 | 0 | ± 67.68 | ± 450 |
| | 9 | 3 | ± 53.58 | ± 450 |
| | 12 | 0 | ± 56.13 | ± 600 |
| | 12 | 3 | ± 54.94 | ± 600 |
| | 15 | 0 | ± 60.78 | ± 750 |
| | 15 | 3 | ± 64.22 | ± 750 |
| | 20 | 0 | ± 67.03 | ± 1000 |
| | 20 | 3.25 | ± 80.16 | ± 1000 |

5.1 Dynamic step load regulation

The following figures show the load transient response when the converter is subjected to repetitive dynamic load transitions from zero to full load at 115 V_{AC} and 230 V_{AC} .

The transition period is 200 ms with a 50% duty cycle and slew rate of 150 mA/ μ s.

There are no abnormal oscillations in the output voltage and the overshoot and undershoot are within the limits defined by the specification.

Figure 33. Dynamic step load ($V_{OUT} = 5$ V, I_{OUT} from 0 to 3 A) at 115 V_{AC}



Figure 34. Dynamic step load ($V_{OUT} = 5$ V, I_{OUT} from 0 to 3 A) at 230 V_{AC}




Figure 35. Dynamic step load ($V_{OUT} = 9$ V, I_{OUT} from 0 to 3 A) at 115 V_{AC}



Figure 36. Dynamic step load ($V_{OUT} = 9$ V, I_{OUT} from 0 to 3 A) at 230 V_{AC}



Figure 37. Dynamic step load ($V_{OUT} = 12\text{ V}$, I_{OUT} from 0 to 3 A) at 115 V_{AC}


Figure 38. Dynamic step load ($V_{OUT} = 12\text{ V}$, I_{OUT} from 0 to 3 A) at 230 V_{AC}

Figure 39. Dynamic step load ($V_{OUT} = 15\text{ V}$, I_{OUT} from 0 to 3 A) at 115 V_{AC}




Figure 40. Dynamic step load ($V_{OUT} = 15\text{ V}$, I_{OUT} from 0 to 3 A) at 230 V_{AC}

Figure 41. Dynamic step load ($V_{OUT} = 20\text{ V}$, I_{OUT} from 0 to 3.25 A) at 115 V_{AC}

Figure 42. Dynamic step load ($V_{OUT} = 20\text{ V}$, I_{OUT} from 0 to 3.25 A) at 230 V_{AC}


6 Conducted noise measurements

The VIPERGAN65 frequency jittering feature allows the spectrum to be spread over frequency bands rather than being concentrated on a single frequency value. Especially when measuring conducted emission with the average detection method, the level reduction can be several dB μ V.

A pre-compliance test for the EN55022 (Class B) European normative was performed and average measurements of the conducted noise emissions, at nominal mains voltages and with output set to 20 V and maximum load (3.25 A), are shown in the following figures.



7 Thermal measurements

A thermal analysis of the board has been performed using an IR image sensor. The test was performed with the output voltage set to 20 V under full load condition for the two nominal input voltages (115 V_{AC} and 230 V_{AC}). The results are shown below.





Table 11. Temperature of key components (T_{AMB} = 25 °C, emissivity = 0.95 for all points)

| Point | Temp (°C) | | Reference |
|------------|---------------------|---------------------|-------------------|
| | 115 V _{AC} | 230 V _{AC} | |
| Bottom - 1 | 103 | 102 | Snubber resistors |
| Bottom - 2 | 79.5 | 77.9 | VIPerGaN65W |
| Bottom - 3 | 72.6 | 75.1 | SR MOSFET |
| Top - 1 | 79.4 | 57 | Bridge diode |
| Top - 2 | 91.2 | 63.4 | Choke |
| Top - 3 | 89 | 91.6 | Transformer |

8 Conclusions

The test results shown demonstrate the good performances achieved by the EVLVIPGAN65WP.

The reference design shows peak efficiency > 93%. It also meets EU CoC Tier 2 and DoE Level 6 efficiency requirements for average efficiency. The quasi-resonant topology helps to minimize the switching losses. The low quiescent current consumption makes it best-in-class no load consumption.

The VIPERGAN65W is an offline quasi-resonant (valley switching at switch turn-on) flyback converter. Depending on the converter's load condition, the device is able to work in different modes. Based on the quasi-resonant, the primary switching losses are minimized. The secondary losses are minimized by using the highly efficient and optimized synchronous rectification controller.

Users no longer need to take care of GaN driving complexity to enjoy the benefits of GaN technology thanks to the highly integrated VIPERGAN65W IC, enhancing the robustness of the application.

Revision history

Table 12. Document revision history

| Date | Version | Changes |
|-------------|---------|------------------|
| 06-Mar-2026 | 1 | Initial release. |

Contents

| | | |
|------------|--|-----------|
| 1 | Overview | 2 |
| 2 | Test board: design and evaluation | 4 |
| 3 | Schematic and bill of materials | 5 |
| 4 | Efficiency measurements | 12 |
| 4.1 | No load consumptions | 14 |
| 5 | Typical waveforms | 15 |
| 5.1 | Dynamic step load regulation | 21 |
| 6 | Conducted noise measurements | 23 |
| 7 | Thermal measurements | 24 |
| 8 | Conclusions | 25 |
| | Revision history | 26 |
| | List of tables | 28 |
| | List of figures | 29 |

List of tables

| | | |
|------------------|---|----|
| Table 1. | Electrical specifications. | 4 |
| Table 2. | Bill of materials of the reference design – input board | 6 |
| Table 3. | Bill of materials of the reference design – main board | 6 |
| Table 4. | Bill of materials of the reference design – daughterboard | 8 |
| Table 5. | Transformer characteristics | 10 |
| Table 6. | Average efficiency at 115 V _{AC} | 12 |
| Table 7. | Average efficiency at 230 V _{AC} | 13 |
| Table 8. | Average efficiency at 10% of the max. output load | 13 |
| Table 9. | No load consumptions | 14 |
| Table 10. | Output voltage ripple test results | 20 |
| Table 11. | Temperature of key components (T _{AMB} = 25 °C, emissivity = 0.95 for all points). | 24 |
| Table 12. | Document revision history | 26 |

List of figures

| | | |
|-------------------|---|----|
| Figure 1. | EVLVIPGAN65WP reference design – top | 2 |
| Figure 2. | EVLVIPGAN65WP reference design – bottom | 3 |
| Figure 3. | Input board circuit schematic | 5 |
| Figure 4. | Main board circuit schematic | 5 |
| Figure 5. | Daughterboard circuit schematic | 6 |
| Figure 6. | Dimensional drawing and pin placement diagram – distances (bottom view) | 10 |
| Figure 7. | Dimensional drawing and pin placement diagram – electrical diagram | 10 |
| Figure 8. | Dimensional drawing and pin placement diagram – bottom, side, and top view | 11 |
| Figure 9. | Efficiency at 115 V _{AC} | 14 |
| Figure 10. | Efficiency at 230 V _{AC} | 14 |
| Figure 11. | VIPerGaN and SR MOSFET V _{DS} at 90 V _{AC} (20 V – 3.25 A) | 15 |
| Figure 12. | VIPerGaN and SR MOSFET V _{DS} at 265 V _{AC} (20 V – 3.25 A) | 15 |
| Figure 13. | Ripple at 115 V _{AC} , 5 V – 0 A | 16 |
| Figure 14. | Ripple at 230 V _{AC} , 5 V – 0 A | 16 |
| Figure 15. | Ripple at 115 V _{AC} , 5 V – 3 A | 16 |
| Figure 16. | Ripple at 230 V _{AC} , 5 V – 3 A | 16 |
| Figure 17. | Ripple at 115 V _{AC} , 9 V – 0 A | 17 |
| Figure 18. | Ripple at 230 V _{AC} , 9 V – 0 A | 17 |
| Figure 19. | Ripple at 115 V _{AC} , 9 V – 3 A | 17 |
| Figure 20. | Ripple at 230 V _{AC} , 9 V – 3 A | 17 |
| Figure 21. | Ripple at 115 V _{AC} , 12 V – 0 A | 18 |
| Figure 22. | Ripple at 230 V _{AC} , 12 V – 0 A | 18 |
| Figure 23. | Ripple at 115 V _{AC} , 12 V – 3 A | 18 |
| Figure 24. | Ripple at 230 V _{AC} , 12 V – 3 A | 18 |
| Figure 25. | Ripple at 115 V _{AC} , 15 V – 0 A | 19 |
| Figure 26. | Ripple at 230 V _{AC} , 15 V – 0 A | 19 |
| Figure 27. | Ripple at 115 V _{AC} , 15 V – 3 A | 19 |
| Figure 28. | Ripple at 230 V _{AC} , 15 V – 3 A | 19 |
| Figure 29. | Ripple at 115 V _{AC} , 20 V – 0 A | 20 |
| Figure 30. | Ripple at 230 V _{AC} , 20 V – 0 A | 20 |
| Figure 31. | Ripple at 115 V _{AC} , 20 V – 3.25 A | 20 |
| Figure 32. | Ripple at 230 V _{AC} , 20 V – 3.25 A | 20 |
| Figure 33. | Dynamic step load (V _{OUT} = 5 V, I _{OUT} from 0 to 3 A) at 115 V _{AC} | 21 |
| Figure 34. | Dynamic step load (V _{OUT} = 5 V, I _{OUT} from 0 to 3 A) at 230 V _{AC} | 21 |
| Figure 35. | Dynamic step load (V _{OUT} = 9 V, I _{OUT} from 0 to 3 A) at 115 V _{AC} | 21 |
| Figure 36. | Dynamic step load (V _{OUT} = 9 V, I _{OUT} from 0 to 3 A) at 230 V _{AC} | 21 |
| Figure 37. | Dynamic step load (V _{OUT} = 12 V, I _{OUT} from 0 to 3 A) at 115 V _{AC} | 22 |
| Figure 38. | Dynamic step load (V _{OUT} = 12 V, I _{OUT} from 0 to 3 A) at 230 V _{AC} | 22 |
| Figure 39. | Dynamic step load (V _{OUT} = 15 V, I _{OUT} from 0 to 3 A) at 115 V _{AC} | 22 |
| Figure 40. | Dynamic step load (V _{OUT} = 15 V, I _{OUT} from 0 to 3 A) at 230 V _{AC} | 22 |
| Figure 41. | Dynamic step load (V _{OUT} = 20 V, I _{OUT} from 0 to 3.25 A) at 115 V _{AC} | 22 |
| Figure 42. | Dynamic step load (V _{OUT} = 20 V, I _{OUT} from 0 to 3.25 A) at 230 V _{AC} | 22 |
| Figure 43. | CE average measurement at 115 V _{AC} (V _{OUT} = 20 V, I _{OUT} = 3.25 A) | 23 |
| Figure 44. | CE average measurement at 230 V _{AC} (V _{OUT} = 20 V, I _{OUT} = 3.25 A) | 23 |
| Figure 45. | Thermal map at 115 V _{AC} (20 V – 3.25 A). Bottom layer | 24 |
| Figure 46. | Thermal map at 115 V _{AC} (20 V – 3.25 A). Top layer | 24 |
| Figure 47. | Thermal map at 230 V _{AC} (20 V – 3.25 A). Bottom layer | 24 |
| Figure 48. | Thermal map at 230 V _{AC} (20 V – 3.25 A). Top layer | 24 |

IMPORTANT NOTICE – READ CAREFULLY

STMicroelectronics NV and its subsidiaries (“ST”) reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice.

In the event of any conflict between the provisions of this document and the provisions of any contractual arrangement in force between the purchasers and ST, the provisions of such contractual arrangement shall prevail.

The purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST’s terms and conditions of sale in place at the time of order acknowledgment.

The purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of the purchasers’ products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

If the purchasers identify an ST product that meets their functional and performance requirements but that is not designated for the purchasers’ market segment, the purchasers shall contact ST for more information.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2026 STMicroelectronics – All rights reserved