



## Rad-Hard 50 V, 0.8 A NPN transistor



LCC-3

UB

Pin 4 in UB is connected to the metallic lid.



DS10450



Product status link

[2N2222AHR](#)

## Features

$V_{ce0}$	$I_C(\text{max.})$	$H_{FE}$ at 10 V, 150 mA	$T_j(\text{max.})$
50 V	0.8 A	> 100	200 °C

- Hermetic packages
- ESCC and JANS qualified
- Up to 100 krad(Si) low dose rate

## Description

The 2N2222AHR is a silicon planar NPN transistor specifically designed and housed in hermetic packages for aerospace and Hi-Rel applications. It is available in the JAN qualification system (MIL-PRF19500 compliance) and in the ESCC qualification system (ESCC 5000 compliance). In case of discrepancies between this datasheet and the relevant agency specification, the latter takes precedence.

## Product summary

Product summary				
Device	Qualification system	Agency specification	Package	Radiation level
JANSR2N2222AUBx	JANSR	MIL-PRF-19500/255	UB	100 krad
JANS2N2222AUBx	JANS	MIL-PRF-19500/255	UB	-
2N2222ARUBx	ESCC Flight	5201/002	UB	100 krad
2N2222AUBx	ESCC Flight	5201/002	UB	-
SOC2222ARHRx	ESCC Flight	5201/002	LCC-3	100 krad
SOC2222AHRx	ESCC Flight	5201/002	LCC-3	-

# 1 Electrical ratings

**Table 1. Absolute maximum ratings**

Symbol	Parameter		Value	Unit
$V_{CBO}$	Collector-base voltage ( $I_E = 0$ )		75	V
$V_{CEO}$	Collector-emitter voltage ( $I_B = 0$ )		50	V
$V_{EBO}$	Emitter-base voltage ( $I_C = 0$ )		6	V
$I_C$	Collector current		0.8	A
$P_{TOT}$	Total dissipation at $T_{amb} \leq 25\text{ °C}$	ESCC	0.5	W
		LCC-3 and UB		
		LCC-3 and UB <sup>(1)</sup>	0.73	
	JANS: UB	0.5		
Total dissipation at $T_{SP(IS)} = 25\text{ °C}$	JANS: UB	1	W	
	Storage temperature range		-65 to 200	°C
$T_J$	Max. operating junction temperature		200	°C

1. When mounted on a 15 x 15 x 0.6 mm ceramic substrate.

**Table 2. Thermal data**

Symbol	Parameter	LCC-3 and UB Value	Unit
$R_{thJSP(IS)}$	Thermal resistance junction-solder pad (infinite sink) (max) for JANS	90	°C/W
$R_{thJA}$	Thermal resistance junction-ambient (max) for JANS	325	
	Thermal resistance junction-ambient (max) for ESCC	350 240 <sup>(1)</sup>	

1. When mounted on a 15 x 15 x 0.6 mm ceramic substrate.

## 2 Electrical characteristics

JANS and ESCC version of the products are assembled and tested in compliance with the agency specification. The electrical characteristics of each version are provided in dedicated tables.

### 2.1 JANS electrical characteristics

**Table 3. Electrical characteristics ( $T_{amb} = 25\text{ °C}$  unless otherwise specified)**

Symbol	Parameter	Test conditions	Min.	Max.	Unit
$I_{CBO}$	Collector-base cut-off current ( $I_E = 0$ )	$V_{CB} = 75\text{ V}$		10	$\mu\text{A}$
		$V_{CB} = 60\text{ V}$		10	nA
		$V_{CB} = 60\text{ V}, T_{amb} = 150\text{ °C}$		10	$\mu\text{A}$
$I_{CES}$	Collector-base cut-off current ( $I_E = 0$ )	$V_{CE} = 50\text{ V}$		50	nA
$I_{EBO}$	Emitter-base cut-off current ( $I_C = 0$ )	$V_{EB} = 6\text{ V}$		10	$\mu\text{A}$
		$V_{EB} = 4\text{ V}$		10	nA
$V_{(BR)CEO}^{(1)}$	Collector-emitter breakdown voltage ( $I_B = 0$ )	$I_C = 10\text{ mA}$	50		V
$V_{CE(sat)}^{(1)}$	Collector-emitter saturation voltage	$I_C = 150\text{ mA}, I_B = 15\text{ mA}$		0.3	V
		$I_C = 500\text{ mA}, I_B = 50\text{ mA}$		1	V
$V_{BE(sat)}^{(1)}$	Base-emitter saturation voltage	$I_C = 150\text{ mA}, I_B = 15\text{ mA}$	0.6	1.2	V
		$I_C = 500\text{ mA}, I_B = 50\text{ mA}$		2	V
$h_{FE}^{(1)}$	DC current gain	$I_C = 0.1\text{ mA}, V_{CE} = 10\text{ V}$	50		
		$I_C = 1\text{ mA}, V_{CE} = 10\text{ V}$	75	325	
		$I_C = 10\text{ mA}, V_{CE} = 10\text{ V}$	100		
		$I_C = 150\text{ mA}, V_{CE} = 10\text{ V}$	100	300	
		$I_C = 500\text{ mA}, V_{CE} = 10\text{ V}$	30		
		$I_C = 10\text{ mA}, T_{amb} = -55\text{ °C}, V_{CE} = 10\text{ V}$	35		
$h_{fe}$	Small signal current gain	$I_C = 20\text{ mA}, f = 100\text{ MHz}, V_{CE} = 20\text{ V}$	2.5		
		$I_C = 1\text{ mA}, f = 1\text{ kHz}, V_{CE} = 10\text{ V}$	50		
$C_{OBO}$	Output capacitance, ( $I_E = 0$ )	$100\text{ kHz} \leq f \leq 1\text{ MHz}, V_{CB} = 10\text{ V}$		8	pF
$C_{IBO}$	Input capacitance, ( $I_C = 0$ )	$100\text{ kHz} \leq f \leq 1\text{ MHz}, V_{EB} = 0.5\text{ V}$		25	pF
$t_{on}$	Turn-on time	$I_{CC} = 150\text{ mA}, I_{B1} = 15\text{ mA}, V_{CC} = 30\text{ V}$		35	ns
$t_{off}$	Turn-off time	$I_{CC} = 150\text{ mA}, I_{B1} = I_{B2} = 15\text{ mA}, V_{CC} = 30\text{ V}$		300	ns

1. Pulsed duration = 300  $\mu\text{s}$ , duty cycle  $\leq 1.5\%$

## 2.2 ESCC electrical characteristics

**Table 4. Electrical characteristics ( $T_{amb} = 25\text{ °C}$  unless otherwise specified)**

Symbol	Parameter	Test conditions	Min.	Max.	Unit
$I_{CBO}$	Collector-base cut-off current ( $I_E = 0$ )	$V_{CB} = 60\text{ V}$		10	nA
		$V_{CB} = 60\text{ V}, T_{amb} = 150\text{ °C}$		10	$\mu\text{A}$
$I_{EBO}$	Emitter-base cut-off current ( $I_C = 0$ )	$V_{EB} = 3\text{ V}$		10	nA
$V_{(BR)CBO}$	Collector-base breakdown voltage ( $I_E = 0$ )	$I_C = 100\text{ }\mu\text{A}$	75		V
$V_{(BR)CEO}^{(1)}$	Collector-emitter breakdown voltage ( $I_B = 0$ )	$I_C = 10\text{ mA}$	50		V
$V_{(BR)EBO}$	Emitter-base breakdown voltage ( $I_C = 0$ )	$I_C = 100\text{ }\mu\text{A}$	6		V
$V_{CE(sat)}^{(1)}$	Collector-emitter saturation voltage	$I_C = 150\text{ mA}, I_B = 15\text{ mA}$		0.3	V
$V_{BE(sat)}^{(1)}$	Base-emitter saturation voltage	$I_C = 150\text{ mA}, I_B = 15\text{ mA}$		1.2	V
$h_{FE}^{(1)}$	DC current gain	$I_C = 0.1\text{ mA}, V_{CE} = 10\text{ V}$	35		
		$I_C = 10\text{ mA}, V_{CE} = 10\text{ V}$	75		
		$I_C = 150\text{ mA}, V_{CE} = 10\text{ V}$	100	300	
		$I_C = 500\text{ mA}, V_{CE} = 10\text{ V}$	40		
		$I_C = 10\text{ mA}, T_{amb} = -55\text{ °C}, V_{CE} = 10\text{ V}$	35		
$h_{fe}$	Small signal current gain	$I_C = 20\text{ mA}, f = 100\text{ MHz}, V_{CE} = 20\text{ V}$	2.5		
$C_{OBO}$	Output capacitance ( $I_E = 0$ )	$100\text{ kHz} \leq f \leq 1\text{ MHz}, V_{CB} = 10\text{ V}$		8	pF
$t_{on}$	Turn-on time	$I_{CC} = 150\text{ mA},$ $I_{B1} = 15\text{ mA},$ $V_{CC} = 30\text{ V}$		35	ns
$t_{off}$	Turn-off time	$I_{CC} = 150\text{ mA},$ $I_{B1} = I_{B2} = 15\text{ mA},$ $V_{CC} = 30\text{ V}$		285	ns

1. Pulsed duration = 300  $\mu\text{s}$ , duty cycle  $\leq 1.5\%$

### 2.3 Electrical characteristics (curves)

Figure 1. DC current gain




Figure 2. Collector emitter saturation voltage






Figure 3. Base emitter saturation voltage



## 2.4 Test circuits


Figure 4. JANS saturated turn-on switching time test circuit



Note: (1) The rise time ( $t_r$ ) of the applied pulse should be  $\leq 2.0$  ns, duty cycle  $\leq 2$  percent, and the generator source impedance shall be  $50 \Omega$ .

Note: (2) Sampling oscilloscope:  $Z_{IN} \geq 100$  k $\Omega$ ,  $C_{IN} \leq 12$  pF, rise time  $\leq 5$  ns.

Figure 5. JANS saturated turn-off switching time test circuit




Note: (1) The rise time ( $t_r$ ) of the applied pulse should be  $\leq 2.0$  ns, duty cycle  $\leq 2$  percent, and the generator source impedance shall be  $50 \Omega$ .

Note: (2) Sampling oscilloscope:  $Z_{IN} \geq 100$  k $\Omega$ ,  $C_{IN} \leq 12$  pF, rise time  $\leq 5$  ns.

Note: (3) Alternate test point for high impedance attenuating probe.

Figure 6. ESCC resistive load switching test circuit



Note: (1) Fast electronic switch

Note: (2) Non-inductive resistor

### 3 Radiation hardness assurance

#### 3.1 JANS radiation assurance

JANSR2N2222A is guaranteed at 100 krad in compliance with the MIL-PRF-19500, Group D between 50 and 300 rad/s with an additional guarantee at 0.1 rad/s as per ESCC 22900.

Radiation verification test report is provided with each shipment.

**Table 5. MIL-PRF-19500 post radiation electrical characteristics ( $T_{amb} = 25\text{ }^{\circ}\text{C}$  unless otherwise specified)**

Symbol	Parameter	Test conditions	Min.	Max	Unit
$I_{CBO}$	Collector cut-off current ( $I_E = 0$ )	$V_{CB} = 75\text{ V}$		20	$\mu\text{A}$
		$V_{CB} = 60\text{ V}$		20	nA
$I_{EBO}$	Emitter cut-off current ( $I_C = 0$ )	$V_{EB} = 6\text{ V}$		20	$\mu\text{A}$
		$V_{EB} = 4\text{ V}$		20	$\mu\text{A}$
$V_{(BR)CEO}^{(1)}$	Collector-emitter breakdown voltage ( $I_B = 0$ )	$I_C = 10\text{ mA}$	50		V
$I_{CES}$	Collector to emitter cut-off current	$V_{CE} = 50\text{ V}$		100	nA
$V_{CE(sat)}$	Collector-emitter saturation voltage	$I_C = 150\text{ mA}, I_B = 15\text{ mA}$		0.35	V
		$I_C = 500\text{ mA}, I_B = 50\text{ mA}$		1.15	
$V_{BE(sat)}$	Base-emitter saturation voltage	$I_C = 150\text{ mA}, I_B = 15\text{ mA}$	0.6	1.38	V
		$I_C = 500\text{ mA}, I_B = 50\text{ mA}$		2.3	
$[h_{FE}]$	Post irradiation gain calculation	$I_C = 0.1\text{ mA}, V_{CE} = 10\text{ V}$	[25] <sup>(2)</sup>		
		$I_C = 1.0\text{ mA}, V_{CE} = 10\text{ V}$	[37.5] <sup>(2)</sup>	325	
		$I_C = 10\text{ mA}, V_{CE} = 10\text{ V}$	[50] <sup>(2)</sup>		
		$I_C = 150\text{ mA}, V_{CE} = 10\text{ V}$	[50] <sup>(2)</sup>	300	
		$I_C = 500\text{ mA}, V_{CE} = 10\text{ V}$	[15] <sup>(2)</sup>		

1. Pulsed duration = 300  $\mu\text{s}$ , duty cycle  $\geq 2\%$

2. See method 1019 of MIL-STD-750 for how to determine  $[h_{FE}]$  by first calculating the delta ( $1/h_{FE}$ ) from the pre- and Post-radiation  $h_{FE}$ . Notice the  $[h_{FE}]$  is not the same as  $h_{FE}$  and cannot be measured directly. The  $[h_{FE}]$  value can never exceed the pre-radiation minimum  $h_{FE}$  that it is based upon.

### 3.2 ESCC radiation assurance

This products is guaranteed in radiation as per ESCC 22900 and in compliance with ESCC 5201/002 specification.

Each lot is tested in radiation according to the following procedure:

- Radiation condition of 0.1 rad (Si)/s.
- Test of 11 samples by wafer, 5 biased at 80% of V(BR)CEO, 5 unbiased and for reference.
- Acceptance criteria of each wafer at 100 krad if all 10 samples comply with the post radiation electrical characteristics as per table 7.
- Radiation verification test (RVT) report is delivered with the lot manufactured with the wafer of the tested samples.

RVT includes the value of each parameter at 30, 50, 70 and 100 krad (Si), post annealing at 24 hour / 25 °C and and post annealing at 168 hours / 100°C.

**Table 6. ESCC 5201/002 post radiation electrical characteristics (T<sub>amb</sub> = 25 °C unless otherwise specified)**

Symbol	Parameter	Test conditions	Min.	Max	Unit
I <sub>CBO</sub>	Collector cut-off current (I <sub>E</sub> = 0)	V <sub>CB</sub> = 60 V		10	nA
I <sub>EBO</sub>	Emitter cut-off current (I <sub>C</sub> = 0)	V <sub>EB</sub> = 3 V		10	nA
V <sub>(BR)CBO</sub>	Collector-base breakdown voltage (I <sub>E</sub> = 0)	I <sub>C</sub> = 100 µA	75		V
V <sub>(BR)CEO</sub> <sup>(1)</sup>	Collector-emitter breakdown voltage (I <sub>B</sub> = 0)	I <sub>C</sub> = 10 mA	50		V
V <sub>(BR)EBO</sub>	Emitter-base breakdown voltage (I <sub>C</sub> = 0)	I <sub>E</sub> = 100 µA	6		V
V <sub>CE(sat)</sub> <sup>(1)</sup>	Collector-emitter saturation voltage	I <sub>C</sub> = 150 mA, I <sub>B</sub> = 15 mA		0.3	V
V <sub>BE(sat)</sub> <sup>(1)</sup>	Base-emitter saturation voltage	I <sub>C</sub> = 150 mA, I <sub>B</sub> = 15 mA		1.2	V
[h <sub>FE</sub> ] <sup>(1)</sup>	Post irradiation gain calculation <sup>(2)</sup>	I <sub>C</sub> = 0.1 mA, V <sub>CE</sub> = 10 V	[17.5]		
		I <sub>C</sub> = 10 mA, V <sub>CE</sub> = 10 V	[37.5]		
		I <sub>C</sub> = 150 mA, V <sub>CE</sub> = 10 V	[50]	300	
		I <sub>C</sub> = 500 mA, V <sub>CE</sub> = 10 V	[20]		

1. Pulsed duration = 300 µs, duty cycle ≥ 2 %

2. The post-irradiation gain calculation of [h<sub>FE</sub>], made using h<sub>FE</sub> measurements from prior to and on completion of irradiation testing and after each annealing step if any, shall be as specified in MILSTD-750 method 1019.

**Table 7. Radiation summary**

Radiation test	100 krad ESCC
Wafer test	Each
Part tested	5 biased + 5 unbiased
Dose rate	0.1 rad/s
Acceptance	ESCC 22900 and ESCC 5201/002
Displacement damage	Optional
Agency part number (ex)	5201/002/04R <sup>(1)</sup>
ST part number (ex)	SOC2222ARHRG
Documents	CoC + RVT

1. Example of the 2N2222A in LCC-3 gold finish.




## 4 Package information

In order to meet environmental requirements, ST offers these devices in different grades of **ECOPACK** packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: [www.st.com](http://www.st.com). ECOPACK is an ST trademark.

### 4.1 UB package information

Figure 7. UB package outline



Pad 1: Emitter

Pad 2: Base

Pad 3: Collector

Pad 4: Shielding connected to the lid

8206487 rev.6


*Note:* For JANS products: the pin out numbering for emitter and base is inverted (base is designated pin 1 and emitter pin 2)

**Table 8. UB package mechanical data**

Symbols	Dimensions in mm			Dimensions in inches (for reference only)		
	Min.	Typ.	Max.	Min.	Typ.	Max.
A	1.16		1.42	0.045		0.056
C	0.46	0.51	0.56	0.018	0.020	0.022
D	0.56	0.76	0.96	0.024	0.030	0.036
E	0.92	1.02	1.12	0.036	0.040	0.044
F	1.95	2.03	2.11	0.077	0.080	0.083
G	2.92	3.05	3.18	0.115	0.120	0.125
I	2.41	2.54	2.67	0.095	0.100	0.105
J	0.42	0.57	0.72	0.0165	0.0225	0.0285
K	1.37	1.52	1.67	0.054	0.060	0.066
L	0.41	0.51	0.61	0.016	0.020	0.024
M	2.46	2.54	2.62	0.097	0.100	0.103
N	1.81	1.91	2.01	0.071	0.075	0.079
N1	0.91	0.96	1.02	0.036	0.038	0.040
r		0.20			0.008	
r1		0.30			0.012	
r2		0.56			0.022	

## 4.2 LCC-3 package information

Figure 8. LCC-3 package outline



0041211 rev.13

Table 9. LCC-3 package mechanical data

Symbols	Dimensions in mm			Dimensions in inches (for reference only)		
	Min.	Typ.	Max.	Min.	Typ.	Max.
A	1.16		1.42	0.046		0.056
C	0.45	0.50	0.56	0.018	0.020	0.022
D	0.60	0.76	0.91	0.024	0.030	0.036
E	0.91	1.01	1.12	0.036	0.040	0.044
F	1.95	2.03	2.11	0.077	0.080	0.083
G	2.92	3.05	3.17	0.115	0.120	0.125
I	2.41	2.54	2.66	0.095	0.100	0.105
J	0.42	0.57	0.72	0.0165	0.0225	0.0285
K	1.37	1.52	1.67	0.054	0.060	0.066
L	0.40	0.50	0.60	0.016	0.020	0.024
M	2.46	2.54	2.62	0.097	0.100	0.103
N	1.80	1.90	2.00	0.071	0.075	0.079
R		0.30			0.012	

## 5 Ordering information

Table 10. Ordering information

Part number	Agency specification	EPPL	Quality level	Radiation level <sup>(1)</sup>	Package	Mass	Lead finish	Marking <sup>(2)</sup>	Packing	
J2N2222AUB1	-	-	Engineering model JANS	-	UB	0.6 g	Gold	J2222AUB1	WafflePack	
2N2222AUB1	-	-	Engineering model ESCC	-				2N2222AUB1		
SOC2222A1	-	-	Engineering model ESCC	-	LCC-3			SOC2222A1		
JANSR2N2222AUBG	MIL-PRF-19500/255	-	JANSR	100 krad	UB			0.6 g		JSR2222
JANSR2N2222AUBT		-	JANSR	high and low dose rate			Solder Dip		JSR2222	
JANS2N2222AUBG		-	JANS	-			Gold		JS2222	
JANS2N2222AUBT		-	JANS	-			Solder Dip		JS2222	
2N2222ARUBG	5201/002/11R	Yes	ESCC Flight	100 krad - low dose rate	UB		0.6 g	Gold	520100211R	Tape and reel
2N2222ARUBT	5201/002/12R							Solder Dip	520100212R	
2N2222ARUBTW	5201/002/12R							Gold	520100211	
2N2222AUBG	5201/002/11			-	LCC-3	0.6 g		Gold	520100211	WafflePack
2N2222AUBT	5201/002/12			-				Solder Dip	520100212	
SOC2222ARHRG	5201/002/04R			100 krad - low dose rate				Gold	520100204R	
SOC2222ARHRT	5201/002/05R			-				Solder Dip	520100205R	
SOC2222AHRG	5201/002/04			-	-	Gold		520100204	WafflePack	
SOC2222AHRT	5201/002/05			-	-	Solder Dip		520100205		
SOC2222AHRTW	5201/002/05			-	-	Solder Dip		520100205		Tape and reel

1. High dose rate as per MIL-PRF-19500 specification group D, subgroup 2 inspection. Low dose rate as per ESCC specification 22900.

2. Specific marking only. The full marking includes in addition: For the Engineering Models: ST logo, date code; country of origin (FR). For ESCC flight parts: ST logo, date code, country of origin (FR), ESA logo, serial number of the part within the assembly lot.

Contact ST sales office for information about specific conditions for products in die form.



## 6 Other information

### 6.1 Traceability information

The date code information is structured as described in the table below.

**Table 11. Date codes**

Model	Date code <sup>(1)</sup>
EM	3yywwN
ESCC	yywwN
JANS FLIGHT	WyywwN

1. yy = year, ww = week number, N = lot index in the week.

### 6.2 Documentation

**Table 12. Documentation provided for each type of product**

Quality level	Radiation level	Documentation
JANS Flight	-	Certificate of conformance
JANSR Flight	100 krad	Certificate of conformance RVT report (50 rad/s and 0.1 rad/s)
Engineering model	-	-
ESCC	-	Certificate of conformance ESCC qualification maintenance lot reference
ESCC	100 krad	Certificate of conformance ESCC qualification maintenance lot reference Radiation data <sup>(1)</sup> at 25 / 50 / 70 / 100 krad at 0.1 rad / s.

1. For key parameters on 5 biased parts + 5 unbiased parts from the same wafer as the delivered part. See Radiation hardness assurance for details.

## Revision history

**Table 13. Document revision history**

Date	Revision	Changes
04-Jan-2010	1	Initial release.
16-Apr-2010	2	Added Table 1 on page 1.
09-Jul-2010	3	Modified: Table 1 on page 1 and Table 12 on page 18.
30-Nov-2011	4	<ul style="list-style-type: none"> <li>– Modified: Table 5 on page 5.</li> <li>– Added: Section 2.3: Electrical characteristics (curves).</li> <li>– Modified: Table 1 and 2;</li> <li>– Added: Table 2, 11, 12.</li> <li>– Minor text changes in the document title and description on the cover page.</li> </ul>
12-Dec-2011	5	Minor text changes to improve readability;
17-Apr-2012	6	<p>Updated:</p> <ul style="list-style-type: none"> <li>– Title and description in cover page.</li> <li>– PTOT in Table 2: Absolute maximum ratings.</li> <li>– The entire Section 2: Electrical characteristics.</li> </ul> <p>Added:</p> <ul style="list-style-type: none"> <li>– Table 3: Thermal data, Section 3: Radiation hardness assurance and Table 13: Ordering information.</li> <li>– Figure 7: JANS saturated turn-on switching time test circuit and Figure 8: JANS saturated turn-off switching time test circuit.</li> <li>– Section 6: Shipping details.</li> </ul>
19-Apr-2012	7	Updated titles in Figure 7: JANS saturated turn-on switching time test circuit and Figure 8: JANS saturated turn-off switching time test circuit.
24-Apr-2012	8	Updated $R_{thJA}$ value in Table 3: Thermal data.
14-May-2012	9	Updated Table 13: Ordering information.
21-Feb-2013	10	Table 1: Device summary and Table 13: Ordering information have been updated. Updated text in Section 3: Radiation hardness assurance.
04-Apr-2013	11	Inserted Table 7: Radiation summary.
06-Jun-2013	12	Updated package name for UB.
18-Sep-2013	13	Table 1: Device summary and Table 13: Ordering information have been updated.
25-Mar-2014	14	Table 1: Device summary and Table 13: Ordering information have been updated. Updated Section 3: Radiation hardness assurance and Section 4: Package mechanical data. Inserted Figure 2: Safe operating area for LCC-3 and UB and Figure 3: Safe operating area for TO-18.
01-Apr-2014	15	Modified note in package silhouette on cover page.
29-May-2014	16	Updated Table 1: Device summary and Table 13: Ordering information.
17-Feb-2015	17	Updated Table 1.: Device summary. Minor text changes.
27-Feb-2015	18	Minor text changes.
05-May-2015	19	Updated Table 1.: Device summary. Minor text changes.
21-Aug-2015	20	Updated: Section 4.3: TO-18 package information. Minor text changes.
02-Apr-2020	21	Removed TO-18 package information. Minor text changes.
10-Jun-2020	22	Modified title and features table on cover page. Minor text changes.

## Contents

<b>1</b>	<b>Electrical ratings</b> .....	<b>2</b>
<b>2</b>	<b>Electrical characteristics</b> .....	<b>3</b>
<b>2.1</b>	JANS electrical characteristics .....	3
<b>2.2</b>	ESCC electrical characteristics .....	4
<b>2.3</b>	Electrical characteristics (curves) .....	5
<b>2.4</b>	Test circuits .....	6
<b>3</b>	<b>Radiation hardness assurance</b> .....	<b>7</b>
<b>3.1</b>	JANS radiation assurance .....	7
<b>3.2</b>	ESCC radiation assurance .....	8
<b>4</b>	<b>Package information</b> .....	<b>9</b>
<b>4.1</b>	UB package information .....	9
<b>4.2</b>	LCC-3 package information .....	11
<b>5</b>	<b>Ordering information</b> .....	<b>13</b>
<b>6</b>	<b>Other information</b> .....	<b>14</b>
<b>6.1</b>	Traceability information .....	14
<b>6.2</b>	Documentation .....	14
	<b>Revision history</b> .....	<b>15</b>



**IMPORTANT NOTICE – PLEASE READ CAREFULLY**

STMicroelectronics NV and its subsidiaries (“ST”) reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST’s terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers’ products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, please refer to [www.st.com/trademarks](http://www.st.com/trademarks). All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2020 STMicroelectronics – All rights reserved