


## Power Schottky rectifier



### Features

- High junction temperature capability
- Avalanche capability specified
- Insulated package: TO-220FPAB
  - Insulating voltage = 2000 V<sub>RMS</sub> sine
- ECOPACK<sup>®</sup>2 compliant component for D<sup>2</sup>PAK, I<sup>2</sup>PAK, TO-220AB and TO-220FPAB on demand

### Description

This device is a dual Schottky rectifier suited for high frequency switch mode power supply.

Available in TO-220AB, TO-220FPAB, I<sup>2</sup>PAK and D<sup>2</sup>PAK, this device is intended to be used in LCD screens or adaptors providing such applications with good efficiency at both low and high load.

Product status	
STPS15LCD80C	
Product summary	
<b>I<sub>F(AV)</sub></b>	2 x 7.5 A
<b>V<sub>RRM</sub></b>	80 V
<b>T<sub>j</sub> (max)</b>	175 °C
<b>V<sub>F</sub> (typ)</b>	0.635 V

# 1 Characteristics

**Table 1. Absolute ratings (limiting values, per diode, at T<sub>amb</sub> 25 °C, unless otherwise stated)**

Symbol	Parameter				Value	Unit
V <sub>RRM</sub>	Repetitive peak reverse voltage				80	V
I <sub>F(RMS)</sub>	Forward rms current				30	A
I <sub>F(AV)</sub>	Average forward current $\delta = 0.5$ , square wave	TO-220AB, D <sup>2</sup> PAK, I <sup>2</sup> PAK	T <sub>C</sub> = 145 °C	Per diode	7.5	A
			T <sub>C</sub> = 140 °C	Per device	15	
		TO-220FPAB	T <sub>C</sub> = 120 °C	Per diode	7.5	
			T <sub>C</sub> = 85 °C	Per device	15	
I <sub>FSM</sub>	Surge non repetitive forward current	t <sub>p</sub> = 10 ms sinusoidal		120	A	
P <sub>ARM</sub>	Repetitive peak avalanche power	t <sub>p</sub> = 10 $\mu$ s, T <sub>j</sub> = 125 °C		190	W	
T <sub>stg</sub>	Storage temperature range				-65 to + 175	°C
T <sub>j</sub>	Maximum operating junction temperature <sup>(1)</sup>				+ 175	°C

1.  $(dP_{tot}/dT_j) < (1/R_{th(j-a)})$  condition to avoid thermal runaway for a diode on its own heatsink.

**Table 2. Thermal parameter**

Symbol	Parameter			Value	Unit
R <sub>th(j-c)</sub>	Junction to case	TO-220AB, D <sup>2</sup> PAK, I <sup>2</sup> PAK	Per diode	3.50	°C/W
		TO-220FPAB		6.50	
		TO-220AB, D <sup>2</sup> PAK, I <sup>2</sup> PAK	Total	2.15	
		TO-220FPAB		5.05	
R <sub>th(c)</sub>	Coupling	TO-220AB, D <sup>2</sup> PAK, I <sup>2</sup> PAK	-	0.80	°C/W
		TO-220FPAB	-	3.60	

When the diodes 1 and 2 are used simultaneously:

$$\Delta T_j(\text{diode1}) = P_{(\text{diode1})} \times R_{th(j-c)} (\text{per diode}) + P_{(\text{diode2})} \times R_{th(c)}$$

**Table 3. Static electrical characteristics (per diode)**

Symbol	Parameter	Test conditions		Min.	Typ.	Max.	Unit
$I_R^{(1)}$	Reverse leakage current	$T_j = 25\text{ °C}$	$V_R = V_{RRM}$	-	2.5	10	$\mu\text{A}$
		$T_j = 125\text{ °C}$		-	2.3	7	$\text{mA}$
$V_F^{(2)}$	Forward voltage drop	$T_j = 25\text{ °C}$	$I_F = 10\text{ A}$	-	0.795	0.855	V
		$T_j = 125\text{ °C}$		-	0.635	0.680	
		$T_j = 25\text{ °C}$	$I_F = 20\text{ A}$	-	0.995	1.110	
		$T_j = 125\text{ °C}$		-	0.725	0.820	

1. Pulse test:  $t_p = 5\text{ ms}$ ,  $\delta < 2\%$


2. Pulse test:  $t_p = 380\text{ }\mu\text{s}$ ,  $\delta < 2\%$

To evaluate the conduction losses, use the following equation:


$$P = 0.540 \times I_{F(AV)} + 0.0187 I_F^2 (RMS)$$

## 1.2 Characteristics (curves)


**Figure 1. Average forward power dissipation versus average forward current (per diode)**




**Figure 2. Average forward current versus ambient temperature ( $\delta = 0.5$ , per diode)**




**Figure 3. Normalized avalanche power derating versus pulse duration ( $T_j = 125^\circ\text{C}$ )**




**Figure 4. Relative variation of thermal impedance junction to case versus pulse duration (TO-220AB, D^2PAK, I^2PAK)**





**Figure 5. Relative thermal impedance junction to case versus pulse duration (TO-220FPAB)**



**Figure 6. Reverse leakage current versus reverse voltage applied (typical values, per diode)**



**Figure 7. Junction capacitance versus reverse voltage applied (typical values, per diode)**

**Figure 8. Forward voltage drop versus forward current (per diode)**


## 2 Package information


---

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK® packages, depending on their level of environmental compliance. ECOPACK® specifications, grade definitions and product status are available at: [www.st.com](http://www.st.com). ECOPACK® is an ST trademark.

## 2.1 TO-220AB package information

- Cooling method: by conduction (C)
- Epoxy meets UL 94,V0
- Recommended torque value: 0.55 N·m
- Maximum torque value: 0.7 N·m

Figure 9. TO-220AB package outline



**Table 4. TO-220AB package mechanical data**


Ref.	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	4.40	4.60	0.173	0.181
b	0.61	0.88	0.240	0.035
b1	1.14	1.55	0.045	0.061
c	0.48	0.70	0.019	0.028
D	15.25	15.75	0.600	0.620
D1	1.27 typ.		0.050 typ.	
E	10.00	10.40	0.394	0.409
e	2.40	2.70	0.094	0.106
e1	4.95	5.15	0.195	0.203
F	1.23	1.32	0.048	0.052
H1	6.20	6.60	0.244	0.260
J1	2.40	2.72	0.094	0.107
L	13.00	14.00	0.512	0.551
L1	3.50	3.93	0.138	0.155
L20	16.40 typ.		0.646 typ.	
L30	28.90 typ.		1.138 typ.	
θP	3.75	3.85	0.148	0.152
Q	2.65	2.95	0.104	0.116



## 2.2 TO-220FPAB package information

- Cooling method: by conduction (C)
- Epoxy meets UL 94,V0
- Recommended torque value: 0.55 N·m
- Maximum torque value: 0.7 N·m

Figure 10. TO-220FPAB package outline




**Table 5. TO-220FPAB package mechanical data**

Ref.	Dimensions			
	Millimeters		Inches (for reference only)	
	Min.	Max.	Min.	Max.
A	4.40	4.60	0.1739	0.1818
B	2.5	2.7	0.0988	0.1067
D	2.50	2.75	0.0988	0.1087
E	0.45	0.70	0.0178	0.0277
F	0.75	1.0	0.0296	0.0395
F1	1.15	1.70	0.0455	0.0672
F2	1.15	1.70	0.0455	0.0672
G	4.95	5.20	0.1957	0.2055
G1	2.40	2.70	0.0949	0.1067
H	10.00	10.40	0.3953	0.4111
L2	16.00 typ.		0.6324 typ.	
L3	28.60	30.60	1.1304	1.2095
L4	9.80	10.6	0.3874	0.4190
L5	2.90	3.60	0.1146	0.1423
L6	15.90	16.40	0.6285	0.6482
L7	9.00	9.30	0.3557	0.3676
Dia	3.0	3.20	0.1186	0.1265

### 2.3 I<sup>2</sup>PAK package information

- Cooling method: by conduction (C)
- Epoxy meets UL 94,V0

Figure 11. I<sup>2</sup>PAK package outline




**Table 6. I<sup>2</sup>PAK package mechanical data**

Ref.	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	4.40	4.60	0.173	0.181
A1	2.40	2.72	0.094	0.107
b	0.61	0.88	0.024	0.035
b1	1.14	1.70	0.044	0.067
c	0.49	0.70	0.019	0.028
c2	1.23	1.32	0.048	0.052
D	8.95	9.35	0.352	0.368
e	2.40	2.70	0.094	0.106
e1	4.95	5.15	0.195	0.203
E	10.00	10.40	0.394	0.409
L	13.00	14.00	0.512	0.551
L1	3.50	3.93	0.138	0.155
L2	1.27	1.40	0.050	0.055

## 2.4 D<sup>2</sup>PAK package information

- Cooling method: by conduction (C)
- Epoxy meets UL 94,V0


Figure 12. D<sup>2</sup>PAK package outline



**Table 7. D<sup>2</sup>PAK package mechanical data**

Ref.	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	4.36	4.60	0.172	0.181
A1	0.00	0.25	0.000	0.010
b	0.70	0.93	0.028	0.037
b2	1.14	1.70	0.045	0.067
c	0.38	0.69	0.015	0.027
c2	1.19	1.36	0.047	0.053
D	8.60	9.35	0.339	0.368
D1	6.90	8.00	0.272	0.311
D2	1.10	1.50	0.043	0.060
E	10.00	10.55	0.394	0.415
E1	8.10	8.90	0.319	0.346
E2	6.85	7.25	0.266	0.282
e	2.54 typ.		0.100	
e1	4.88	5.28	0.190	0.205
H	15.00	15.85	0.591	0.624
J1	2.49	2.90	0.097	0.112
L	1.90	2.79	0.075	0.110
L1	1.27	1.65	0.049	0.065
L2	1.30	1.78	0.050	0.070
R	0.4 typ.		0.015	
V2	0°	8°	0°	8°

**Figure 13. D<sup>2</sup>PAK Recommended footprint**



### 3 Ordering information

**Table 8. Ordering information**

Order code	Marking	Package	Weight	Base qty	Delivery mode
STPS15LCD80CT	STPS15LCD80C	TO-220AB	1.95 g	50	Tube
STPS15LCD80CFP	STPS15LCD80C	TO-220FPAB	1.9 g	50	Tube
STPS15LCD80CR	STPS15LCD80C	I <sup>2</sup> PAK	1.5 g	50	Tube
STPS15LCD80CG-TR	STPS15LCD80C	D <sup>2</sup> PAK	1.38 g	1000	Tape and reel



## Revision history

**Table 9. Document revision history**

Date	Revision	Changes
13-Jan-2011	1	First issue.
16-Jun-2015	2	Updated features, and packages silhouette in cover page. Updated Section 2: "Characteristics" and Section 2.1:"Characteristics (curves)". Updated Section 3.2: "D <sup>2</sup> PAK package information".
16-Apr-2018	3	Updated <a href="#">Table 6. I<sup>2</sup>PAK package mechanical data</a> .

**IMPORTANT NOTICE – PLEASE READ CAREFULLY**

STMicroelectronics NV and its subsidiaries (“ST”) reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST’s terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers’ products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2018 STMicroelectronics – All rights reserved