


NUCLEO-U3C5ZIQ

MB2222 -U3C5ZIQ

Table of contents

- Sheet 1: Project Overview (this page)
- Sheet 2: Top
- Sheet 3: MCU I/Os
- Sheet 4: MCU Power
- Sheet 5: Connectors
- Sheet 6: Power Sources
- Sheet 7: Peripherals
- Sheet 8: M2 Serial Memory Connector
- Sheet 9: FDCAN
- Sheet 10: USB User
- Sheet 11: ST-LINK V3EC_LS
- Sheet 12: External Debug Interface

U_Top
Top.SchDoc



HW2

STICKER PRODUCT

N/A

HW1

PCB


MB2222

Legend

General comment such as function title, configuration, ...

Text to be added to silkscreen.

Warning text.



Open Platform License Agreement


The Open Platform License Agreement (“Agreement”) is a binding legal contract between you (“You”) and STMicroelectronics International N.V. (“ST”), a company incorporated under the laws of the Netherlands acting for the purpose of this Agreement through its Swiss branch 39, Chemin du Champ des Filles, 1228 Plan-les-Ouates, Geneva, Switzerland.

By using the enclosed reference designs, schematics, PC board layouts, and documentation, in hardcopy or CAD tool file format (collectively, the “Reference Material”), You are agreeing to be bound by the terms and conditions of this Agreement. Do not use the Reference Material until You have read and agreed to this Agreement terms and conditions. The use of the Reference Material automatically implies the acceptance of the Agreement terms and conditions.







The complete Open Platform License Agreement can be found on www.st.com/opla.

Title: Project Overview		
Project: NUCLEO-U3C5ZIQ		
Variant: U3C5ZIQ		
Revision: B-03		Reference: MB2222
Size: A4	Date: 9-Sep-2025	Sheet: 1 of 12








MCU IOs



STM32U3C5ZIT6Q



STM32U3C5ZIT6Q






Title: MCU IOs	
Project: NUCLEO-U3C5ZIQ	
Variant: U3C5ZIQ	
Revision: B-03	Reference: MB2222
Size: A4	Date: 9-Sep-2025
Sheet: 3 of 12	



MCU POWER SUPPLY



Operating range: $1V71 < VDD < 3V6$
 Operating range: $1V08 < VDDIO2 < 3V6$ (only for IO PG[2:15])
 Operating range: $1V65 < VBAT < 3V6$
 Operating range: $1V58$ (COMPs) / $1V6$ (DACs, OPAMP) / $1V62$ (ADCs) / $1V8$ (VREFBUF) $< VDDA < 3V6$
 Operating range: $1V58 < VREF < 3V6$ (depend of VDDA)
 Operating range: $1V71 < VDDSMPS < 3V6$

Operating range: $3V0 < VDDUSB < 3V6$



MCU DECAPS




Ceramic capacitor (Low ESR, ESR < 1ohm)



Title: STM32 microcontroller power	
Project: NUCLEO-U3C5ZIQ	
Variant: U3C5ZIQ	
Revision: B-03	Reference: MB2222
Size: A4	Date: 9-Sep-2025
Sheet: 4 of 12	



CONNECTORS





COLOR LEGEND
MORPHO SPECIFICATION
ARDUINO SPECIFICATION
STM32 ALTERNATE FUNCTION
STM32 IO PORT
FUNCTION NOT-AVAILABLE

ST MORPHO CONNECTOR LEFT SIDE





ARDUINO V3

Operating range: 3V < VCC < 3.6V

ST MORPHO CONNECTOR RIGHT SIDE



SB64, SB66 ON, ARD_D3 and ARD_D4 support ADF.
SB63, SB65 ON, ARD_D3 supports WAKE UP.
ARD_D3 supports SWO/Moto control TIM.




- (1): VIN (NUCLEO INPUT) WARNING voltage applied to 7V < VIN < 12V
- (2): 5V_EXT, AREF (NUCLEO INPUT)
- (3): 5V, 3V3, IOREF, 5V_STLK (NUCLEO OUTPUT, SHIELD INPUT)

POWER SOURCES


VIN / 5V PWR/ 800mA

Operating range: $7V < V_{IN} < 12V$



3V3 PWR/ 1.3A


Operating range: $4.5V < V_I < 5.5V$




1V8 PWR/ 1.3A

Operating range: $3V < V_I < 5.5V$

$$V_{out} = 1.22 * (1 + 27K/56K)$$




5V PWR SELECTION



5V_STLK from USB STLINK (500mA max)
 5V_VIN from Arduino (800mA max)
 5V_EXT from Morpho connector (1.3A max)
 5V_USB_SINK from USB User (0.5A max)

VDD SELECTION 1V8/3V3




GND HEADERS




PERIPHERALS

USER BUTTON




BOOT SELECT


DEFAULT = INTERNAL FLASH
B3 PRESSED = BOOTLOADER




RESET



LEDs



Peripherals




Title: Peripherals	
Project: NUCLEO-U3C5ZIQ	
Variant: U3C5ZIQ	
Revision: B-03	Reference: MB2222
Size: A4	Date: 9-Sep-2025
Sheet: 7 of 12	





M2 SERIAL-MEMORY CONNECTOR

3V3 / Max current budget 500mA



OctoSPI configuration:



	U3C5ZIQ	U5
D0	PG4	PF0
D1	PG5	PF1
D2	PG8	PF2
D3	PG2	PF3
D4	PG3	PG0
D5	PG6	PG1
D6	PG9	PG9
D7	PG10	PG10
CLK	PG13	PF4
NCLK	PG14	PF5



M2_SOCKET_SER-MEM_KEY_A
Socket 67pins



CAN FD




Operation Volatage: VDD: 4.5 ~ 5.5V; VIO: 1.8 ~ 5.5V

Title: FDCAN	
Project: NUCLEO-U3C5ZIQ	
Variant: U3C5ZIQ	
Revision: B-03	Reference: MB2222
Size: A4	Date: 9-Sep-2025
Sheet: 9 of 12	




USB Type-C, SNK Only, No UCPD


SINK PATH 2.5W / 5V / 500mA




5V_USB_LED




5V_USB_SINK



STLINK-V3EC



5V_STLK OVERVOLTAGE AND OVERCURRENT PROTECTION




5V_STLK OVERCURRENT PROTECTION MANAGEMENT


	T_PWR_SEL2/PD5	T_PWR_SEL1/PD4
PowerDefault.SNK (current limit: 550mA)	Hi-Z	Hi-Z
Power1.5.SNK (current limit: 1.66A)	Hi-Z	0
Power3.0.SNK (current limit: 3.2A)	0	0

Hi-Z = IO set in high impedance


EXTERNAL DEBUGGER SELECTION




ST-LINK POWER (3V3/300mA)




LED POWER STATUS




STMP2151STR is backup of the TPS25953DSG




INTERFACE WITH TARGET MCU




VOLTAGE LEVEL SHIFTER




STLINK MCU POWER




External Debug Interface



ESD PROTECTIONS




MIPI-20 CONNECTOR



^A Trace signals: 50Ω +/-10%


^A Specific constraints for MCU.SWDIO and MCU.SWCLK (must be same length and must be Shielded).






Project: NUCLEO-U3C5ZIQ	
Layer: M14-Top Assembly	Gerber: .GM14
Variant: U3C5ZIQ	MB2222
Date: 9-Sep-2025	Rev: B






Project: NUCLEO-U3C5ZIQ	
Layer: M15-Bottom Assembly	Gerber:.GM15
Variant: U3C5ZIQ	MB2222
Date: 9-Sep-2025	Rev: B





MB2222B



Product 25x9 sticker

GND

GND



PC8
PD15
PB4
5V
STLK
PB11
PA12
PA11
PE15
PA2
GND
PB2
PB1
PB15
PB14
PB13
AGND
PA3
PD12
PD11
PD3
PF8
PD10
PE12
PE9
PF14
GND
PG7
PG6
PG4
PG2
PG9
NC
PG10
PG12

PC9
PB6
PB7
AREF
GND
PA5
PA6
PA7
PD14
PC7
PE11
PA8
PB10
PC6
D4
D3
PE13
PD8
PD9
GND
PE0
PF10
PE14
PE10
PF15
PF11
PG8
PG5
PG3
PG15
GND
PG13
PG14
NC

SCL
D15
SDA
D14
AREF
GND
SCK
D13
MISO
D12
PWM
MOSI
D11
PWM
CS
D10
PWM
D9
IO
D8
IO
D7
PWM
D6
PWM
D5
IO
D4
PWM
D3
IO
D2
TX
D1
RX
D0

SB66

SB64

R89
R91
R93
R95
R97
R99
R101
R103

SB68
SB69
SB70
SB71
SB72
SB73
SB74
SB75

C86

C87 SB76

CN19

1

NC
IOREF
NRST
3V3
5V
GND
GND
GND
VIN
A0
A1
A2
A3
A4
A5

PC11
PD2
5V_EXT
GND
PD1
IOREF
NRST
3V3
5V
GND
GND
VIN
PD5
PA0
PA1
PA4
PB0
PC1
PC0
PE3
PE6
NC
PF0
PF1
PF4
PF3
PA9
PE1
GND
PF12
PG0
PD7
NC
NC

PC10
PC12
VDD
PH3
PF6
PF7
PA13
PA14
PA15
GND
PD13
PC13
PC14
PC15
PH0
PH1
VBAT
PC2
PC3
PE2
PE5
PE4
PF2
NC
PF5
PF9
NC
PD0
PD4
PF13
PG1
PD6
PB9
PB8

GND

GND