

STM32H5F5J Discovery Kit

MB2114 H5F5LJ

Table of contents

- Sheet 1: Project overview (this page)
- Sheet 2: MB2114 TOP
- Sheet 3: MCU System
- Sheet 4: MCU Power
- Sheet 5: MCU Interfaces
- Sheet 6: Board Power
- Sheet 7: Display
- Sheet 8: Camera
- Sheet 9: Sensor
- Sheet 10: User Interface
- Sheet 11: Octo SPI Flash
- Sheet 12: Octo SPI RAM Memory
- Sheet 13: Micro SD Card
- Sheet 14: Ethernet
- Sheet 15: USB Type C
- Sheet 16: Arduino UNO Rev3 Connectors
- Sheet 17: M2 Level Shifters
- Sheet 18: M2 Connectivity
- Sheet 19: STLINK V3EC
- Sheet 20: External Debug Connectors



Top.SchDoc

HW2

STICKER BOARD

N/A

HW14

PCB


MB2114

Legend

General comment such as function title, configuration, ...

Text to be added to silkscreen.

Warning text.



Open Platform License Agreement

The Open Platform License Agreement (“Agreement”) is a binding legal contract between you (“You”) and STMicroelectronics International N.V. (“ST”), a company incorporated under the laws of the Netherlands acting for the purpose of this Agreement through its Swiss branch 39, Chemin du Champ des Filles, 1228 Plan-les-Ouates, Geneva, Switzerland.


By using the enclosed reference designs, schematics, PC board layouts, and documentation, in hardcopy or CAD tool file format (collectively, the “Reference Material”), You are agreeing to be bound by the terms and conditions of this Agreement. Do not use the Reference Material until You have read and agreed to this Agreement terms and conditions. The use of the Reference Material automatically implies the acceptance of the Agreement terms and conditions.

The complete Open Platform License Agreement can be found on www.st.com/opla.


Title: Project overview		
Project: STM32H5F5J Discovery Kit		
Variant: H5F5LJ		
Revision: C-01		Reference: MB2114
Size: A4	Date: 09 July 2025	Sheet: 1 of 20




STM32H5F5J Discovery Kit



MCU System



STM32 microcontroller power



MCU Interfaces










UIC STM32H5F5LJH7Q

STM32H5F5 GPIOs	
PA0	L2 PA0-ADC12_INP0
PA1	L4 PA1-ETH_RMII_REF_CLK
PA2	M3 PA2-USART2_TX
PA3	M4 PA3-USART2_RX
PA4	N3 PA4-SPI1_NSS-LPTIM2_CH1
PA5	P2 PA5-TIM2_CH1
PA6	R2 PA6-OSPI1_IO3
PA7	P3 PA7-TIM14_CH1
PA8	G1 PA8
PA9	G13 PA9
PA10	F13 PA10-ETH_CLK
PA11	F15 PA11-SPI2_NSS
PA12	F14 PA12
PB0	R3 PB0-UART4_CTS
PB1	L6 PB1-OSPI1_NCLK
PB2	P4 PB2-LCD_R3
PB5	E7 PB5-SPI1_MOSI-TIM3_CH2
PB6	E8 PB6
PB7	A6 PB7-LCD_G7
PB8	C6 PB8-TIM16_CH1
PB9	A5 PB9-TIM17_CH1
PB10	M10 PB10-LCD_G4
PB11	P11 PB11-ETH_RMII_TX_EN
PB12	P14 PB12-ETH_RMII_TXD0
PB13	N13 PB13-SPI2_SCK
PB14	K11 PB14-UART4_RTS
PB15	M13 PB15-SDMMC2_D1
PC0	L1 PC0-ADC12_INP10
PC1	K2 PC1-ADC12_INP11
PC2	M1 PC2-I2S2_SDI
PC3	M2 PC3-ADC12_INP13
PC4	N4 PC4-ETH_RMII_RXD0
PC5	M5 PC5-OSPI1_DQS
PC6	L15 PC6-I2S2_MCK
PC7	H14 PC7
PC8	H13 PC8-SDMMC1_D0
PC9	G14 PC9-OSPI1_IO0
PC10	D12 PC10-SDMMC1_D2
PC11	B14 PC11-SDMMC1_D3
PC12	B15 PC12-TIM15_CH1
PC13	C3 PC13
PD0	E10 PD0-LCD_R2
PD1	C12 PD1-ETH_RMII_CRS_DV
PD2	D11 PD2-OSPI2_IO1
PD3	A14 PD3-LCD_B4
PD4	B13 PD4-LCD_B7
PD5	B12 PD5
PD6	A10 PD6-SDMMC2_CK
PD7	C9 PD7-SDMMC2_CMD
PD8	L12 PD8-LCD_R5
PD9	P15 PD9-LCD_R4
PD10	N14 PD10
PD11	N15 PD11-LCD_R6
PD12	M14 PD12-UART4_TX
PD13	L13 PD13-I3C1_SDA
PD14	I11 PD14
PD15	K12 PD15-TIM4_CH4
PE0	D6 PE0-OSPI1_NCS2
PE1	B5 PE1
PE2	B3 PE2-OSPI1_IO2
PE3	D5 PE3-LCD_G1
PE4	C4 PE4-LCD_G3
PE5	D4 PE5-ETH_RMII_RXD1
PE6	F6 PE6-TIM15_CH2
PE7	L8 PE7-UART7_RX
PE8	M8 PE8-UART7_TX
PE9	N8 PE9-OSPI1_IO6
PE10	N9 PE10-OSPI1_IO7
PE11	R10 PE11-LCD_B5
PE12	L9 PE12-ADC3_INP6
PE13	P10 PE13-ADC3_INP7
PE14	N10 PE14-OSPI2_CLK
PE15	R11 PE15-OSPI2_NCS1
PF0	E1 PF0-SDMMC2_D2
PF1	G4 PF1-SDMMC2_D3
PF2	F2 PF2
PF3	H5 PF3
PF4	G1 PF4
PF5	H4 PF5-OSPI2_DQS
PF6	H3 PF6-LCD_DE
PF7	H2 PF7-SDMMC1_D1
PF8	H1 PF8-TIM13_CH1
PF9	L4 PF9-OSPI1_IO1
PF10	K1 PF10-OSPI1_CLK
PF11	L7 PF11
PF12	P6 PF12
PF13	R6 PF13-LCD_B6
PF14	M7 PF14-LCD_G5
PF15	N7 PF15-OSPI2_NCS2





UID STM32H5F5LJH7Q

STM32H5F5 GPIOs	
PG0	P7 PG0-OSPI2_IO0
PG1	R7 PG1-SPI2_MOSI
PG2	L15 PG2-OSPI2_IO2
PG3	J12 PG3-OSPI2_IO3
PG4	K14 PG4-OSPI2_IO4
PG5	K15 PG5-OSPI2_IO5
PG6	J13 PG6-OSPI1_NCS1
PG7	H11 PG7-I3C1_SCL
PG8	J14 PG8-OSPI2_NCLK
PG9	B9 PG9-SPI1_MISO
PG10	A9 PG10-OSPI2_IO6
PG11	D8 PG11-SPI1_SCK
PG12	C8 PG12-ETH_RMII_TXD1
PG15	A7 PG15-OSPI2_IO7
PH2	N1 PH2-OSPI1_IO4
PH3	N2 PH3-OSPI1_IO5
PH4	P1 PH4-I2C2_SCL
PH5	K6 PH5-I2C2_SDA
PH6	N11 PH6
PH7	M11 PH7-I2C3_SCL
PH8	N12 PH8-I2C3_SDA
PH9	P13 PH9-LCD_R7
PH10	K10 PH10-TIM5_CH1
PH11	M12 PH11-I2C4_SCL
PH12	R14 PH12-I2C4_SDA
PH13	E15 PH13
PH14	E14 PH14
PI0	E12 PI0-I2S2_WS
PI1	D15 PI1-SDMMC2_D0
PI2	F10 PI2-SPI2_MISO
PI3	D14 PI3-I2S2_SDO
PI5	A4 PI5-LCD_R0
PI6	A3 PI6
PI7	B4 PI7
PI8	E4 PI8
PI9	E2 PI9-UART4_RX
PI10	C1 PI10
PI11	F3 PI11-LCD_B1
PI12	G3 PI12
PI13	G2 PI13
PI14	G2 PI14
PI15	N5 PI15
PJ0	R4 PJ0
PJ1	M6 PJ1
PJ2	P5 PJ2
PJ3	R5 PJ3
PJ4	N6 PJ4-LCD_G2
PJ5	P8 PJ5
PJ6	R8 PJ6-ETH_MDIO
PJ7	R9 PJ7-ETH_MDC
PJ8	P9 PJ8-LCD_R1
PJ9	N9 PJ9-LCD_CLK
PJ10	D13 PJ10-LCD_HSYNC
PJ11	C14 PJ11-LCD_VSYNC
PJ12	A13 PJ12
PJ13	C11 PJ13
PJ14	D10 PJ14
PJ15	E9 PJ15-LCD_G6
PK0	M15 PK0
PK1	L14 PK1
PK2	K13 PK2
PK3	A12 PK3
PK4	B11 PK4
PK5	C10 PK5
PK6	A11 PK6
PK7	B10 PK7-SDMMC1_CMD
PK8	D9 PK8-SDMMC1_CK
PK9	A2 PK9-I2C1_SCL
PK10	B2 PK10-I2C1_SDA
PK11	C2 PK11-LCD_B0
PK12	F5 PK12-LCD_B3
PK13	B1 PK13-LCD_B2
PK15	G5 PK15-LCD_G0
OTG_HSDP	G15 HSDP
OTG_HSDM	H15 HSDN


VDDIO2




- Free GPIOs**
- PI10, PI13, PI14, PI15, PJ0, PJ1, PJ2, PJ3, PJ5, PJ12, PJ13, PJ14, PK0, PK1, PK2, PK3, PK4, PK5, PK6, TP106, TP107, TP108, TP109, TP110, TP111, TP112, TP113, TP114, TP115, TP116, TP117, TP118, TP119, TP120, TP121, TP122, TP123, TP124




Board power



Display




Camera




HW13
DNF
CAM-55G1




Sensor




User Interface




OctoSPI Flash Memory




OctoSPI RAM Memory



μSD Card




Ethernet (10/100 Mbps)




USB-C Sink Only









SINK PATH (Bus Powered Mode)
2.5W / 5V / 500mA




Arduino UNO Rev3 Connectors



M2 Connectivity Level Shifters




STLINK-V3EC



STLINK

5V_STLK option for Board Power - Overvoltage and Overcurrent protection




5V_STLK OVERCURRENT PROTECTION MANAGEMENT




	T_PWR_SEL2/PD5	T_PWR_SEL1/PD4
PowerDefault.SNK (current limit: 550mA)	Hi-Z	Hi-Z
Power1.5.SNK (current limit: 1.66A)	Hi-Z	0
Power3.0.SNK (current limit: 3.2A)	0	0

Hi-Z = IO set in high impedance




Backup for 5V_STLK generation




ST-LINK Power (3V3/300mA)




External Debug Connectors






Project: STM32H5F5J Discovery Kit		
Layer: M14-Top Assembly	Gerber: .GM14	
Variant: H5F5LJ	Ref: MB2114	
Date: 09 July 2025	Rev: C	




Project: STM32H5F5J Discovery Kit		
Layer: M15-Bottom Assembly	Gerber: .GM15	
Variant: H5F5LJ	Ref: MB2114	
Date: 09 July 2025	Rev: C	



Top Overlay

.GTO



MB2114C

Bottom Overlay

.GBO