



STM32WL3x wireless MCU line

Wireless MCUs for efficient long-range communications





The STM32 portfolio

Five product categories

Wireless
MCU

Short- and long-range connectivity

Ultra-low-power
MCU

32-bit general-purpose microcontrollers: from 75 to 5,072 CoreMark score

Mainstream
MCU

High-performance
MCU

Embedded
MPU

32- and 64-bit microprocessors



Enabling edge AI solutions



Scalable security



[MPU portfolio](#)
[MCU portfolio](#)



sub-GHz connectivity in wireless applications

Smart industries



Smart cities



Smart agriculture



Smart homes



Asset tracking

Low-power, **global coverage, roaming**. Combined with sensing applications (accelerometer, pressure sensors).

Metering

Multiprotocol and low power
10 years from non-rechargeable battery
Fluid flow sensing
LCD driver

Alarm systems

Ultra-low-power Rx profile (**Rx sniff mode**) radio with combination of proprietary protocol support.

Remote controls

NEW

Efficient transmitter

Ultra-low-power modes with wake-up and retention capability.



STM32 sub-GHz product families



sub-GHz MCU dual core

sub-GHz MCU single core

sub-GHz transceiver

STM32WL55

STM32WLE5

STM32WL3x

1st generation SPIRIT1

2nd generation S2-LP

General-purpose sub-GHz radio

Ultra-low-power sub-GHz radio

Supported modulation

- 2 (G)FSK
- (G)MSK
-
- OOK
- ASK
-

- 2/4 (G)FSK
- (G)MSK
- BPSK (Sigfox)
- OOK
- ASK
- DSSS + IQ I/F (STM32WL3 only)

- 2 (G)FSK
- (G)MSK
- BPSK (Sigfox)
-
-
- LoRa

Supported protocols





Highly integrated, low-power MCU for long-range connectivity



Arm Cortex® M0+ core up to 64 MHz
+ sub-GHz dual radio



What the STM32WL3x offers

Lower design complexity

One single die in packages down to 5 x 5 mm integrating:

- 256 Kbytes of flash memory
- 2 radios: sub-GHz multi-modulation radio & wide band wake-up radio
- Analog sensing peripherals
- LCD driver

Flexibility

- Simple and ultra flexible platform with multiple modulation support: 4-(G)FSK up to 600 Kbps, 2-(G)FSK, (G)MSK, DBPSK, DSSS, OOK, ASK
- IQ interface to develop your own modulation for even more flexibility
- OOK always on wake-up radio

Longer battery life for IoT devices

- Low-power consumption radio down to 5.6 mA (Rx) & 10 mA (Tx at 10 dBm)*
- Additional dedicated wake-up on radio with 4.2 μ A always-on receiver for system wake-up

* Including MCU core consumption (in WFI mode)




Wireless MCU combining multiprotocol sub-GHz radio & application features



PACKAGES

- QFN48 6 x 6 mm
- QFN32 5 x 5 mm





High integration for reduced design complexity



Reliable & efficient system architecture

- Arm Cortex®-M0+ driving both applications and sub-GHz protocols
- Internal buses (AHB & APB): peripherals and sub-GHz radio IP interfaced with internal for concurrent access
- 2 x 16 Kbytes of SRAM banks: **up to 32 Kbytes** – selectable retention
- Up to 256 Kbytes of flash memory
- 1 byte of OTP Store ID, keys, and calibration data
- DMA controller with 8 channels

Integrated peripherals

- Standard peripherals (2 x SPI, 2 x I²C, UART, low-power UART)
- 12-bit ADC (1 Msp/s frequency, 8 channels, single-ended & differential, temperature, and battery level)
- Timers: 2 general-purpose 16-bit timers, 4+1 PWMs, watchdog timer, RTC, 3 specific sub-GHz IP timers (LP timer)
- Analog comparator and 6-bit DAC (threshold)
- Analog LC sensor
- Up to 20-pin LCD driver



STM32WL3x ultra-low-power dual radios

Highly efficient
sub-GHz radio



Dedicated ultra-low-power
Wideband wake-up radio

Main radio (RX/TX)
Rx current (LPM): **5.6 mA***
Tx current (10 dBm): **10 mA***



4.2 μ A always-on receiver
(from 100 MHz to 2.4 GHz)
Rx OOK at -50 dBm

With autonomous sequencer
sniff-mode, frequency hopping,
low duty-cycle mode,
listen before talk (LBT).

Zzzz

CPU

autonomous radio
management

Fully autonomous radio
for proximity detection tracking
Pass through factory application
Drive by metering application



* Including MCU core consumption (in WFI mode)



STM32WL3x main radio for long-range communication

Transmission: dual-output architecture

Up to **+16 dBm**
output power
(low-power
optimized)



Up to **+20 dBm**
output power
(long-range
capable)

Frequency range
159-185 MHz* / 276-319 MHz **
/ 413 – 479 MHz / 826 - 958 MHz


**Optimized for
your country regulation**

* Available on dedicated P/N: STM32WL33xxxxxA

** Available on STM32WL3R Line

Reception: Single-ended architecture

32-bit I/Q sampling:
**better sensitivity,
interference robustness**
(adjacent channel
blocking)




Rx sensitivity 2(G)FSK
-128 dBm at 0.3 kbps
-113 dBm at 38.4 kbps



Top-class RF performance



STM32WL3x main radio offers great versatility



One single platform



Multiprotocol capability



sub-GHz proprietary



802.15.4g


PLC-RF hybrid





STM32WL3x main radio provides a sequencer for extended battery life

Radio sequencer simplifies proprietary protocol support



Radio settings: full radio registers settings
Events: radio interrupts or low-power timer interrupts

Radio sequencer principle

- **Arm Cortex®-M0+ application NOT scheduled**
- Preloaded RAM-based chained list of RF actions
- Flexible actions (dynamic register setting changes)
- Scheduled with timers

Radio features - examples

- Rx sniff mode
- Dual-band Rx sniff mode
- FHSS (frequency hopping)
- High configurable CSMA
- Auto-ACK

⇒ **NO LIMIT**

Zzzz
CPU





STM32WL33 wake-up radio extends battery life



Ultra-low-power wireless proximity detection and system wake-up

Wide band: 1 single BOM for worldwide ISM
(from 100 MHz to 2.4 GHz)

**4.2 μ A
Continuous Rx**

Dedicated to proximity detection
(tens of meters) -50 dBm sensitivity

OOK modulated packet detection





STM32WL3 internal DC-DC converter

State-of-the-art efficiency

RF SoC architecture for battery-operated applications:

Application modes	Power modes	STM32WL3 current (*)
Standby	Deep-sleep current	<1.5 μ A (LSI on)
Transmission	+10 dBm	10 mA
	+14 dBm	22 mA
Reception with standard radio	Continuous Rx	5.6 mA
	Rx sniff mode	down to a few μ A average
Reception with wideband radio	Rx wake-up mode (OOK modulation)	4.2 μ A

Supply voltage range:

3.6 V
down to
1.7 V



(*) **Radio + CPU** power consumption characterization obtained at 3.3 V – 868 MHz radio band

The DC-DC converter can be bypassed thanks to internal LDOs.

Many application possibilities



WATER & GAS METERS

- **Ultra-low-power MCU**
960 nA deep-stop mode
LC sensors an LCD controller
- **Worldwide deployment**
Dual power output: +14 dBm & +20 dBm
WW RF bands: 169 MHz*, 433 MHz, 868 MHz, 915/920 MHz



ASSET TRACKING

- Ultra-low-power **wake-up radio**
→ 4.2 μ A **always on** receiver
→ (100 MHz to 2.4 GHz) Rx OOK at -50 dBm



HEAT COST ALLOCATORS

- **Internal LCD driver**
Up to 12x8 or 16x4 matrix elements
- **Outstanding sensitivity**
-132 dBm (OOK) / -128 dBm (FSK)



ALARM SYSTEMS

- **Low-power main radio**
Rx current (LPM): 5.6 mA
Tx current (10 dBm): 10 mA



REMOTE CONTROLS



- **Battery life extension**
14 nA shutdown mode with 6 wake-up pins
450 nA ultra-deep-stop with RAM retention
- **Worldwide deployment**
315 MHz, 433 MHz, 868 MHz, 915/920 MHz



SMART HOMES

- **Multiple modulations, protocols**
4-(G)FSK up to 600 Kbps, 2-(G)FSK, (G)MSK, DBPSK, DSSS, OOK, ASK
- **+ IQ interface**



* 169MHz available on dedicated P/N (STM32WL3xxxxxA)



STM32WL3x product lines tailored for your application needs

	Applications	Flash	Package	Radio	SPI/ UART	I2C	ADC	LCD/LCSC/ COMP/DAC
STM32WL33x Metering line	Water/ gas meters Heat cost allocators	Up to 256 KB	QFN32 and QFN48	Main radio + wake-up on radio	✓	✓	✓	✓
STM32WL31x IoT line	IoT sensors IoT asset tracking	Up to 128 KB	QFN32 and QFN48	Main radio	✓	✓	✓	
NEW STM32WL3Rx Remote control line	Remote controls Garage door openers	Up to 128 KB	QFN32 up to 6 wake-up pins	Main radio	✓	✓	2ch*	
STM32WL30x Modem line	Open coprocessor	Up to 128 KB	QFN32	Main radio	✓			

*ADC channels





STM32WL3x global radio compliance

	169 MHz	315 MHz	433 MHz	868/920 MHz
	159-185 MHz	276-319 MHz	413-479 MHz	826-958 MHz
STM32WL33x Metering line	✓ on dedicated P/N (STM32WL3xxxxxA)		✓	✓
STM32WL31x IoT line			✓	✓
NEW STM32WL3Rx Remote control line		✓	✓	✓
STM32WL30x Modem line			✓	✓



STM32WL3x low-power modes

Low-power mode	DEEP STOP + WAKE-UP RADIO	DEEP STOP	ULTRA DEEP STOP	SHUTDOWN
Current	4.2 μ A	960 nA	450 nA	14 nA
Wake-up sources	Wake-up radio + All GPIO	All GPIO	Wake-up pin + RST	Wake-up pin + RST
RAM retention	Up to 32KB SRAM	Up to 32KB SRAM	Up to 16KB SRAM	N/A
STM32WL33x Metering line	✓	✓		✓ Up to 1 wake-up pin
STM32WL31x IoT line		✓		✓ Up to 1 wake-up pin
STM32WL3Rx Remote control line		✓	✓ Up to 6 wake-up pins	✓ Up to 6 wake-up pin
STM32WL30x Modem line		✓		✓ Up to 1 wake-up pin

NEW



STM32WL33: metering line (1/2)

Extending battery lifetime in smart metering applications

Multi-band support

169 MHz*, 433 MHz, 868 MHz, 915/920 MHz

Dual radio

Main radio + wake up on radio

Ready for analog metering

ADC + DAC + COMP

LC-based measurement of fluid flow metering (AFE + Digital)

LCD driver supporting up to 96 segments

Applications



Water & gas metering



Heat cost allocators



Packages

QFN48 6 x 6 mm
QFN32 5 x 5 mm

Arm Cortex®-M0+ Up to 64 MHz	Memory	Connectivity	Main radio
Nested vector interrupt controller (NVIC) Memory protected unit (MPU) SWD interface	Flash up to 256 KB 10 k cycles, 2 KB page	Up to 2x SPI (with 1x I2S) 2x I2C 1x USART 1x LPUART	8 mA @ + 10 dBm Tx 4 mA Rx
	RAM up to 32 KB (full retention)		2-(G)FSK, 4-(G)FSK, (G)MSK, OOK, ASK, DSSS, DBPSK
	1 KB OTP	Up to 32 GPIOs	Up to + 20 dBm Tx power -132 dBm Rx sensitivity
Accelerators	Security	Timers	413-479 MHz 826-958 MHz 159-185 MHz*
CRC calculation unit	AES 128 16-bit TRNG 64-bit unique ID	2x 16-bit GP timers 1x LP timer RTC	16-bit IQ access
DMA 8 channels	Secure boot with SWD disabling	Watchdog: IWDG SysTick	Direct radio registers access
	Bootloader with write and readout protection		
System	Analog	Display	Wake-up on radio
48 MHz (radio + HSE) 64 MHz HIS 32.768 kHz (LSE) Internal 32 kHz RCO (LSI)	12-bit ADC SAR 1 Msps	LCD driver 12x8 / 16x4	Rx OOK @-50 dBm
RTC 20 bytes backup registers	Temperature sensor	Fluid sensor controller	100 MHz- 2.4 GHz
LDO, POR/PDR/PVD/BOR VDD 1.7-3.6V	Analog comparator + DAC	2x LC channel (wheel rotation) 1x LC channel (tamper)	Down to 4uA always on

Radio features

MCU features

*159-185MHz on dedicated P/N (STM32WL3xxxxxA)







STM32WL33 for metering applications (2/2)

Ultra-low-power analog sensing unit based on L-C sensor controller for monitoring fluid flow

- Designed for **cost-effective** **mechanic-wheel fluid metering**
 - Measuring of L-C network oscillations enable detection of fluid flow metering
- The feature is based on L-C network oscillation measurement
 - Supporting **up to 3x L-C** networks
 - **Autonomous metering circuitry** (no CPU intervention, Arm Cortex® M0+ in deep stop)
 - **Very little μA average current** for continuous L-C metering



STM32WL31: IoT line

Empowering IoT with precision sensing, seamless connectivity, and energy efficiency

Ready for ISM bands

433 MHz, 868 MHz, 915 MHz/920 MHz

Connecting actuators & digital sensors

Up to 32 GPIO
PWM, I2C, LPUART, USART, 2xSPI

Connecting analog sensors

Internal ADC with single ended and differentials
For analog sensors monitoring

Applications



Environment sensors



Asset tracking



Smoke & fire alarms



Packages

QFN48 6 x 6 mm
QFN32 5 x 5 mm

Arm Cortex®-M0+ Up to 64 MHz Nested vector interrupt controller (NVIC) Memory protected unit (MPU) SWD interface	Memory Flash up to 256 KB 10 k cycles, 2 KB page RAM up to 16 KB (full retention) 1 KB OTP	Connectivity Up to 2x SPI (with 1x I2S) 2x I2C 1x USART 1x LPUART Up to 32 GPIOs	Main radio 8 mA @ + 10 dBm Tx 4 mA Rx 2-(G)FSK, 4-(G)FSK, (G)MSK, OOK, ASK, DSSS, DBPSK Up to + 20 dBm Tx power -132 dBm Rx sensitivity	
	Accelerators CRC calculation unit DMA 8 channels	Security AES 128 16-bit TRNG 64-bit unique ID Secure boot with SWD disabling Bootloader with write and readout protection	Timers 2x 16-bit GP timers 1x LP timer RTC Watchdog: IWDG SysTick	413-479 MHz 826-958 MHz 16-bit IQ access Direct radio registers access
	System 48 MHz (radio + HSE) 64 MHz HIS 32.768 kHz (LSE) Internal 32 kHz RCO (LSI) RTC 20 bytes backup registers LDO, POR/PDR/PVD/BOR VDD 1.7-3.6V	Analog 12-bit ADC SAR 1 Msps Temperature sensor		

Radio features

MCU features





STM32WL3R: remote control line

Small footprint, maximum battery life, and simplified remote-control design

Universal remote control

4 bands supported on the same P/N:
315 MHz, 433 MHz, 868 MHz, 915MHz/920 MHz

Tailored for remote controls

Small footprint: 5x5mm, Up to 18 GPIOs, Cortex®-M0+-based
Available in TX only: P/N STM32WL3R-X

Long battery life

Internal SMPS, Tx current (10dBm): 10 mA
450nA ultra-deep-stop with RAM retention
14 nA shutdown mode with 6 wake-up pins

Applications



Garage openers



Call/bell systems



Wireless key pads



Packages
QFN32 5 x 5 mm

Arm Cortex®-M0+ Up to 64 MHz Nested vector interrupt controller (NVIC) Memory protected unit (MPU) SWD interface	Memory Flash up to 128 KB 10 k cycles, 2 KB page RAM up to 16 KB (full retention) 1 KB OTP	Connectivity Up to 1x SPI 1x I2C 1x USART 1x LPUART Up to 18 GPIOs 6 wakeup pins* from shutdown	Main radio 8 mA @ + 10 dBm Tx 4 mA Rx 2-(G)FSK, 4-(G)FSK, (G)MSK, OOK, ASK, DSSS, DBPSK Up to + 20 dBm Tx power -132 dBm Rx sensitivity	
	Accelerators CRC calculation unit DMA 8 channels	Security AES 128 16-bit TRNG 64-bit unique ID Secure boot with SWD disabling Bootloader with write and readout protection	Timers 2x 16-bit GP timers 1x LP timer RTC Watchdog: IWDG SysTick	413-479 MHz 826-958 MHz 276-319 MHz* 16-bit IQ access Direct radio registers access
	System 48 MHz (radio + HSE) 64 MHz HIS 32.768 kHz (LSE) Internal 32 kHz RCO (LSI) RTC 20 bytes backup registers LDO, POR/PDR/PVD/BOR VDD 1.7-3.6V	Analog 12-bit ADC SAR 1 Msps Temperature sensor		

Radio features

MCU features

*Available only for STM32WL3R product line



STM32WL30: modem line

The best fit for hosted applications

Ready for ISM bands

433 MHz, 868 MHz, 915 MHz

Open SoC architecture


Develop your own wireless co-processor based on STM32WL3 SoC

With minimalist peripheral set

For host connectivity
GPIO, UART & SPI



Packages
QFN32 5 x 5 mm




Arm Cortex®-M0+ Up to 64 MHz Nested vector interrupt controller (NVIC) Memory protected unit (MPU) SWD interface	Memory Flash up to 128 KB 10 k cycles, 2 KB page RAM up to 16 KB (full retention) 1 KB OTP	Connectivity Up to 1x SPI 1x USART 1x LPUART Up to 17 GPIOs	Main radio 8 mA @ + 10 dBm Tx 4 mA Rx 2-(G)FSK, 4-(G)FSK, (G)MSK, OOK, ASK, DSSS, DBPSK Up to + 20 dBm Tx power -132 dBm Rx sensitivity	
	Accelerators CRC calculation unit DMA 8 channels	Security AES 128 16-bit TRNG 64-bit unique ID Secure boot with SWD disabling Bootloader with write and readout protection	Timers 2x 16-bit GP timers 1x LP timer RTC Watchdog: IWDG SysTick	413-479 MHz 826-958 MHz 16-bit IQ access Direct radio registers access
	System 48 MHz (radio + HSE) 64 MHz HIS 32.768 kHz (LSE) Internal 32 kHz RCO (LSI) RTC 20 bytes backup registers LDO, POR/PDR/PVD/BOR VDD 1.7-3.6V			

Radio features MCU features



STM32WL3x and SPIRIT portfolio



Legend: Transceiver only ● Available in 169 MHz on dedicated P/N (STM32WL3xxxxxA) ● TX-only version available

Single Cortex®-M0+ legend: Metering line IoT line Modem line Remote control line



STM32CubeWL3 framework

Tools and software supporting you throughout all your design steps

Evaluation,
prototyping
and selection

Hardware and
software
configuration

Application development and debug

Code and hardware
options
programming

Runtime
application
monitoring



Worldwide support channels

STM32WL3x & wireless protocols firmware

Comprehensive stack offer



Proprietary & 802.15.4

Mioty stack	OMS stack	wM-Bus applications	Sigfox applications	sub-GHz radio examples
<p>Modes Z (UL) and A (UL & DL)</p> <p>Uplink (UL) encoding interleaving, FEC, symbol mapping</p> <p>Downlink (DL) via IQ I/F demodulation & decoding</p> 	<p>OMSV4.5.1 ready for end device & for gateway devices</p> <p>Application layers (APL) transportation layers (TPL) authentication & fragmentation extended data link layers</p> 	<p>Meter and concentrator mode T2, C2, S2, and concurrent (T+C) examples.</p>	<p>CLI interface for Sigfox commands. Push-button transmission demo.</p>	<p>802.15.4g & basic mode based on flexible packet handler</p> <p>Rx sniff mode, CSMA, LBT based on RF sequencer</p> <p>Wakeup radio and low-power applications</p>
<p>Low layers & HAL radio drivers</p>				

Available via partners

Available in STM32CubeWL3

Radio development tools



WiSE-RadioExplorer


The **STM32CubeWISEre** is a graphical user interface to interact with the STM32WL3x line devices and evaluate their radio capabilities.

WiSE-RadioCodeGen

The **STM32CubeWISEcg** is a PC application that can be used to build a flow graph which defines the radio actions to execute under specific conditions, using the sequencer driver.

Development tools for the STM32WL3x


Speed-up evaluation, prototyping, and design



**NUCLEO-WL33CC1
& NUCLEO-WL33CC2**

High band 826-958 MHz (for NUCLEO-WL3xxx1)
and low band 413-479 MHz (for NUCLEO-WL3xxx2)

QFN48 6 x 6 mm
STM32WL30/31/33




**NUCLEO-WL3RKB1
& NUCLEO-WL3RKB2**

Available soon

QFN32 5 x 5 mm
STM32WL3R

Resources to get you started: schematics, layout, BoM, and firmware examples




Free reference designs
STDES-WL3xxxxx

\$0

RF bands: 169, 315, 433, 868, 915/920 MHz
Power output: 10 dBm, 16 dBm, 20 dBm

Both QFN32 and QFN48
on 2L and 4L PCB STM32WL3x

RF IPD products as companion chips to the STM32WL3



Releasing your creativity



[@STM32](#)



[@ST_World](#)



[community.st.com](#)



[www.st.com/stm32wl3x](#)



[wiki.st.com/stm32mcu](#)



[github.com/stm32-hotspot](#)



[STM32 MCU Developer Zone](#)



[STM32WL3x blog article](#)



Our technology starts with You



Find out more at www.st.com/stm32wl3x

© STMicroelectronics - All rights reserved.

ST logo is a trademark or a registered trademark of STMicroelectronics International NV or its affiliates in the EU and/or other countries.

For additional information about ST trademarks, please refer to www.st.com/trademarks.

All other product or service names are the property of their respective owners.

